

Customer Part:

Description

The IQXT-260-17 employs an analogue ASIC for the oscillator and a high-order temperature compensation circuit in a 2.5 x 2.0mm size package. Model IQXT-260-17

2

Model Issue number

Frequency Parameters

Frequency

- 19.20MHz Frequency Tolerance ±1.00ppm
- @ 25°C ±2°C **Tolerance Condition**
- -±0.50ppm
- Frequency Stability
- **Operating Temperature Range** -30.00 to 85.00°C Ageing
 - ±0.7ppm max over 1yr @ 25°C
- Frequency Stability: TA varied over operating temperature range, measurement referenced to frequency observed with Fref=(Fmax+Fmin)/2, Vs=1.8V, VC=0.9V and load=10kΩ//10pF.
- Frequency Slope (minimum of one frequency reading every 2°C and VC=0.9V):
- -10°C to 60°C: 0.05ppm/°C max
- Frequency Drift (calculated from frequency slope with temperature varied at a maximum of 1.92°C/min (0.032°C/s) over -10°C to 60°C): 1.6ppb/sec max
- Frequency Slope (minimum of one frequency reading every 2°C and VC=0.9V):
- -30°C to 85°C: 0.1ppm/°C max
- Frequency Drift (calculated from frequency slope with temperature varied at a maximum of 0.96°C/min (0.016°C/s) over -30°C to 85°C): 1.6ppb/sec max
- Note: Frequency Drift rate is calculated from the equation ppb/s=°C/s x ppb/°C.
- Small Thermal Cycle Frequency Slope (measured at 0.5°C intervals over any 5°C heating and 5°C cooling cycle, at a minimum rate of 1°C/minute within the operating temperature range): 50ppb/°C max (Note: Discard the first 0.5°C interval of each heating and

cooling cycle.)


- Small Thermal Cycle Hysteresis (difference in frequency measurements over any 5°C heating and 5°C cooling cycle, at a minimum rate of 1°C/minute within the operating temperature range): 50ppb pk-pk max
- Supply Voltage Variation (±5% change @ 25°C): ±0.1ppm max
- Load Variation (±10% change @ 25°C): ±0.2ppm max
- Reflow Variation (after two consecutive reflows as per profile shown and 1hr recovery @ 25°C): ±1ppm max
- Note: Parts should be shielded from drafts causing unexpected thermal gradients. Temperature changes due to ambient air currents can lead to short term frequency drift.

Electrical Parameters


- Supply Voltage
- Current Draw
- Supply Current (@ TA=25°C, Vs max and load=10kΩ//10pF): 1 5mA max

1.8V ±5%


1.500mA







Pb-Free Reflow



Sales Office Contact Details: UK: +44 (0)1460 270200

Germany: 0800 1808 443

France: 0800 901 383 USA: +1.760.318.2824 Email: info@iqdfrequencyproducts.com Web: www.iqdfrequencyproducts.com





Customer Part:

Pulling

Frequency Adjustment

±15.6ppm to ±24.0ppm 0.9V ±0.6V

500kΩ

- Control Voltage
- Input Impedance
- Input Impedance: Measured between control voltage and GND pins.
- Linearity (deviation from a straight line curve fit): 20% max

Output Details

- **Output Compatibility**
- **Clipped Sine**

10kΩ//10pF ±10%

- Drive Capability
- Output Voltage Level (@ TA=25°C, Vs min and load=10kΩ//10pF): 0.8V pk-pk min
- Start Up Time (frequency within ±0.5ppm of steady state frequency): 0.5ms max
- Output: DC coupled
- Note: AC-coupled output requires an external capacitor, ≥1nF recommended.

Noise Parameters

- Phase Noise @ 25°C (max):
 - -86dBc/Hz @ 10Hz
 - -110dBc/Hz @ 100Hz
 - -137dBc/Hz @ 1kHz
 - -143dBc/Hz @ 10kHz
- -150dBc/Hz @ 100kHz
- Harmonics: -5dBc max

Environmental Parameters

- Storage Temperature Range: -40 to 85°C
- Shock: MIL-STD-202 M213: Half sine wave acceleration of 3000G peak amplitude, duration 0.3ms, velocity 12.3ft/s.
- Vibration: JESD22-B103-B: 10G peak acceleration for 20mins, 12 cycles in each of the 3 orientations, tested from 10-2000Hz.
- Moisture Resistance: MIL-STD-202 M106g: 1000hrs @ 85°C, 85% RH, biased.
- Thermal Cycling: JESD22 Method JA-104C: 1000 temperature cycles, where each cycle consists of a 25mins soak time @ -40°C followed by a 25mins soak time @ 85°C, with a 60secs maximum transition time between temperatures, air to air transition.
- Note: Frequency shift ≤1ppm after environmental conditions.

Manufacturing Details

Maximum Process Temperature: 260°C (40secs max)

Compliance

- RoHS Status (2015/863/EU) Compliant
- **REACh Status**
- Compliant MSL Rating (JDEC-STD-033): Not Applicable

Packaging Details

- Pack Style: Reel Tape & reel in accordance with EIA-481-D Pack Size: 3,000
- Alternative packing option available

Sales Office Contact Details:

UK: +44 (0)1460 270200 Germany: 0800 1808 443 France: 0800 901 383 USA: +1.760.318.2824 Email: info@iqdfrequencyproducts.com Web: www.iqdfrequencyproducts.com