

Material:

Insulator: PBT UL 94V-0

Contact: Brass

Front Shell: SPCC, Nickel plated over Cu

Rear Shell: SPCC, Tin plated over Cu

Ordering Code

CD51 50 S * 1 **A
① ② ③ ④ ⑤ ⑥

① Series No.

② No. of Circuits:

③ Contact type: S= Receptacle(Female)

④ Plating option:

2= Gold flash plated over Nickel

A= Selective Gold flash plated over Nickel

⑤ Color: 1= Black


⑥ Other Option:





00-A= With $\phi 3.10$ mm holes on shell(Standard)

A0-A= Riveted #4-40 UNC close nuts on front shell

C0-A= Riveted #4-40 UNC open nuts on rear shell

G1-A= Riveted #4-40 UNC open nuts on rear shell &
With #4-40 Hexagon Screw



Mounting Style				RoHS Compliant			
Code	00-A	Code	A0-A	Code	C0-A	Code	G1-A
		DIM. L= 5.8mm 		DIM. L= 4.0mm 		DIM. L1= 4.8mm DIM. L2= 4.0mm 	

4					DATE	UNIT: mm / inch	TITLE: D-SUB MALE 50P SOLDER CUP TYPE	 瀚荃股份有限公司 CviLux Corporation			
3				DRAWN BY:	Wayne	2/24-25'	TOLERANCE UNLESS OTHERWISE SPECIFIED				
2				ENGINEER:	Sun	2/24-25'	.X ±0.35/.014 X' ±	DRAWING NO. CD5158S1 PART NO. CD5150S*1**-A			
1				CHECKED BY:	Eisley	2/24-25'	.XX ±0.25/.010 X' ±				
SYM	NAME	DATE	REVISIONS	APPROVED BY:	Eisley	2/24-25'	.XXX ±0.15/.006 X' ±	FINISH:	SCALE	2 / 1	SHEET 1 OF 1