




Material:

Insulator: PBT UL 94V-0

Contact: Brass

Front Shell: SPCC, Nickel plated over Cu

Rear Shell: SPCC, Tin plated over Cu

Ordering Code

CD51 ** P 2 1 **-A
① ② ③ ④ ⑤ ⑥

① Series No.

② No. of Circuits: 9,15,25,37

③ Contact type: P= Plug(Male)

④ Plating option:

2= Gold flash plated over Nickel

⑤ Color: 1= Black

⑥ Other Option:

00-A = With 3.05mm holes on shell(Standard)

A0-A = Riveted #4-40 UNC close nuts on front shell

B0-A = Riveted #4-40 UNC open nuts on front shell

G1-A = Rivet nut lock screw

Circuits	Dimension			
	A	B	C	D
9	24.99(.984)	30.80(1.213)	16.95(.667)	19.28(.759)
15	33.32(1.312)	39.20(1.543)	25.30(.996)	27.51(1.083)
25	47.04(1.852)	53.05(2.089)	39.00(1.535)	41.28(1.625)
37	63.50(2.500)	69.40(2.732)	55.40(2.181)	57.30(2.256)

Mounting Style

Code	00-A	Code	A0-A	Code	B0-A	Code	G1-A
			DIM. L= 5.8mm		DIM. L= 4.0mm		DIM. L1= 4.0mm DIM. L2= 4.8mm

4					DATE	UNIT: mm / inch	TITLE: D-SUB SOLDER CUP SERIES	瀚荃股份有限公司 CviLux Corporation			
3				DRAWN BY: Jack	8/30-24'	TOLERANCE UNLESS OTHERWISE SPECIFIED	MATERIAL:				
2				ENGINEER: Sun	8/30-24'	.X ±0.25/.010 X' ±1'		DRAWING NO. CD5154S1	PART NO. CD51**P21**-A		
1				CHECKED BY: Eisley	8/30-24'	.XX ±0.15/.006 .X' ±	FINISH:	SCALE 2 / 1	SHEET 1 OF 1		
SYM	NAME	DATE	REVISIONS	APPROVED BY: Eisley	8/30-24'	.XX' ±					