






Circuits	Dimension			
	A	B	C	D
9	24.99(.984)	30.80(1.213)	16.35(.643)	19.28(.759)
15	33.30(1.311)	39.20(1.543)	24.75(.974)	27.65(1.089)
25	47.04(1.852)	53.05(2.089)	38.35(1.510)	41.28(1.625)
37	63.50(2.500)	69.40(2.732)	54.75(2.156)	57.30(2.256)

Material:

Insulator: PBT UL 94V-0

Contact: Brass

Front Shell: SPCC, Nickel plated over Cu

Rear Shell: SPCC, Tin plated over Cu

Ordering Code

CD51 ** S 2 1 **-A
① ② ③ ④ ⑤ ⑥

① Series No.

② No. of Circuits: 9,15,25,37

③ Contact type: S= Receptacle(Female)

④ Plating option:

2= Gold flash plated over Nickel

⑤ Color: 1= Black

⑥ Other Option:

00-A = With $\phi 3.05$ mm holes on shell(Standard)

A0-A = Riveted #4-40 UNC close nuts on front shell

C0-A = Riveted #4-40 UNC open nuts on rear shell

G1-A = Rivet nut lock screw

Mounting Style

Code	00-A	Code	A0-A	Code	C0-A	Code	G1-A
			DIM. L= 5.8mm		DIM. L= 4.0mm		DIM. L1= 4.0mm DIM. L2= 4.8mm

4					DATE	UNIT: mm / inch	TITLE:	瀚荃股份有限公司 CviLux Corporation			
3				DRAWN BY:	Jack	8/30-24'	D-SUB SOLDER CUP SERIES				
2				ENGINEER:	Sun	8/30-24'	MATERIAL:	DRAWING NO.	CD5156S1	PART NO.	CD51**S21**-A
1				CHECKED BY:	Eisley	8/30-24'	FINISH:	SCALE	2 / 1	SHEET	1 OF 1
SYM	NAME	DATE	REVISIONS	APPROVED BY:	Eisley	8/30-24'					