
Vishay Siliconix



EL Series Power MOSFET



PRODUCT SUMMARY				
V _{DS} (V) at T _J max.	650			
R _{DS(on)} typ. (Ω) at 25 °C	$V_{GS} = 10 V$	0.035		
Q _g max. (nC)	342			
Q _{gs} (nC)	34			
Q _{gd} (nC)	57			
Configuration	Single			

FEATURES

- Low figure-of-merit (FOM) Ron x Qa
- Low input capacitance (C_{iss})
- Reduced switching and conduction losses
- Ultra low gate charge (Qg)
- Avalanche energy rated (UIS)
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Server and telecom power supplies
- Switch mode power supplies (SMPS)
- Power factor correction power supplies (PFC)
- Lighting
 - High-intensity discharge (HID)
 - Fluorescent ballast lighting
- Industrial
 - Welding
 - Induction heating
 - Motor drives
 - Battery chargers
 - Renewable energy
 - Solar (PV inverters)

ORDERING INFORMATION	
Package	TO-247AC
Lead (Pb)-free and halogen-free	SiHG73N60AEL-GE3

ABSOLUTE MAXIMUM RATINGS ($T_c = 25 \degree C$, unless otherwise noted)						
PARAMETER		SYMBOL	LIMIT	UNIT		
Drain-source voltage		V _{DS}	600	N		
Gate-source voltage	V _{GS}	± 30	V			
Continuous drain current (T _J = 150 °C)	V_{GS} at 10 V $\frac{T_C = 25 \degree C}{T_C = 100 \degree C}$	- I _D	69			
	V_{GS} at 10 V $T_C = 100 \text{ °C}$		44	A		
Pulsed drain current ^a	I _{DM}	206	1			
Linear derating factor			4.2	W/°C		
Single pulse avalanche energy ^b		E _{AS}	1706	mJ		
Maximum power dissipation		PD	520	W		
Operating junction and storage temperature range		T _J , T _{stg}	-55 to +150	°C		
Reverse diode dv/dt d		dv/dt	3.2	V/ns		
Soldering recommendations (peak temperature) ^c	For 10 s		260	°C		

Notes

Initial samples marked as SiHG73N60BE

a. Repetitive rating; pulse width limited by maximum junction temperature

b. V_{DD} = 120 V, starting T_J = 25 °C, L = 28.2 mH, R_g = 25 $\Omega,\,I_{AS}$ = 11 A

c. 1.6 mm from case

d. $I_{SD} \leq I_D, \, di/dt = 60$ A/µs, starting $T_J = 25 \ ^\circ C$

THERMAL RESISTANCE RATINGS					
PARAMETER	SYMBOL	TYP.	MAX.	UNIT	
Maximum junction-to-ambient	R _{thJA}	-	40	°C/W	
Maximum junction-to-case (drain)	R _{thJC}	-	0.24	0/10	

S18-0173-Rev. A, 12-Feb-18

1 For technical questions, contact: <u>hvm@vishay.com</u> Document Number: 92068



COMPLIANT HALOGEN

FREE

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishav.com/doc?91000</u>

www.vishay.com

Vishay Siliconix

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static					•	•	•
Drain-source breakdown voltage	V _{DS}	$V_{GS} = 0 V, I_D = 250 \mu A$		600	-	-	V
V _{DS} temperature coefficient	$\Delta V_{DS}/T_{J}$	Reference to 25 °C, I _D = 1 mA		-	0.46	-	V/°C
Gate-source threshold voltage (N)	V _{GS(th)}	V _{DS} =	$V_{DS} = V_{GS}, I_D = 250 \ \mu A$		-	4.0	V
	1	$V_{GS} = \pm 20 V$		-	-	± 100	nA
Gate-source leakage	I _{GSS}	,	$V_{GS} = \pm 30 \text{ V}$	-	-	± 1	μA
Zava gata valtaga dvaja avvent	1	V _{DS} =	: 600 V, V _{GS} = 0 V	-	-	1	μA
Zero gate voltage drain current	IDSS	V _{DS} = 480 V	′, V _{GS} = 0 V, T _J = 125 °C	-	-	100	
Drain-source on-state resistance	R _{DS(on)}	$V_{GS} = 10 V$	I _D = 36.5 A	-	0.035	0.042	Ω
Forward transconductance ^a		V _{DS} =	40 V, I _D = 36.5 A	-	28	-	S
Dynamic		-			•	•	•
Input capacitance	C _{iss}		V _{GS} = 0 V, V _{DS} = 100 V,		6709	-	pF
Output capacitance	Coss	- ,			282	-	
Reverse transfer capacitance	C _{rss}	f = 1 MHz		-	7	-	
Effective output capacitance, energy related ^a	C _{o(er)}	- V _{DS} = 0 V to 480 V, V _{GS} = 0 V		-	181	-	
Effective output capacitance, time related ^b	C _{o(tr)}			-	888	-	
Total gate charge	Qg			-	171	342	
Gate-source charge	Q _{gs}	$V_{GS} = 10 V$	I _D = 36.5 A, V _{DS} = 480 V	-	34	-	nC
Gate-drain charge	Q _{gd}				57	-	1
Turn-on delay time	t _{d(on)}	V _{DD} = 480 V, I _D = 36.5 A,		-	51	102	- ns
Rise time	t _r			-	80	160	
Turn-off delay time	t _{d(off)}	V _{GS} =	$V_{GS} = 10 \text{ V}, \text{ R}_{g} = 10 \Omega$		244	488	
Fall time	t _f	1 1		-	104	208	
Gate input resistance	Rg	f = 1 MHz, open drain		0.3	0.7	1.5	Ω
Drain-Source Body Diode Characteristic	cs	-			•	•	•
Continuous source-drain diode current	١ _S	MOSFET symbol showing the integral reverse p - n junction diode		-	-	68	
Pulsed diode forward current	I _{SM}			-	-	206	A
Diode forward voltage	V _{SD}	T _J = 25 °C, I _S = 36.5 A, V _{GS} = 0 V		-	-	1.2	V
Reverse recovery time	t _{rr}	$T_{J} = 25 \text{ °C, } I_{F} = I_{S} = 36.5 \text{ A,}$ di/dt = 100 A/ μ s, V _R = 400 V		-	479	958	ns
Reverse recovery charge	Q _{rr}			-	11	22	μC
Reverse recovery current	I _{RRM}			-	42	-	A

Notes

a. $C_{oss(er)}$ is a fixed capacitance that gives the same energy as C_{oss} while V_{DS} is rising from 0 % to 80 % V_{DSS} b. $C_{oss(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 % to 80 % V_{DSS}





Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)





Fig. 1 - Typical Output Characteristics








Fig. 3 - Typical Transfer Characteristics




Fig. 4 - Normalized On-Resistance vs. Temperature




Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 6 - C_{oss} and E_{oss} vs. V_{DS}

S18-0173-Rev. A, 12-Feb-18

3

Document Number: 92068

For technical questions, contact: <u>hvm@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Siliconix




Fig. 7 - Typical Gate Charge vs. Gate-to-Source Voltage





Fig. 8 - Typical Source-Drain Diode Forward Voltage






Fig. 10 - Maximum Drain Current vs. Case Temperature




Fig. 11 - Temperature vs. Drain-to-Source Voltage


S18-0173-Rev. A, 12-Feb-18


4



SiHG73N60AEL

Vishay Siliconix








Fig. 13 - Switching Time Test Circuit




Fig. 14 - Switching Time Waveforms




Fig. 15 - Unclamped Inductive Test Circuit




Fig. 16 - Unclamped Inductive Waveforms




Fig. 17 - Basic Gate Charge Waveform




Fig. 18 - Gate Charge Test Circuit

S18-0173-Rev. A, 12-Feb-18

5


Document Number: 92068

For technical questions, contact: <u>hvm@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>





Peak Diode Recovery dV/dt Test Circuit



a. $V_{GS} = 5$ V for logic level devices

Fig. 19 - For N-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?92068.



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.