

## HUE Series

### Features

- 145°C, 2,000 hours assured
- Low ESR and High ripple current
- RoHS compliant
- AEC-Q200 compliant




Marking color: Dark Green

### Specifications

Items	Performance						
Category Temperature Range	-55°C ~ +145°C						
Capacitance Tolerance	± 20% (at 120 Hz, 20°C)						
Leakage Current (at 20°C)	I = 0.01CV or 3 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V						
Tanδ (at 120 Hz, 20°C)	See Standard Ratings						
Low Temperature Characteristics (at 100k Hz)	Impedance ratio shall not exceed the values given in the table below						
	Rated Voltage	25	35	50	63		
	Impedance ratio	Z (-25°C) / Z (+20°C)	1.5	1.5	1.5	1.5	
		Z (-55°C) / Z (+20°C)	2.0	2.0	2.0	2.0	
Endurance		Test Time	145°C		135°C		
			2,000 Hrs		4,000 Hrs		
		Capacitance Change	Within ± 30% of initial value				
		Tanδ	Less than 200% of specified value				
		ESR	Less than 200% of specified value				
		Leakage Current	Within specified value				
	* The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied with rated ripple current for: 2,000 hours at 145°C / 4,000 hours at 135°C.						
Shelf Life Test	* After storage for 1,000 hours at 145 ± 2°C with no voltage applied and then being stabilized at 20°C, capacitors shall meet the limits specified in Endurance. (With voltage treatment)						
Resistance to Soldering Heat (Please refer to page 15 for reflowsoldering conditions)		Capacitance Change	Within ± 10% of initial value				
		Tanδ	Within specified value				
		ESR	Within specified value				
		Leakage Current	Within specified value				
Ripple Current and Frequency Multipliers		Frequency (Hz)	120 ≤ f < 1k	1k ≤ f < 10k	10k ≤ f < 100k	100k ≤ f < 500k	
		Multiplier	0.1	0.3	0.6	1.0	

### Diagram of Dimensions




### Lead Spacing and Diameter

φD	L	A	B	C	W	P
8	10.0 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1
10	10.0 ± 0.5	10.3	10.3	11.0	0.7 ~ 1.3	4.7

The diagram is marking " ( ) " for reference dimension.

### Marking



### Standard Ratings

Rated Voltage (V)	Surge Voltage (V)	Capacitance (μF)	Size φD×L(mm)	Tanδ (120 Hz, 20°C)	LC (μA)	ESR (mΩ/at 100kHz, 20°C max.)	Rated R. C. (mA/rms at 100k Hz)	
							135°C	145°C
25V (1E)	28.8	220	8 × 10	0.14	55.0	27	1,600	700
		330	10 × 10	0.14	82.5	20	2,000	900
35V (1V)	40.3	150	8 × 10	0.12	52.5	27	1,600	700
		270	10 × 10	0.12	94.5	20	2,000	900
50V (1H)	57.5	68	8 × 10	0.10	34.0	30	1,250	600
		100	10 × 10	0.10	50.0	28	1,600	800
63V (1J)	72.5	33	8 × 10	0.08	20.8	40	1,100	600
		56	10 × 10		35.3	30	1,400	800
		82	10 × 10		51.7	30	1,400	800

### Part Numbering System

HUE Series	220μF	± 20%	25V	Carrier Tape	8 φ × 10L	Regional Tracking Purpose
<b>HUE</b>	<b>221</b>	<b>M</b>	<b>1E</b>	<b>TR</b>	<b>-</b>	<b>0810</b>
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case Size

Note: For more details, please refer to "Part Numbering System" on page 87.

All product specifications in the catalog are subject to change without notice. (Cat. 2025E3)