

VES Series

Features

- $4\phi \sim 6.3\phi$, 105°C, 1,000 hours assured
- Vertical chip type miniaturized for 4.5 / 5.3mm high capacitor
- Designed for surface mounting on high density PC board
- RoHS compliant
- AEC-Q200 compliant parts available (replace "S" Suffix with "KS")




Marking color: Black

Specifications

Items	Performance																													
Category Temperature Range	-55℃ ~ +105℃																													
Capacitance Tolerance	± 20% (at 120 Hz, 20℃)																													
Leakage Current (at 20℃)	I = 0.01CV or 3 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V																													
Tanδ (at 120 Hz, 20℃)	<table><tr><td>Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>Tanδ (max.)</td><td>0.30</td><td>0.26</td><td>0.22</td><td>0.16</td><td>0.13</td><td>0.12</td></tr></table>							Rated Voltage	6.3	10	16	25	35	50	Tanδ (max.)	0.30	0.26	0.22	0.16	0.13	0.12									
Rated Voltage	6.3	10	16	25	35	50																								
Tanδ (max.)	0.30	0.26	0.22	0.16	0.13	0.12																								
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td colspan="2">Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td rowspan="2">Impedance Ratio</td><td>Z(-25℃) / Z(+20℃)</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z(-55℃) / Z(+20℃)</td><td>8</td><td>5</td><td>4</td><td>3</td><td>3</td><td>3</td></tr></table>							Rated Voltage		6.3	10	16	25	35	50	Impedance Ratio	Z(-25℃) / Z(+20℃)	4	3	2	2	2	2	Z(-55℃) / Z(+20℃)	8	5	4	3	3	3
Rated Voltage		6.3	10	16	25	35	50																							
Impedance Ratio	Z(-25℃) / Z(+20℃)	4	3	2	2	2	2																							
	Z(-55℃) / Z(+20℃)	8	5	4	3	3	3																							
Endurance	<table><tr><td>Test Time</td><td>1,000 Hrs</td></tr><tr><td>Capacitance Change</td><td>Within ± 25% of initial value for 4.5 mmL Within ± 20% of initial value for 5.3 mmL</td></tr><tr><td>Tanδ</td><td>Less than 300% of specified value for 4.5 mmL Less than 200% of specified value for 5.3 mmL</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20℃ after the rated voltage applied for 1,000 hours at 105℃.							Test Time	1,000 Hrs	Capacitance Change	Within ± 25% of initial value for 4.5 mmL Within ± 20% of initial value for 5.3 mmL	Tanδ	Less than 300% of specified value for 4.5 mmL Less than 200% of specified value for 5.3 mmL	Leakage Current	Within specified value															
Test Time	1,000 Hrs																													
Capacitance Change	Within ± 25% of initial value for 4.5 mmL Within ± 20% of initial value for 5.3 mmL																													
Tanδ	Less than 300% of specified value for 4.5 mmL Less than 200% of specified value for 5.3 mmL																													
Leakage Current	Within specified value																													
Shelf Life Test	Test time: 1,000 hours; other items are the same as those for the Endurance.																													
Ripple Current and Frequency Multipliers	<table><tr><td>Frequency (Hz)</td><td>50</td><td>120</td><td>1k</td><td>10k up</td></tr><tr><td>Multiplier</td><td>0.7</td><td>1.0</td><td>1.3</td><td>1.4</td></tr></table>							Frequency (Hz)	50	120	1k	10k up	Multiplier	0.7	1.0	1.3	1.4													
Frequency (Hz)	50	120	1k	10k up																										
Multiplier	0.7	1.0	1.3	1.4																										

Diagram of Dimensions




Lead Spacing and Diameter

Unit: mm

φD	L ± 0.2	A	B	C	W	P
4	4.5 / 5.3	4.3	4.3	5.1	0.5 ~ 0.8	1.0
5	4.5 / 5.3	5.3	5.3	5.9	0.5 ~ 0.8	1.5
6.3	4.5 / 5.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0

The diagram is marking "()" for reference dimension.

Marking



Dimension and Permissible Ripple Current

Dimension: φD × L(mm)

Ripple Current: mA/rms at 120 Hz, 105°C

Rated Volt. (V _{DC})		6.3V (0J)		10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)	
Cap. (μF)	Contents	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA	φ D×L	mA
1	010											4×4.5 4×5.3	5.4 7
2.2	2R2											4×4.5 4×5.3	9.6 10
3.3	3R3											4×4.5 4×5.3	11 12
4.7	4R7							4×4.5 4×5.3	11 12	4×4.5 4×5.3	13 14	5×4.5 5×5.3	16 17
10	100			4×4.5 4×5.3	14 15	4×4.5 4×5.3	15 16	5×4.5 5×5.3	20 21	5×4.5 5×5.3	22 23	6.3×4.5 6.3×5.3	26 28
22	220	4×4.5 4×5.3	19 21	5×4.5 5×5.3	22 25	5×4.5 5×5.3	26 28	6.3×4.5 6.3×5.3	33 36	6.3×4.5 6.3×5.3	36 50	6.3×5.3	51
33	330	5×4.5 5×5.3	26 30	5×4.5 5×5.3	28 31	6.3×4.5 6.3×5.3	35 40	6.3×4.5 6.3×5.3	42 44				
47	470	5×4.5 5×5.3	32 36	6.3×4.5 6.3×5.3	40 43	6.3×4.5 6.3×5.3	44 47	6.3×4.5 6.3×5.3	57 60				
100	101	6.3×4.5 6.3×5.3	52 61	6.3×4.5 6.3×5.3	60 65	6.3×5.3	70						

Part Numbering System

VES Series	10μF	± 20%	16V	Carrier Tape		4 ϕ × 5.3L
<u>VES</u>	<u>100</u>	<u>M</u>	<u>1C</u>	<u>TR</u>	<u>-</u>	<u>0405</u>
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case Size

Note: For more details, please refer to "Part Numbering System - SMD Type" on page 106.

All product specifications in the catalog are subject to change without notice. (Cat. 2025E3)