

**SKYWORKS®**

DATA SHEET

SKY66399-11: 1900 to 2000 MHz Wide Instantaneous Bandwidth High-efficiency Power Amplifier

Applications

- FDD and TDD 2G/3G/4G LTE systems
- 3GPP bands 2, 25, 33, 36, and 37 small-cell base stations
- Driver amplifier for micro-base and macro-base stations
- Active antenna array and massive MIMO

Features

- High efficiency: PAE = 34% @ +28 dBm (CW)
- High linearity: +28 dBm with < -50 dBc ACLR with pre-distortion (40 MHz LTE, 8.5 dB PAR signal)
- High gain: 36.5 dB
- Excellent input and output return loss to 50 Ω systems
- Integrated active bias: performance compensated over temperature
- Integrated enable on/off function: PAEN = 1.7 to 2.5 V
- Single supply voltage: 5.0 V
- Pin-to-pin compatible PA family supporting all 3GPP bands
- Compact (16-pin, 5 x 5 x 1.3 mm) package
- (MSL3, 260 °C per JEDEC J-STD-020)
- For RoHS and other product compliance information, see the [Skyworks Certificate of Conformance](#).

Description

The SKY66399-11 is a high-efficiency fully input/output matched power amplifier (PA) with high gain and linearity. The compact PA is designed for FDD and TDD 2G/3G/4G LTE small-cell base stations operating from 1900 to 2000 MHz.

The active biasing circuitry is integrated to compensate PA performance over temperature, voltage, and process variation.

The SKY66399-11 is part of high-efficiency, pin-to-pin compatible PA family supporting all 3GPP bands.

Table 1 lists the pin-to-pin compatible parts in the PA family. A block diagram of the SKY66399-11 is shown in Figure 1. The device package and pinout are shown in Figure 2. Signal pin assignments and functional pin descriptions are described in Table 2.

Table 1. Pin-to-Pin Compatible PA Family

Part Number	Frequency (MHz)	3GPP Band
SKY66391-11	1800 to 1900	Bands 3 and 9
SKY66399-11	1900 to 2000	Bands 2, 25, 33, 36, and 37
SKY66394-11	2000 to 2300	Bands 1, 4, 10, 23, and 66
SKY66397-11	2300 to 2700	Bands 7, 38, and 41




Figure 1. Block Diagram




Figure 2. Pinout (Top View)

Table 2. Signal Descriptions¹

Pin	Name	Description	Pin	Name	Description
1	GND	Ground	9	RFOUT	RF output port
2	RFIN	RF input port	10	GND	Ground
3	GND	Ground	11	GND	Ground
4	GND	Ground	12	VCC3	Stage 3 collector voltage
5	VBIAS	Bias voltage	13	GND	Ground
6	PAEN	PA enable	14	VCC2	Stage 2 collector voltage
7	GND	Ground	15	GND	Ground
8	GND	Ground	16	VCC1	Stage 1 collector voltage

1. The center ground pad must have a low inductance and low thermal resistance connection to the application's printed circuit board ground plane.

Technical Description

The matching circuits are contained within the device. An on-chip active bias circuit is included within the device for both input and output stages, which provides excellent gain tracking over temperature and voltage variations.

The SKY66399-11 is internally matched for maximum output power and efficiency. The input and output stages are independently supplied using the VCC1, VCC2, and VCC3 supply lines (pins 16, 14, and 12, respectively). The DC control voltage that sets the bias is supplied by the VCBIAS signal (pin 5).

Electrical and Mechanical Specifications

The absolute maximum ratings of the SKY66399-11 are provided in Table 3. Recommended operating conditions are specified in Table 4, and electrical specifications are provided in Table 5.

Typical performance characteristics are shown in Figures 3 through 14.

Table 3. Absolute Maximum Ratings¹

Parameter	Symbol	Minimum	Maximum	Units
RF input power (CW)	PIN_MAX		+8	dBm
Supply voltage (VCC1, VCC2, VCC3, VBIAS)	VCC		5.5	V
PA enable	VEN		3	V
Operating temperature	Tc	-40	+100	°C
Storage temperature	TST	-55	+125	°C
Junction temperature	TJ		+150	°C
Power dissipation ($T_{CASE} = +85$ °C, POUT = +28 dBm, CW)	PD		1.55	W
Device thermal resistance ($T_{CASE} = +85$ °C, POUT = +28 dBm, CW)	θJC		22	°C/W
Electrostatic discharge: Charged Device Model (CDM) Human Body Model (HBM)	ESD		500 1000	V V

1. Exposure to maximum rating conditions for extended periods may reduce device reliability. Exceeding any of the limits listed here may result in permanent damage to the device.

ESD Handling: Industry-standard ESD handling precautions must be adhered to at all times to avoid damage to this device.

Table 4. Recommended Operating Conditions

Parameter	Symbol	Min	Typ	Max	Units
Supply voltage (VCC1, VCC2, VCC3, VBIAS)	Vcc1, Vcc2, Vcc3, VBIAS	4.75	5	5.25	V
PA enable: ON OFF	PA _{EN}	1.7	2.0 0	2.5 0.5	V V
PA enable current	IENABLE		1	12	μA
Operating frequency	f	1900		2000	MHz
Operating temperature	Tc	-40	+25	+85	°C

Table 5. Electrical Specifications¹

Parameter	Symbol	Test Condition	Min	Typ	Max	Units
Frequency	f		1930		1995	MHz
Small signal gain	S21	PIN = -30 dBm	33	34		dB
Gain @ +28 dBm	S21 @+28dBm	POUT = +28 dBm		36.5		dB
Input return loss	S11	PIN = -20 dBm		18		dB
Output return loss	S22	PIN = -20 dBm		18		dB
Reverse isolation ²	S12	PIN = -30 dBm		50		dB
ACLR @ +28 dBm	ACLR	POUT = +28 dBm (2x20 MHz LTE, 8.5 dB PAR signal)		-28	-26	dBc
Saturated output power	Psat	CW, PIN = +8 dBm		+36		dBm
Output power at 3 dB gain compression	P3dB	CW, reference to small signal gain (PIN = -30 dBm)	+34.5	+35.5		dBm
Second harmonic	2fo	CW, POUT = +28 dBm		-25	-21	dBc
Third harmonic	3fo	CW, POUT = +28 dBm		-40	-35	dBc
Power-added efficiency	PAE	CW, POUT = +28 dBm	30	34		%
Quiescent current	Iccq	No RF signal		90	120	mA

1. Performance is guaranteed only under the conditions listed in this table.

2. Not tested in production. Verified by design.

Typical Performance Characteristics

(VCC1 = VCC2 = VCC3 = VBIAS = 5 V, PAEN = 2.0 V, $f = 1962.5$ MHz, $TC = +25$ °C, Input/Output Load = 50 Ω , Unless Otherwise Noted)




Figure 3. PAE vs. POUT over Frequency (CW)




Figure 4. PAE vs. POUT over Temperature (CW)




Figure 5. ACLR vs. POUT Over Freq, LTE 2x20 MHz, PAR = 8.5 dB




Figure 6. ACLR vs. POUT Over Temp, LTE 2x20 MHz, PAR = 8.5 dB




Figure 7. Gain vs. POUT over Freq (CW)




Figure 8. Gain vs. POUT over Temp (CW)




Figure 9. Total Current vs. POUT over Freq (CW)




Figure 10. Total Current vs. POUT over Temp (CW)




Figure 11. 2fo vs POUT at Different Temp




Figure 12. 3fo vs POUT at Different Temp




Figure 13. Gain @ POUT = +28 dBm vs Freq Over Temp




Figure 14. Gain @ POUT = +28 dBm vs Freq over Voltage

Evaluation Board Description

An Evaluation Board is used to test the performance of the SKY66399-11. An application schematic is provided in Figure 15. Table 6 provides the Bill of Materials (BOM) list for Evaluation Board components.

An assembly drawing for the Evaluation Board is shown in Figure 16. Board layer details are shown in Figure 17. Layer detail physical characteristics are noted in Figure 18.

Circuit Design Considerations

The following design considerations are general in nature and must be followed regardless of final use or configuration:

- Paths to ground should be made as short as possible.
- The ground pad of the SKY66399-11 has special electrical and thermal grounding requirements. This pad is the main thermal conduit for heat dissipation. Because the circuit board acts as the heat sink, it must shunt as much heat as possible from the device.

Therefore, design the connection to the ground pad to dissipate the maximum wattage produced by the circuit board. Multiple vias to the grounding layer are required.

NOTE: A poor connection between the ground pad and ground increases junction temperature (T_J), which reduces the life of the device.

Evaluation Board Test Procedure


Turn-on Sequence

1. Connect 50 Ω test equipment or load to the input and output RF ports of the Evaluation Board.
2. Connect the DC ground.
3. Connect all VCCs and VBIAS lines to a +5 V supply. Connect PAEN to a 2.0 V supply.
4. Without applying RF, turn on the 5 V supply, then turn on the 2 V PAEN.
5. Apply RF signal data at –30 dBm and observe that the gain of the device is approximately 36 dB. Begin measurements.

Turn-off Sequence

1. Turn off the RF input to the device.
2. Turn off PAEN (set to 0 V).
3. Turn off all VCCs and VBIAS.

NOTE: It is important to adjust the VCC voltage sources so that +5 V is measured at the board. High collector currents drop the collector voltage significantly if long leads are used. Adjust the bias voltage to compensate.



8-Pin Header

203764-015

Figure 15. Application Schematic

Table 6. Evaluation Board Bill of Materials (BOM)

Component	Description	Size
C1	Resistor, 0 W, 0.063 W	0402
C3	Ceramic capacitor, 1 μF, ±10%, 16 V	0402
C4, C7	Ceramic capacitor, 3300 pF, X7R, ±10%, 50 V	0402
C6, C9, C11	Ceramic capacitor, 0.47 μF	0402
C8, C10, C12	Ceramic capacitor, 10 μF, X7R, ±10%, 16 V	1206
L1	DNI	




Figure 16. Evaluation Board Assembly Drawing




Figure 17. Board Layer Detail

50 Ohm	Cross Section	Name	Thickness (mm)	Materials
W = 0.500 mm	—	TMask	0.010	Solder Resist
—	—	L1	0.035	Cu, 1 oz.
—	■■■■■	Dielectric	0.250	R04350
—	—	L2	0.035	Cu, 1 oz.
—	■■■■■	Dielectric	0.350	FR4
—	—	L3	0.035	Cu, 1 oz.
—	■■■■■	Dielectric	0.250	FR4
—	—	L4	0.035	Cu, 1 oz.
—	—	BMask	0.010	Solder Resist

203764-018

Figure 18. Layer Detail Physical Characteristics

Application Circuit Notes

Center Ground. It is extremely important to sufficiently ground the bottom ground pad of the device for both thermal and stability reasons. Multiple small vias are acceptable and work well under the device if solder migration is an issue.

GND (pins 1, 3, 4, 7, 8, 10, 11, 13, and 15). Attach all ground pins to the RF ground plane with the largest diameter and lowest inductance via that the layout allows. Multiple small vias are acceptable and will work well under the device if solder migration is an issue.

VCBIAS (pin 5). The bias supply voltage for each stage, nominally set to +5 V.

RFOUT (pin 9). Amplifier RF output pin ($Z_0 = 50 \Omega$). The module includes an internal DC blocking capacitor. All impedance matching is provided internal to the module.

VCC1, VCC2, and VCC3 (pin 16, 15, and 12, respectively). Supply voltage for each stage collector bias is nominally set to 5 V. The evaluation board has inductors L1 and L2. These are place holders, and should be populated with 0Ω resistors. Bypass and decoupling capacitors C6 through C12 should be placed in the approximate location shown on the evaluation board assembly drawing, although exact placement is not critical.

RFIN (pin 2). Amplifier RF input pin ($Z_0 = 50 \Omega$). All impedance matching is provided internal to the module.

Package and Handling Information

Since the device package is sensitive to moisture absorption, it is baked and vacuum packed before shipping. Instructions on the shipping container label regarding exposure to moisture after the container seal is broken must be followed. Otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

The SKY66399-11 is rated to Moisture Sensitivity Level 3 (MSL3) at 260 °C. It can be used for lead or lead-free soldering. For additional information, refer to Skyworks Application Note, PCB Design and SMT Assembly/Rework Guidelines for MCM-L Packages, document number 101752.

Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. Production quantities of this product are shipped in a standard tape and reel format.





Figure 19. Typical Part Markings



Notes:

1. Thermal vias should be resin filled and capped in accordance with IPC-4761 type VII vias.
2. Recommended Cu thickness is 30 to 35 μ m.

203764-020

Figure 20. PCB Layout Footprint




Figure 21. Package Dimensions




Figure 22. Tape and Reel Dimensions

Ordering Information

Part Number	Description	Evaluation Board Part Number
SKY66399-11	1900 to 2000 MHz Wide Instantaneous Bandwidth High-efficiency Power Amplifier	SKY66399-11EK1

Copyright © 2015-2016, 2018-2019, 2024, 2025, Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc., and its subsidiaries ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks' Terms and Conditions of Sale.

THE INFORMATION IN THIS DOCUMENT AND THE MATERIALS AND PRODUCTS DESCRIBED THEREIN ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not designed, intended, authorized, or warranted for use or inclusion in life support or life endangering applications, devices, or systems where failure or inaccuracy might cause death or personal injury. Skyworks customers agree not to use or sell the Skyworks products for such applications, and further agree to, without limitation, fully defend, indemnify, and hold harmless Skyworks and its agents from and against any and all actions, suits, proceedings, costs, expenses, damages, and liabilities including attorneys' fees arising out of or in connection with such improper use or sale.

Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of Skyworks' published specifications or parameters. Customers are solely responsible for their products and applications using the Skyworks products.

"Skyworks" and the Skyworks Starburst logo are registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.