



Figure similar

transformer SITAS; phases: 3; Pn/Pn(S6)(kVA): 2.5 /11; Upri(V): Y500-440-380+/-20/D289- 254-220+/-11; Usec(V): Y 400 / D 230; Isec(A): 3.6-6.26; F(Hz): 50...60; vector group/shielding winding: IIIIII0 /0; temperature rise/insulation class: 40 /B; IP00; connection: screw/flat-type connection; mounting: screws; EN 61558-2-1, -2-2, -2-4 >UL/CSA-recognized< >control transformer< >isolation transformer<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	2 500
efficiency		0.94
connection method for transformers		IIIIII0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	11 000
relative short-circuit voltage	%	3.9
Inputs		
phase number of the inputs		3
input voltage		
• _1 rated value	V	520
• _2 rated value	V	500
• _3 rated value	V	480
• _4 rated value	V	460
• _5 rated value	V	440
• _6 rated value	V	420
• _7 rated value	V	400
• _8 rated value	V	380
• _9 rated value	V	360
• _10 rated value	V	300
• _11 rated value	V	289
• _12 rated value	V	277
• _13 rated value	V	266
• _14 rated value	V	254
• _15 rated value	V	240
• _16 rated value	V	230
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		3
output voltage		

• _1 rated value	V	400
• _2 rated value	V	230
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50

Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP00

Mechanical data		
type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals
fastening method		screws
construction form of the iron core		3UI 132/70
width	m	0.264
height	m	0.242
depth	m	0.242

Certificates/ approvals		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Confirmations](#)

Further information

- Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
- Information for data generation and storage
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
- Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
- Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AP2742-8CC40-0HA0>
- Cax online generator
<http://support.automation.siemens.com/WWW/CAXorder/default.aspx?lang=en&mlfb=4AP2742-8CC40-0HA0>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/4AP2742-8CC40-0HA0>
- Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AP2742-8CC40-0HA0&lang=en

last modified: 4/2/2025