



PROHEAT® 1200A VARITEMP® PROFESSIONAL HEAT GUN & KIT



Performance & Durability

- **ADJUSTABLE TEMP & AIRFLOW SETTINGS**– 6 temperature settings (ambient to 1200F) & 4 airflow settings (4-18 CFM)
- **LIGHTWEIGHT DESIGN**– Weighing only 1.9 lbs, Master Proheats are compact, lightweight and easy to use

- **RUGGED, IMPACT-RESISTANT HOUSING** – Durable construction built to withstand daily professional use.
- **AUTO COOLDOWN FEATURE**– Auto Cool down feature can be turned on or off at your convenience
- **PATENTED ELECTRONIC TEMPERATURE CONTROL SYSTEM** – Maintains constant temperature under varying airflows and voltage fluctuations for consistent results.
- **VERSATILE APPLICATIONS** — Bend plastics, cure adhesives, dry parts, shrink tubing and packaging, strip paint, and more.

Usability & Serviceability

- **QUICK-CHANGE HEATING ELEMENT** — Plug-in design makes replacement simple and fast.
- **BUILT-IN HANG LOOP** — Convenient hanging loop on top of heat gun.
- **OPTIMIZED FOR SERVICEABILITY** — Full selection of replacement part kits available for easy serviceability.
- **ERGONOMIC SOFT GRIP HANDLE** — Maximizes user comfort during operation.
- **Users should independently evaluate the suitability of the product for their application.**

In-The-Box

Kit Includes:

- (1) Proheat PH-1200A Varitemp® Professional Heat Gun
- (1) 35016 Spreader Attachment
- (1) 35017 Shrink Tubing Attachment
- (1) 35292 Specialty Connector
- (1) 35293 Reducer Attachment
- (1) 5294 Pinpoint Reducer Attachment
- (1) 35679 Storage and carrying case

ABOUT THE PROHEAT 1200A VARITEMP HEAT GUN

- **VERSATILE & PRECISE** – Easily pre-select and maintain any temperature from ambient to 1200°F for a wide range of applications.
- **LIGHTWEIGHT & ERGONOMIC** – Compact design minimizes operator fatigue during long projects and continuous use.
- **BUILT FOR CONTROL** – Six temperature settings and a convenient top-mounted hanging loop make it practical in any workspace.
- **RELIABLE PERFORMANCE** – Ideal for desoldering heat-sensitive materials, shrinking tubing, terminating specialty connectors, and more.
- **YOUR HEAT TOOL SOLUTION** – Wherever fast, portable heat is needed, the Proheat 1200A Varitemp delivers professional-grade results.

PROHEAT 1200A VARITEMP KIT

- **COMPLETE ACCESSORY SET** – Comes equipped with a spreader attachment, shrink tubing attachment, specialty connector, and reducers.
- **DURABLE STORAGE CASE** – Rugged molded case with organized slots for attachments keeps tools protected and ready for transport.
- **ADAPTABLE FOR ANY JOB** – Expand your capabilities with optional nozzles and accessories for new materials and processes.
- **CONTACT MASTER APPLIANCE** – Have questions? Call us at [262-633-7791](tel:262-633-7791) to speak with one of our helpful customer service representatives.

Available Models

MODEL NO.	DESCRIPTION
PH-1200A	Proheat Varitemp Professional Heat Gun, Ambient to 1200°F (649°C), Airflow 4-18 CFM, 120V
PH-1200-00-K	Proheat Varitemp Professional Heat Gun Kit includes PH-1200A Varitemp Heat Gun, 3" spreader attachment, specialty connector, 9/16" reducer, and 5/16" reducer packed in a rugged storage/carrying case
PH-1200A-SS	Proheat Varitemp Professional Heat Shrink System, 120V (Comes with bench stand 35678 and 1200A Varitemp Heat Gun)

35669	Proheat Dust Filter
35677	Proheat Nozzle Guard

Adjustable Temp: Ambient to 1200° F
Ambient to 649° C

Nozzle Opening: 1.3" Dia. O.D.

Adjustable Air Volume: 4-18 CFM

Nozzle Opening: 1.3" Dia. O.D.

Hertz: 50/60 Amps: 13A Watts: 1560W Max Cordset: 6 ft., 2-Prong Double Insulated

Motor: Permanent Magnet

Net Weight - Single Unit: 1.9 lbs.

Dimensions: 9.25" L x 3.43" W x 8.2" H

Shipping Weight - Single Unit: 3 lbs.,
Kit: 10 lbs.