

# HC-A3-STQ1,5-KML-G-PA - Connector



1641604

<https://www.phoenixcontact.com/in/products/1641604>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON QUICKON coupling housing A3, for single locking latch, 3-pos., with PE connection, plug, QUICKON connection, straight cable outlet

## Commercial data

Item number	1641604
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF7
Product key	AF7AJX
GTIN	4017918890001
Weight per piece (including packing)	34.46 g
Weight per piece (excluding packing)	34.46 g
Customs tariff number	85366990
Country of origin	PL

# HC-A3-STQ1,5-KML-G-PA - Connector



1641604

<https://www.phoenixcontact.com/in/products/1641604>

## Technical data

### Product properties

Product type	Connector set
Housing type	Complete housing
Series	HC-A
Application	Standard
Type	D7
Number of positions	3
Connection profile	3+PE
Contact numbering	1 - 3
No. of cable outlets	1
Shielded	no
Cable outlet	straight

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage (II/2)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (III/3)	4 kV
Rated current	10 A
rated voltage (II/2)	630 V
rated voltage (III/2)	320 V
Rated voltage (III/3)	230 V (Conductor-PE)
	400 V (Conductor-Conductor)

### Connection data

Connection method	IDC connection
Connection technology	IDC connection
Conductor cross section	0.75 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	0.75 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Connection cross section AWG	18 ... 16
Tightening torque	3 Nm

### Dimensions


# HC-A3-STQ1,5-KML-G-PA - Connector



1641604

<https://www.phoenixcontact.com/in/products/1641604>

Dimensional drawing



Width	34 mm
Height	62.8 mm
Length	26.5 mm

## Material specifications

Material Housing	PA
Flammability rating according to UL 94	V0
Material wire insulation	PVC / PE
Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PA

## Cable/line

Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 Cl.2-5, min. wire diameter 0.2 mm
External cable diameter	6 mm ... 12 mm
Wire diameter including insulation	1.8 mm ... 3 mm

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	>= 500
-----------------------------	--------

## Environmental and real-life conditions

### Ambient conditions


Degree of protection	IP65
Ambient temperature (operation)	-25 °C ... 80 °C
Temperature when conductor connected	-5 °C ... 50 °C (specifications of the cable manufacturer must also be observed)
Ambient temperature (storage/transport)	-40 °C ... 70 °C

## Mounting

Assembly note	This product is only intended for use outdoors.  If the conductor is reconnected, it must be cut off above the last contact point. QUICKON components may only be operated when under no load.
---------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

## Drawings


Dimensional drawing



Dimensional drawing

1641604

<https://www.phoenixcontact.com/in/products/1641604>



Derating diagram

# HC-A3-STQ1,5-KML-G-PA - Connector



1641604

<https://www.phoenixcontact.com/in/products/1641604>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1641604>

### DNV

Approval ID: TAE000037S



### cUL Recognized

Approval ID: E118976

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	600 V	10 A	18 - 16	-



### UL Recognized

Approval ID: E118976

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	600 V	10 A	18 - 16	-



### EAC

Approval ID: RU C-DE.AI30.B.01102

# HC-A3-STQ1,5-KML-G-PA - Connector



1641604

<https://www.phoenixcontact.com/in/products/1641604>

## Classifications

### ECLASS

ECLASS-13.0	27440113
ECLASS-15.0	27440113

### ETIM

ETIM 9.0	EC002636
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-A3-STQ1,5-KML-G-PA - Connector



1641604

<https://www.phoenixcontact.com/in/products/1641604>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	0.543 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)