


PS1023 PANEL MOUNT PUSH BUTTON SWITCHES



MECHANICAL SPECIFICATIONS

Mechanical Life: 6,000 Cycles
Electrical Life: 6,000 cycles

ELECTRICAL SPECIFICATIONS

Contact Rating: 3A@125VAC
1.5A@250VAC


Contact Resistance (Initial Max): 50m Ohms

Insulation Resistance: 500VDC 100M Ohms Min.

Dielectric Strength: 1000VAC 1 minute

ENVIRONMENTAL SPECIFICATIONS

Operating/Storage Temp: -20°C to 65°C



How To Order

SERIES

PS1023

CIRCUITA=OFF-(ON)
B=OFF-ON

()=Momentary

CAP COLORBLK=BLACK
RED=RED