

Ledex® Low Profile Size 5EC — Push or Pull

Medium Stroke, Conical Face
Part Number: 129415-0XX

All catalog products manufactured after
April 1, 2006 are RoHS Compliant

Performance

Maximum Duty Cycle	100%	50%	25%	10%
Maximum ON Time (sec) when pulsed continuously ¹	∞	100	36	10
Maximum ON Time (sec) for single pulse ²	∞	160	44	13
Watts (@ 20°C)	21	42	84	210
Ampere Turns (@ 20°C)	1015	1440	2030	3210

Coil Data

awg (0XX) ³	Resistance (@20°C)	# Turns ⁴	VDC (Nom)	VDC (Nom)	VDC (Nom)	VDC (Nom)
23	2.70	384	7.2	10.1	14.3	23.0
24	4.30	486	9.0	12.7	18.0	28.0
25	6.66	590	11.5	16.2	23.0	36.0
26	10.30	737	14.0	20.0	28.0	44.0
27	15.70	900	17.7	25.0	35.0	56.0
28	26.60	1190	23.0	32.0	45.0	72.0
29	38.00	1380	28.0	40.0	56.0	89.0
30	62.10	1768	36.0	51.0	71.0	113.0
31	96.10	2166	45.0	64.0	90.0	143.0
32	157.00	2816	57.0	80.0	113.0	179.0
33	241.00	3432	71.0	101.0	143.0	226.0

¹ Continuously pulsed at stated watts and duty cycle

² Single pulse at stated watts (with coil at ambient room temperature 20°C)

³ Other coil awg sizes available — please consult factory

⁴ Reference number of turns

Specifications


Dielectric Strength	23 awg, 1000 VRMS ; 24-33 awg, 1200 VRMS
Recommended Minimum Heat Sink	Maximum watts dissipated by solenoid are based on an unrestricted flow of air at 20°C, with solenoid mounted on the equivalent of an aluminum plate measuring 7 1/2" square by 1/8" thick
Coil Resistance	23-33 awg, ±5%
Weight	11.5 oz (326.0 gms)
Holding Force	27.0 lb (120.1 N) @ 105°C
Dimensions	Ø1.875" x 1.035" L (See page G17)

How to Order

Add the coil awg number (0XX) to the part number (for example: to order a 25% duty cycle unit rated at 35 VDC, specify 129415-027).


Please see www.ledex.com (click on Stock Products tab) for our list of stock products available through our North American distributors.

Size 5EC— Typical Force @ 20°C



Force values for reference only.

Size 5EC— Typical Speed @ No Load, 20°C




All specifications subject to change without notice.

Ledex® Low Profile Dimensions


Inches (mm)

All solenoids are illustrated in energized state


Size 4EF/4EC



Size 5SF



Size 5EC



LINEAR Low Profile

All specifications subject to change without notice.