

Jabil PA 4500 Filament Technical Data Sheet

Product Description

PA 4500 Filament is a low warp, neat nylon copolymer that has good lay flat/low warp properties, excellent appearance, strength in both XY and XZ directions, toughness, and can be printed at lower temps (240-260° C).

Applications for this material include component production of less than 20,000 per year with complex geometries that require good wear properties and appearance are required but also strength and durability, such as slides, screen printing pallets, automation sleds, adaptors for fluid and materials handling, end of arm tooling (EOAT), masking covers, die cast models and patterns, clips, covers, housings, and gears.

Advantages

Along with easier printability, PA 4500 filament also delivers better appearance, over 100% elongation at break and better overall strength compared to other commercial PA's and products like PETg and PLA.

Storage and Use

PA 4500 is highly hygroscopic, meaning it will quickly absorb and retain moisture from the atmosphere, affecting visual quality and mechanical properties. For best results, print and store filament in a dry environment. If necessary, dry filament in an oven at up to 75 °C (165 °F) for 6 - 12 hours. <u>Download Jabil's optimized print profile by clicking here.</u>

Properties

Mechanical Properties - Dry as Printed ¹			
	Test Condition	Typical Value	Method
Tensile Modulus (MPa)		1930	
Tensile Elongation at Break (%)	XY coupons, Ambient	>100	ASTM D638, Type I
Ultimate Tensile Strength (MPa)		56.0	
Flexural Modulus (MPa)		1440	
Flexural Strength (MPa)	XY coupons, Ambient	56.9	ASTM D790
Flexural Strain (%)		>5	
Izod Impact, notched (J/m)	XY coupons, Ambient	61.5	ASTM D256
Izod impact, un-notched (J/m)	XY coupons, Ambient	830	A3114 D230

^{1.} Testing conducted on bars printed at 260 °C and tested at <0.20 wt% moisture. Typical values are for reference only.



Jabil PA 4500 Filament Technical Data Sheet

Mechanical Properties - Moisture Conditioned ¹			
	Test Condition	Typical Value	Method
Tensile Modulus (MPa)		1050	
Tensile Yield Strength (Mpa)	XY coupons, Ambient	30.8	ASTM D638, Type I
Tensile Elongation at Break (%)		>500	
Ultimate Tensile Strength (MPa)		41.6	
Flexural Modulus (MPa)		497	
Flexural Strength (MPa)	XY coupons, Ambient	20.4	ASTM D790
Flexural Strain (%)		>5	
Izod Impact, notched (J/m)	XY coupons, Ambient	282	ASTM D256
Izod impact, un-notched (J/m)	XY coupons, Ambient	1714	ASTITI D230

^{1.} Testing conducted on bars printed at 260 $^{\circ}$ C and conditioned for 14 days at 23 $^{\circ}$ C and 50 $^{\circ}$ RH. Typical values are for reference only.

Thermal Properties			
	Test Condition	Typical Value	Method
Heat Deflection Temperature (°C)	0.455 Mpa	62	DMA
Melt Temperature, Peak (°C)	20°C/min ramp	190	DSC

Other Physical Properties			
	Test Condition	Typical Value	Method
Density (g/cm3)	Ambient	1.10	ASTM D792

Dimensional Properties			
	Test Condition	Typical Value	Method
Diameter: Mean, Indiv. Axis (mm)	In-line, 100% inspection	1.75±0.05 2.85±0.05	Laser Micrometer



Jabil PA 4500 Filament Technical Data Sheet

Disclaimer: The information in this technical data sheet, including material properties, are obtained from testing representative samples under carefully controlled conditions and are provided for reference only. Material properties may be impacted by storage, handling, processing equipment/parameters, and product design, among other factors. The information is not a substitute for user testing to determine fitness for any specific use and the user is responsible for ensuring safe and lawful use of the product.

No express or implied warranties are provided and the implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. No representations are made, and no liability is assumed arising from or relating to the product.

Copyright/Trademark: © 2019 Jabil Inc. All rights reserved. JABIL® and the JABIL logo are registered trademarks of Jabil Inc.

United States: en 19-MT60-00048 Rev A Page 3 of 3