



Proheat® 1100A Quick Touch™ 3-Temperature Professional Heat Gun & Kit



PERFORMANCE & DURABILITY

- **THREE HEAT SETTINGS** – Choose from Ambient, 600°F (315°C), or 1200°F (649°C) for precise temperature control across multiple applications.
- **TWO AIRFLOW OPTIONS** – Adjustable 9 CFM and 18 CFM airflows provide flexibility for light or heavy-duty tasks.
- **RELIABLE PERFORMANCE** – Compact, lightweight design delivers professional-grade results in a portable tool.
- **TRIGGER SWITCH SYSTEM** – Features Master's new switch, safety, and lock configuration for safe and controlled operation.
- **DURABLE CONSTRUCTION** – Engineered for long-term reliability in industrial and commercial environments.
- **ENGINEERED IN THE USA** – Designed and built with precision at Master Appliance headquarters in Racine, Wisconsin.

USABILITY & SERVICEABILITY

- **INDUSTRY-LEADING FIELD REPAIRABILITY** – Built for easy maintenance and extended tool life.
- **PLUG-IN HEATING ELEMENT** – Quick, easy-to-replace element minimizes downtime and keeps you productive.
- **REPLACEABLE CORDSET** – Simple cord replacement saves service time and cost.
- **EASY CONNECT NOZZLE COVERS** – Swap attachments quickly to match the job at hand.
- **COMPLETE KIT INCLUDED** – Comes with Proheat Heat Gun, attachments #35016, #35017, #35679, and a molded storage carrying case.
- **ACCESSORY OPTIONS** – Additional attachments available separately for expanded functionality.
- **VERSATILE APPLICATIONS** – Perfect for activating adhesives, bending plastics, drying filler, heat-shrinking tubing and connectors, packaging, stretching vinyls, stripping paint, and more.

In-The-Box

- Kit Includes:

- (1) Proheat 1100A Professional Heat Gun
- (1) 35016 Spreader attachment
- (1) 35017 Shrink Tubing attachment
- (1) 35679 storage carrying case

ABOUT THE PROHEAT PH-1100A HEAT GUN

- **VERSATILE PROFESSIONAL TOOL** – Compact, ergonomic, and easy to use — the PH-1100A quickly becomes your go-to heat gun for countless applications.
- **3 TEMPERATURE SETTINGS** – Choose from no heat (ambient), 600°F, or 1200°F to tackle a wide range of projects with precision.
- **READY-TO-WORK KIT** – The PH-1100A-00-K includes a heat spreader attachment, shrink tubing attachment, and a durable plastic storage case with molded slots.
- **EXPAND YOUR CAPABILITIES** – Ideal for industrial, commercial, and hobby applications that require controlled, flameless heat.

APPLICATIONS & ACCESSORIES

- **MULTI-PURPOSE PERFORMANCE** – Commonly used to activate adhesives, bend plastics, dry filler material, shrink tubing, package, stretch vinyl, and strip paint.
- **ADDITIONAL USES** – Perfect for shrink wrapping, desoldering, drying paint, welding plastics, joining tarps, thawing frozen pipes, tinting windows, removing dents, repairing leather, and more.
- **LIGHTWEIGHT DESIGN** – Comfortable to hold at any angle for long periods, reducing operator fatigue without sacrificing performance.
- **OPTIONAL ATTACHMENTS** – Expand versatility with available accessories such as butt welding heat discs, reducers, reflectors, nozzle guards, and welding slits.
- **CONTACT MASTER APPLIANCE** – Have questions? Call us at [262-633-7791](tel:262-633-7791) for more information about the PH-1100A 3-Temperature Heat Gun Kit.

Available Models

MODEL NO.	DESCRIPTION
PH-1100A	Proheat A-Series Quick-Touch 3-Temp Professional Heat Gun, No Heat (Ambient) 600°F (315°C) & 1200°F (649°C), 120V, 50/60 Hz, 13A, 1560W
PH-1100A-00-K	Proheat Quick-Touch 3-Temp Professional Heat Gun Kit includes PH-1100A Heat Gun, spreader and shrink tubing attachments packed in a rugged storage/carrying case
35669	Proheat Dust Filter
35677	Proheat Nozzle Guard

Adjustable Temp: Ambient to 600° F to 1200° F Shipping Weight - Single Unit: 3 lbs.,
(Ambient to 315°C to 649° C) Kit: 10 lbs.

Avg. Air Volume: 9 & 18 CFM

Dimensions: 9.25" L x 3.43" W x 8.2" H

Hertz: 50/60 Amps: 13A Watts: 1560W

Cordset: 6 ft., 2-Prong Double Insulated

Motor: Permanent Magnet

Net Weight - Single Unit: 1.9 lbs.

Nozzle Opening: 1.3" Dia.