



**Pan-Lug™ Aluminum Mechanical Lug**

**Pan-Lug™ LAMA2/0-14-L Al Mech,2/0, Tin Plt, 1hole, 1/4" Stud,PK50**

**Part Number: LAMA2/0-14-L**

**Secure and reliable aluminum connections for various wire sizes with our mechanical lug, designed to accommodate a single wire, ideal for use in electrical applications.**



## Specifications

<b>Product Type</b>	<b>Mechanical Lug</b>
<b>Base Material</b>	<b>Aluminum</b>
<b>Number of Stud Holes</b>	<b>1</b>
<b>Barrel Type</b>	<b>Single Barrel</b>
<b>Tongue Type</b>	<b>Straight Tongue</b>
<b>Tongue Angle</b>	<b>Straight</b>
<b>Finish/Coating</b>	<b>Tin-Plated</b>
<b>Stud Hole Size (In.)</b>	<b>1/4</b>
<b>Stud Hole Size (mm)</b>	<b>6.4</b>
<b>Screw Type</b>	<b>Hex</b>
<b>Aluminum Conductor Size</b>	<b>14-2/0 AWG</b>
<b>Copper Conductor Size</b>	<b>14-2/0 AWG</b>
<b>Tongue Length (In.)</b>	<b>0.83</b>
<b>Tongue Length (mm)</b>	<b>21</b>
<b>Tongue Width (In.)</b>	<b>0.63</b>
<b>Tongue Width (mm)</b>	<b>16</b>
<b>Tongue Thickness (In.)</b>	<b>0.19</b>

<b>Tongue Thickness (mm)</b>	<b>4.8</b>
<b>Overall Length (In.)</b>	<b>1.46</b>
<b>Overall Length (mm)</b>	<b>37</b>
<b>Overall Width (In.)</b>	<b>0.63</b>
<b>Overall Width (mm)</b>	<b>16</b>
<b>Overall Height (In.)</b>	<b>0.77</b>
<b>Overall Height (mm)</b>	<b>19.5</b>
<b>Standards Met</b>	<b>cULus Listed for use up to 600V &amp; Temperature Rated to 90°C</b>
<b>CSA Temperature Rating (°C)</b>	<b>90</b>
<b>UL Temperature Rating (°C)</b>	<b>90</b>
<b>Maximum Voltage (V)</b>	<b>600</b>
<b>Wire Strip Length (In.)</b>	<b>5/8</b>
<b>Wire Strip Length (mm)</b>	<b>15.7</b>
<b>Note</b>	<b>Stranded Aluminum or Copper Code Conductor</b>
<b>Sub Brand</b>	<b>Pan-Lug™</b>
<b>Application</b>	<b>Stranded Aluminum or Copper Code Conductor</b>

**Packaging Detail**

<b>UPC</b>	<b>61305687847</b>
<b>Std. Pkg. Qty.</b>	<b>50</b>
<b>Std. Pkg. Volume (cf)</b>	<b>0.0017</b>
<b>Std. Ctn. Qty.</b>	<b>1000</b>
<b>Std. Ctn. Volume (cf)</b>	<b>0.0347</b>