


THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.



NOTES:

TAPE AND REEL SPECIFICATIONS:

1. TAPE:

MAT'L - ALL CONDUCTIVE POLYSTYRENE CARRIER

ANSI/EIA-481 STANDARD

1.26 [32.0] WIDE; .945 [24.0] PITCH

2. REEL:


13.0 [330] DIA. 125 PIECES OF

PART NO. 933 PER REEL.

11.17.25	UPDATED POCKETS STYLE.	A
DATE	DESCRIPTION	REV.

KEYSTONE ELECTRONICS CORP.			
www.keyelco.com • NEW HYDE PARK NY 11040 • Tel (516)328-7500			
PART NAME			
USB SMT SOCKET ON TAPE			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		NT	7.26.11
		APP'D	SCALE
		RH	1X
TOLERANCES	INCH [MM]	CODE	DWG NO.
DECIMAL	±.005 [±0.13]	C	933TR
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED			

DATE	DESCRIPTION	REV.



Notes:

Front Shell: Brass, Nickel Plate.
Rear Shell: Steel, Nickel Plate.

Insulator: Matl: Thermoplastic
UL 94V-0

Contacts: Matl: Phosphor Bronze
Finish: Gold Plate over
Nickel Plate over
Contact Area.
Tin Plate over
Nickel Plate
on Solder Tail.

Electrical Specifications
Rated Voltage:
30V AC (rms)

Contact Current Rating:
1A Max.




Contact Resistance:
30 milliohms Max.

Dielectric Withstanding:
500V AC

Operating Temperature:
-20°C to 85°C

PACKAGING DESCRIPTION:

Packed in 500 Pieces per lot.
50 Pieces per Tray, 10 Trays per lot.



KEYSTONE ELECTRONICS CORP.			
www.keyelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500			
PART NAME			
USB B-TYPE HORIZONTAL SMT SOCKET			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		BOONE	5.30.06
TOLERANCES		APPD	SCALE
INCH [MM]		RH	3X
DECIMAL $\pm .010$ [± 0.25]			
ANGULAR $\pm 1^\circ$			
UNLESS OTHERWISE SPECIFIED		CODE	DWG NO.
		C	933