

SULLINS ELECTRONICS CORP


SAN MARCOS, CA 760-744-0125 FAX 760-744-6081



A = 0.600+-.020 [15.24+-0.51] B = 0.500+-.008 [12.70+-0.20] C = 0.100+-.003 [2.54+-0.08] D = 0.200+-.005 [5.08+-0.13] E = 0.050+-.005 [1.27+-0.13] F = 0.100+-.005 [2.54+-0.13] G = 0.230+-.015 [5.84+-0.38] H = 0.100+-.005 [2.54+-0.13] I = 0.620+-.015 [15.75+-0.38]



.025[0.64] SQUARE POSTS FIT .040[1.02] MINIMUM DIAMETER HOLE



- 1.0 SPECIFICATIONS FOR A DUAL 6/12 POSITION HEADER
- 2.0 INSULATOR MATERIAL: BLACK THERMOPLASTIC POLYESTER
- 3.0 CONTACT MATERIAL: CA510, PHOSPHOR BRONZE GRADE A
- 4.0 PLATING: .000100" TIN OVERALL, .000050" NICKEL UNDERPLATE
- 5.0 TEMPERATURE: TO 125 DEGREES C CONTINOUS
- 6.0 UL FLAMMABILITY RATING: 94V-0
- 7.0 VOLTAGE RATING: 600 VDC MINIMUM AT SEA LEVEL
- 8.0 CURRENT RATING: 3 AMPERES
- 9.0 INSULATION RESISTANCE: 5,000 MEGA OHMS
- 10.0 SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
- 11.0 NOT DRAWN TO SCALE

SULLINS PART NUMBER: PTC06DAFN

Print PDF

DATE: 1-29-03