SHARP PQ033ES3MXP PQ050ES3MXP

Under developmentNew product

Low Power-Loss Voltage Regulator


Low Output Current, Compact Surface Mount Type Low Power-Loss Voltage Regulators

Features

- (1) Compact package : TO-92 type
 - (Size(mold part) $5.2 \times 5.5 \times 4.2$ mm)
- (2) Small current output : 300 mA(MAX.)
- (3) Low power-loss :
- Dropout voltage : MAX. 0.7 V at Io=300 mA
- (4) Built-in overcurrent, overheat protection functions
- (5) Taped package

Applications

- (1) TV
- (2) VCR
- (3) Air conditioner
- (4) DVD player
- (5) Audio equipment



Absolute Maximum Ratings

		(Ta=25°C)	
Symbol	Ratings	Unit	
Vin	9	V	
Io	300	mA	
Pd	520	mW	*1 All are open except GND and applicable terminals.
Tj	150	°C	*2 At mounted condition
Topr	-30 to +80	°C	*3 Overheat protection may operate
Tstg	-55 to +150	°C	at 125≤Tj́≤150°C.
Tsol	260(For 10s)	°C	
	Vin Io Pd Tj Topr Tstg	Vin 9 Io 300 Pd 520 Tj 150 Topr -30 to +80 Tstg -55 to +150	Symbol Ratings Unit Vin 9 V Io 300 mA Pd 520 mW Tj 150 °C Topr -30 to +80 °C Tstg -55 to +150 °C

⁽Notice)

•In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

10

•Specifications are subject to change without notice for improvement.

•Data for Sharp's optoelectronic/power devices is provided on internet. (Address http://sharp-world.com/ecg/)

⁽Internet)

SHARP PQ033ES3MXP Q050ES3MXP

Low Power-Loss Voltage Regulator

Electrical Characteristics

(Unless otherwise specified, Vin=Vo(TYP.)+1.0V, Io=30mA.Ta=25								
Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit		
Output voltage	Vo	-	Refer to the table below.		V			
Load regulation	RegL	Io=5 mA to 300 mA	-	35	160	mV		
		Vin=Vo(TYP.)+1V to						
Line regulation	RegI	Vo(TYP.)+6V(MAX. 9V)	-	3.0	20	mV		
Temperature coefficient of output voltage	TcVo	Io=10mA, Tj=-25 to +75°C	-	0.05	-	mV/°C		
Ripple rejection	RR	-	-	55	-	dB		
Dropout voltage	Vi-o	Io=300 mA, Vin=*4	-	0.3	0.7	V		
Quiescent current	Iq	Io=0mA	-	190	650	μΑ		

*4 Dropout voltage when output voltage lowers 0.1V from the voltage at Vin=Vo+1V.

Output Voltage Line-up

(Vin=Vo(TYP.)+1.0V, Io=30mA.Ta=25°C)

P	arameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Output voltage	PQ033ES3MXP	Vo	_	3.234	3.3	3.366	v
	PQ050ES3MXP			4.900	5.0	5.100	

D5-020903

NOTICE

- The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
 - (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - --- Personal computers
 - --- Office automation equipment
 - --- Telecommunication equipment [terminal]
 - --- Test and measurement equipment
 - --- Industrial control
 - --- Audio visual equipment
 - --- Consumer electronics
 - (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection with equipment that requires higher reliability such as:
 - --- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
 - --- Traffic signals
 - --- Gas leakage sensor breakers
 - --- Alarm equipment
 - --- Various safety devices, etc.

(iii)SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:

- --- Space applications
- --- Telecommunication equipment [trunk lines]
- --- Nuclear power control equipment
- --- Medical and other life support equipment (e.g., scuba).
- If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this publication.