


SIGN	DATE	DESCRIPTION	APPROVER



Ratings

	B	C	D		
Use Group	B	C	D		
Rated Voltage	300 V	-	300 V	160 V	
Rated Current	8 A	-	8 A	9 A	
Rated Wire Size				min	max
solid	-	-	-	-	-
flexible	-	-	-	-	-
Screw Size	-	-	-	-	-

Insulating Material

Material	PA 6.6
Flammability Class	UL 94 V-0

Materials

Contact Pin	Copper Alloy
Temperature Range	-30 °C - 105 °C

RoHS Compliant

PART NUMBER:
EDSTLZ1550/X

No. of Poles →
2: 2 Poles
3: 3 Poles
:
20 20 Poles

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

OST ON-SHORE TECHNOLOGY, INC.					
TITLE: EDSTLZ1550 3.81mm series header					
PART. NO.: EDSTLZ1550/X			DWG NAME: EDSTLZ1550.DWG		
APPROVED BY	CHECKED BY	DESIGNED BY	DRAWN BY	CUSTOM NO.:	
	H.Walters		S.Vogel		
				UNITS: mm	
				SCALE: none	
				REVISION: A	