GP1A50HR/GP1A51HR GP1A52HR/GP1A53HR

OPICPhotointerrupter

(Unit: mm)

■ Features

1. High sensing accuracy (Slit width: 0.5mm)

2. LSTTL and TTL compatible output

3. Both-sides mounting type: **GP1A50HR** (Gap: 3mm)

Either-side mounting type: **GP1A51HR** (Gap: 3mm)

PWB mounting type: **GP1A52HR** (Gap: 3mm)

GP1A53HR (Gap: 5mm)

■ Applications


1. OA equipment, such as printers, facsimiles, etc.


2. VCRs


*"OPIC" (Optical IC) is a trademark of the SHARP Corporation.


An OPIC consists of a light-detecting element and signalprocessing circuit integrated onto a single chip.

■ Outline Dimensions









■ Absolute Maximum Ratings

(Ta= 25°C)

	Parameter	Symbol	Rating	Unit	
Input	Forward current	I_F	50	mA	
	*1Peak forward current	I _{FM}	1	A	
Input	Reverse voltage	V _R	6	V	
	Power dissipation	P	75 mW - 0.5 to + 17 V	mW	
	Supply voltage	V _{CC}	- 0.5 to + 17	V	
Output	Output current	Io	50	mA	
	Power dissipation	Po	Io 50 mA Po 250 mW	mW	
Operating	Operating temperature		- 25 to + 85	°C	
Storage ter	mperature	T_{stg}	- 40 to + 100	°C	
*2Soldering	temperature	T _{sol}	260	°C	

^{*1} Pulse width<=100 $\mu\,s,$ Duty ratio= 0.01

■ Electro-optical Characteristics

 $(Ta = 25^{\circ}C)$

Parameter		Symbol	Conditions	MIN.	TYP.	MAX.	Unit		
Input	E11	would violate as	GP1A50HR/GP1A51HR GP1A52HR	VF	I _F = 5mA	-	1.1	1.4	V
	Forward voltage		GP1A53HR	V _F	I _F = 8mA	-	1.14	1.4	V
	Reverse current		I_R	$V_R = 3V$	-	-	10.0	μΑ	
Output	Operating supply voltage		Vcc		4.5	-	17.0	V	
	Low level output voltage		Vol	V_{CC} = 5V, I $_{F}$ = 0, I $_{OL}$ = 16mA	-	0.15	0.4	V	
	High level output voltage		V _{OH}	$V_{CC}=5V$, *5 $I_F=5mA$	4.9	-	-	V	
	Low level supply current		Iccl	$V_{CC}=5V, I_{F}=0$	-	1.7	3.8	mA	
	High level supply current		Icch	$V_{CC}=5V$, *5 $I_{F}=5mA$	-	0.7	2.2	mA	
Transfer charac- teristics	*3"Low→High" GP1A50HR/GP1A51HR GP1A52HR threshold input current GP1A53HR		IFLH	V _{CC} = 5V	-	1.0	5.0	mA	
			GP1A53HR	I_{FLH}	V _{CC} = 5V	-	1.5	8.0	mA
	*4 Hysteresis			I FHL /I FLH	V _{CC} = 5V	0.55	0.75	0.95	
	Response time	"Low→High propagation o		t _{PLH}	$V_{CC} = 5V$, *5 $I_{F} = 5mA$	-	3.0	9.0	μs
		"High→Low propagation o		t _{PHL}		-	5.0	15.0	
		Rise time		t _r	RL= 28082	-	0.1	0.5	
		Fall time		t _r		-	0.05	0.5	

^{*3} I $_{\mbox{\scriptsize FLH}}$ represents forward current when output changes from low to high.

^{*2} For 5 seconds

^{*4} I FHL represents forward current when output changes from high to low. Hysteresis stands for I FHL /I FLH.

^{*5} GP1A53HR Condition of V_{OH} , I $_{CCH}$, Response time; I_F = 8mA

■ Recommended Operating Conditions

Parameter	Symbol	Operating temp.	MIN.	MAX.	Unit
Low level output current	IoL	T- 0.4 70°C	-	16.0	mA
Forward current	I_F	$Ta = 0 \text{ to } + 70^{\circ}C$	10.0	20.0	mA

Fig. 1 Forward Current vs. Ambient Temperature




Fig. 3 Low Level Output Current vs. Ambient Temperature




Fig. 2 Output Power Dissipation vs.
Ambient Temperature




Fig. 4 Forward Current vs. Forward Voltage




Fig. 5 Relative Threshold Input Current vs. Supply Voltage




Fig. 7 Low Level Output Voltage vs. Low Level Output Current




Fig. 9 Supply Current vs. Ambient Temperature




Fig. 6 Relative Threshold Input Current vs.
Ambient Temperature




Fig. 8 Low Level Output Voltage vs.
Ambient Temperature




Fig.10-a Propagation Delay Time vs. Forward Current (GP1A50HR/GP1A51HR/GP1A52HR)




Fig.10-b Propagation Delay Time vs. Forward Current






Fig.12 Rise Time, Fall Time vs. Load Resistance



Test Circuit for Response Time



■ Precautions for Use

- In order to stabilize power supply line, connect a by-pass capacitor of more than 0.01μF between Vcc and GND near the device.
- (2) In case of cleaning, use only the following type of cleaning solvent. Ethyl alcohol, Methyl alcohol, Isopropyl alcohol
- (3) As for other general cautions refer to the chapter "Precautions for Use".

NOTICE

- •The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- •Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
 - (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - Personal computers
 - Office automation equipment
 - Telecommunication equipment [terminal]
 - Test and measurement equipment
 - Industrial control
 - Audio visual equipment
 - Consumer electronics
 - (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection with equipment that requires higher reliability such as:
 - Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
 - Traffic signals
 - Gas leakage sensor breakers
 - Alarm equipment
 - Various safety devices, etc.
 - (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - Space applications
 - Telecommunication equipment [trunk lines]
 - Nuclear power control equipment
 - Medical and other life support equipment (e.g., scuba).
- •Contact a SHARP representative in advance when intending to use SHARP devices for any "specific" applications other than those recommended by SHARP or when it is unclear which category mentioned above controls the intended use.
- •If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Control Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- •This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this
 publication.