S21MT1/S21MT2

Compact 4-pin DIP Type Phototriac Coupler

Features

- 1. Compact 4-pin DIP type
 - (Package area : 2/3 of conventional model)
- 2. Popular type
- 3. Recognized by UL (No. E64380)

Model Line-ups

	For 200V line
Zero-cross circuit not built in	S21MT1
Zero-cross circuit built in	S21MT2

Application

1. For SSR

Outline Dimensions (Unit:mm) .2^{±0.3} 0.3 Anode mark a S21MT1 s £ $6.5^{\pm 0.5}$ 0 7.62^{±0.3} $4.58^{\pm 0.5}$ $3.5^{\pm 0.5}$ 0.5TYP. 0.26±0.1 د 0 0 0.5^{±0.1} θ : 0 to 13° 3.4+ Internal connection diagram S21MT2 S21MT1 a 3 Þ 1 2 2 1 1 Anode ④ Anode/ Zero-cross circuit 2 Cathode Cathode ③ Anode/ Cathode

Absolute Maximum Ratings

(Ta=25°C)

	Parameter	Symbol	Rating	Unit
Input	Forward current	IF	50	mA
	Reverse voltage	VR	6	V
Output	*1 RMS ON-state current	IT	I _T 0.1	
	Peak one cycle surge current	Isurge	1.2 (50Hz sine wave)	Α
	Repetitive peak OFF-state voltage	VDRM	600	V
*2Isolation voltage		V _{iso}	5 000	V _{rms}
Operating temperature		Topr	-30 to+100	°C
Storage temperature		T _{stg}	-55 to+125	°C
*3Soldering temperature		T _{sol}	260 (for 10 sec)	°C

*1 Decrease in the ambient temperature range of the Absolute Max. Rating : Shown in Figs. 1 and 2.

*2 40 to 60% RH, AC for 1 minute

*3 For 10 seconds

⁽ⁱⁱⁱ In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that occur in equipment using any of SHARP's devices, shown in catalogs, data books, etc. Contact SHARP in order to obtain the latest version of the device specification sheets before using any SHARP's device."

Electro-optical Characteristics

(Ta=25°C)

Parameter		Symbol	Conditions	MIN.	TYP.	MAX.	Unit	
Input	Forward voltage		VF	$I_F = 20 m A$	-	1.2	1.4	V
	Reverse current		IR	$V_R = 3V$	-	-	10	μA
	Repetitive peak OFF-state current		I _{DRM}	V _{DRM} = Rated	-	-	1	μA
Output	ON-state voltage		VT	$I_T = 0.05 A$	-	-	3.0	V
	Holding current		I _H	$V_D = 6V$	0.1	-	3.5	mA
	Critical rate of rise of OFF-state voltage		dv/dt	$V_{DRM} = (1/\sqrt{2}) \bullet Rated$	100	-	-	V/µs
	Zero-cross voltage	S21MT2	Vox	$I_F = 15 \text{mA}$, Resistance load	-	-	35	V
Transfer characteristics	Minimum trigger current		I _{FT}	$R_L = 100\Omega, V_D = 6V$	-	-	10	mA
	Insulation resistance		RISO	DC = 500V, 40 to 60% RH	5 x 10 ¹⁰	$1 \ge 10^{11}$	-	Ω
	Turn-on timeS21MT1S21MT2	ton	$V_D = 6V, R_L = 100 \Omega, I_F = 20 m A$	-	-	100		
				-	-	50	μs	

Fig. 1 RMS ON-state Current vs. Ambient Temperature





Fig. 2 Forward Current vs. Ambient Temperature



• Please refer to the chapter "Precautions for Use." (Page 78 to 93)

NOTICE

- •The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- •Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- •Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
 - (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - Personal computers
 - Office automation equipment
 - Telecommunication equipment [terminal]
 - Test and measurement equipment
 - Industrial control
 - Audio visual equipment
 - Consumer electronics

(ii)Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection with equipment that requires higher reliability such as:

- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- Traffic signals
- Gas leakage sensor breakers
- Alarm equipment
- Various safety devices, etc.

(iii)SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:

- Space applications
- Telecommunication equipment [trunk lines]
- Nuclear power control equipment
- Medical and other life support equipment (e.g., scuba).
- •Contact a SHARP representative in advance when intending to use SHARP devices for any "specific" applications other than those recommended by SHARP or when it is unclear which category mentioned above controls the intended use.
- •If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Control Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- •This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- •Contact and consult with a SHARP representative if there are any questions about the contents of this publication.