MULTILAYER CERAMIC ANTENNA FOR BLUETOOTH & WLAN IEEE 802.11b (2.45G Hz ISM Band) (Long Shape)

Product Specification¹ (**Preliminary**)

QUICK REFERENCE DATA

Dimension 8* 3.5 * 0.9 mm

Central Frequency* 2.45 GHz

Bandwidth >100 MHz

Gain 0dBi max

VSWR 2.0 max

Polarization Linear

Azimuth Omni-directional

Azımun Onin-direci

Impedance 50Ω

Operating Temperature -55~125 °C

Termination Ni/Sn (Environmentally-Friendly Leadless)

Resistance to soldering heat 260°C, 10 sec.

Maximum Power 1W


* Three types of antenna are available for central frequency adjustment (type 245, type 260, type 270)

Special Environmental Concerns- Green Products Design: The foil making process is using environmentally-friendly aqueous solvent technology. Termination is lead free (Pb free) and packing materials can be re-cycled

¹ All the technical data and information contained herein are subject to change without priot notice

HF R&D	Print date 01/12/13	Print date 01/12/13			ernal use only
	Long Shape				Aug. 6, 01
	Multilayer Ceramic Antenna for Bluetooth (ISM Band 2.45GHz)		4311 11	4311 115 00245/260/270	
Grant Lin/Cliff	2	2001-08-06	Page 1	sheet 190-1	A4
spec.doc	Phycomp Taiwan Ltd.		10 -		1 1

APPLICATION



DIMENSIONAL DATA


Figure	Dimension	Port
$\begin{array}{c c} s1 \\ \hline C \\ C \\ \hline T \\ \hline F \\ \end{array}$	L 8±0.25 mm W 3.5±0.2 mm T 0.9±0.2 mm F 1.25±0.25 mm C 0.5±0.3 mm 1.25±0.25 mm	

HF R&D	Print date 01/12/13		Preliminary intern			use only	
	Long Shape					A	Aug. 6, 01
	Multilayer Ceramic Antenna for Bluetooth (ISM Band 2.45GHz)			4311 115 00245/260/270			
Grant Lin/Cliff		2001-08-06		Page 2	sheet 190-2		A4
spec.doc	Phycomp Taiwan Lto	d.					•

SOLDER LAND PATTERN

	Dimensions	Remark
L	9 ± 0.10 mm	
F	1.40 ± 0.10 mm	Feed Pad
С	$0.90 \pm 0.10 \text{ mm}$	
S1	1.40 ± 0.10 mm	NC Mount Pad
	F C	L 9 \pm 0.10 mm F 1.40 \pm 0.10 mm C 0.90 \pm 0.10 mm


Radiation Pattern Polar plot



HF R&D	Print date 01/12/13		Preliminary internal use				
	Long Shape					A	ug. 6, 01
	Multilayer Ceramic Antenna for Bluetooth (ISM Band 2.45GHz)		4311 115 00245/260/270				
Grant Lin/Cliff		2001-08-06		Page 3	sheet 190-3		A4
spec.doc	Phycomp Taiwan Lt	d.					

STANDARD TEST BOARD FOR SWR

(Note: Only for SWR Measurement, not for suggested layout)



HF R&D	Print date 01/12/13		Preliminary internal us			use only
	Long Shape				A	ug. 6, 01
	Multilayer Ceramic Antenna for Bluetooth (ISM Band 2.45GHz)		4311 115 0	4311 115 00245/260/270		
Grant Lin/Cliff		2001-08-06	Page 4	sheet 190-4		A4
spec.doc	Phycomp Taiwan Ltd		•		•	•

RELIABILITY DATA (Reference to IEC Specification)

IEC 384-10/ CECC 32 100 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
4.4		Mounting	The antenna can be mounted on printed-circuit boards or ceramic substrates by applying wave soldering, reflow soldering (including vapour phase soldering) or conductive adhesive	No visible damage
4.5		Visual inspection and dimension check	Any applicable method using × 10 magnification	In accordance with specification (chip off 4mm)
4.6.1		Antenna	Frequency = 2.45 GHz; at 20 °C	Standard test board in page 4
4.8		Adhesion	A force of 3 N applied for 10 s to the line joining the terminations and in a plane parallel to the substrate	No visible damage
4.9		Bond strength of plating on end face	Mounted in accordance with CECC 32 100, paragraph 4.4	No visible damage
			Conditions: bending 0.5 mm at a rate of 1mm/s, radius jig. 340 mm, 2mm warp on FR4 board of 90 mm length	No visible damage
4.10	20(Tb)	Resistance to soldering heat	260 ± 5 °C for 10 ± 0.5 s in a static solder bath	The terminations shall be well tinned after recovery and Central Freq. Change $\pm 6\%$

HF R&D	Print date 01/12/13			Preliminary internal use o			
	Long Shape					1	Aug. 6, 01
	Multilayer Ceramic Antenna for Bluetooth (ISM Band 2.45GHz)		43	4311 115 00245/260/270			
Grant Lin/Cliff		2001-08-06	Page 5		sheet 190-5		A4
spec.doc	Phycomp Taiwan Ltd	d.	•	•			•

IEC 384-10/ CECC 32 100 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
		Resistance to leaching	260 ± 5 °C for 30 ± 1 s in a static solder bath	Using visual enlargement of × 10, dissolution of the termination shall not exceed 10%
4.11	20(Ta)	Solderability	Zero hour test, and test after storage (20 to 24 months) in original atmosphere; un-mounted chips completely immersed for 2 ± 0.5 s in $235 \pm 5^{\circ}$ C.	The termination must be well tinned, at least 75% is well tinned at termination
4.12	4(Na)	Rapid change of temperature	-55 °C (30 minutes) to +125 °C (30 minutes); 100 cycles	No visible damage Central Freq. Change ± 6%
4.14	3(Ca)	Damp heat	500 ± 12 hours at 60 °C; 90 to 95 % RH	No visible damage 2 hours recovery Central Freq. Change ± 6%
4.15		Endurance	500 ± 12 hours at 125 °C;	No visible damage 2 hours recovery Central Freq. Change ±6%

HF R&D	Print date 01/12/13			Preliminary inte	nternal use only		
	Long Shape				Aug. 6, 01		
	Multilayer Ceramic A for Bluetooth (ISM B			4311 115 00245/260/270			
Grant Lin/Cliff		2001-08-06	Page 6	sheet 190-6	A4		
spec.doc	Phycomp Taiwan Ltd		•	· .			

ORDERING INFORMATION: Method I- by 12NC Ordering Code

The antennas may be ordered by using the 12 NC ordering code. These code numbers can be determined by the following rules:

 $\frac{43}{1}$ 1 1 15 00 245 F C M S T A

F. Family Code

43 = Antenna

C. Packing Type Code

11 = 180 mm / 7" blister (1000pcs), 12 = 330 mm / 13" blister (4000 pcs)

13 = Bulk (1000 pcs)

M. Materials Code

1 = High Frequency Material

S. Size Code

15 = 8 * 3.5 * 0.9 mm

T. Tolerance

00 = 100 M Hz Band Width

A. Working Frequency (three types of antenna are available)

245 = 2.45 GHzType 245260 = (2.45+0.15) GHz * Intention for shift up 150MHzType 260270 = (2.45+0.25) GHz * Intention for shift up 250MHzType 270

Example: 12NC 4311 111 00245

Product description: Antenna (43) by 180 mm blister (11) of High

Frequency Material (1), Size 7.35*5.5*1.3 mm (1);

Tolerance (00) of 100 MHz (VSWR<2)

Working Frequency (245) = 2.45G Hz

ORDERING INFORMATION: Method II- by Clear Text Code

The antennas may be ordered by using the 16-digit clear text ordering code. These code numbers can be determined by the following rules:

	AN2450000708031K (Clear Text Code Example)											
AN	2450	00	07	0803	1	K						
Product	Central Freq.	Bandwidth	Material	Size	Quantities	Packing						
AN=	2450=2.45GHz	00 = > 100 MHz	07=K7	0803=8*3.5*	1 = 1K	K=7" plastic						
Antenna	2600=2.60GHz			0.9 mm	4 = 4K	F=13" plastic						
	2700=2.70GHz					B = Bulk						

HF R&D	Print date 01/12/13		Preliminary inter			use only	
	Long Shape					A	ug. 6, 01
	Multilayer Ceramic Antenna for Bluetooth (ISM Band 2.45GHz)			4311 115 00245/260/270			
Grant Lin/Cliff		2001-08-06		Page 7	sheet 190-7		A4
spec.doc	Phycomp Taiwan Lto	d.					