

FOR .205 (5.2) × .025 (.64) STANDARD BLADE FUSES

For Littelfuse ATOF 287 series/Bussmann ATC series or equivalent

- Holds fuse securely, even after multiple insertions
- Thru hole-mount, maintains position during wave soldering
- Withstands the rigors of shock and vibration
- Holder design prevents solder wicking

SPECIFICATIONS


Contacts: .016 (.41) Brass, Tin-Nickel Plate
Insulator: Glass filled Nylon, UL Rated 94V-0

UL Current Rating: 20 Amps @ 500V AC

UL Temperature Rating: -58°F to +292°F (-50°C to +145°C)

3522-2


Mounting Detail For Two Clips



CAT. NO. 3522-2

3522-3

Mounting Detail For Two Clips



CAT. NO. 3522-3



VERTICAL ENTRY

SPECIFICATIONS

UL Current Rating: 30 Amps @ 500V AC

LOW INSERTION FORCE

Mounting Detail For Two Clips



CAT. NO. 3573
BULK & REEL*

*Reel Spec's: 24" diameter (4000 pieces per reel)

Material: .016 Brass, Matte-Tin Plate


CAT. NO. 3522

Material: .016 (.41) Brass, Tin-Nickel Plate

2 IN 1 FUSE HOLDER

For Littelfuse ATOF 287 series/Bussmann ATC series, Littelfuse Low Profile Mini (LP) series or equivalents

- Low insertion force
- Fuse holder fully insulates clips to protect fuse from shorting
- Holder assures proper spacing and reduces assembly time
- Thru hole PC mountable, maintains position during wave soldering




SPECIFICATIONS

Contacts: .016 (.41) Brass, Tin-Nickel Plate
Insulator: Nylon 46, UL Rated 94V-0


UL Current Rating: 30 Amps @ 500V AC

UL Temperature Rating: -58°F to +292°F (-50°C to +145°C)

Mounting Detail



Mounting Detail



CAT. NO. 3557 - Top Entry

CAT. NO. 3577 - Bottom Entry


CAT. NO.	COLOR	FUSE REF.
3557-2	Black	-
3557-10	Red	10 Amp
3557-15	Blue	15 Amp
3557-20	Yellow	20 Amp

All colors UL rated for 30 Amp.

UNIVERSAL CLIP

For Littelfuse ATOF 287 series/Bussmann ATC series, Littelfuse Mini 297 or 997 series/Bussmann ATM series, Littelfuse Low Profile Mini (LP) series or equivalents

- Accepts most Auto-Blade Fuses
- Low insertion force
- Thru hole PC mountable, maintains position during wave soldering



HORIZONTAL FUSE ENTRY

- Designed for low height clearance applications
- Fuse will be inserted parallel to board
- Thru hole mount, maintains position during wave soldering
- Fuse holder fully insulates clips to protect fuse from shorting
- Holder assures proper spacing and reduces assembly time
- Polarized legs assure proper orientation of clips onto board



SPECIFICATIONS

Contacts: .012 (.30) Brass

Insulator: Nylon 6/6, UL Rated 94V-0

UL Temperature Rating: -58°F to +292°F (-50°C to +145°C)

Mounting Detail For Two Clips



CAT. NO. 3550-2 Tin Plate

UL Current Rating: 20 Amps @ 500V AC

UL Current Rating: 30 Amps @ 500V AC

CAT. NO. 3550 Tin-Nickel Plate