


Series  
EPXSIZE 16 REAR REMOVABLE REAR RELEASE CRIMP SOCKET CONTACT  
FOR AWG 16, 18 AND 20 CABLESIssue:  
May 30, 2016Page  
1/1

MATERIAL :  
CONTACT BODY : BERYLLIUM COPPER PER ASTM B 196

PROTECTION SLEEVE : STAINLESS STEEL PER SAE AMS-5514


FINISH :  
CONTACT BODY : PLATING .00005 INCH OF GOLD PER SAE AMS-2422 OVER NICKEL PER SAE AMS-QQ-N-290  
PROTECTIVE SLEEVE : PASSIVATED PER SAE AMS-QQ-P-35

WIRING INSTRUCTIONS :  
WIRES ACCOMODATED : AWG 16 - 18 and 20  
INSULATION DIAMETER : 2,60 max (.071)  
STRIP LENGTH : 6 (.236)

TOOLING : (ORDERED SEPARATLY)  
CRIMPING TOOL : M22520/1-01 (RADIAL P/N : 282291)  
SELECTOR POSITION : 6 FOR AWG 16  
5 FOR AWG 18  
4 FOR AWG 20

POSITIONER : M22520/1-02 (RADIAL P/N : 282972)  
INS/EXT TOOL : M81969/1-03 (RADIAL P/N : 282546)  
SPL RADIAL INS. 282 89929 / EXT. 282 892

DIMENSIONS : mm (inch are given for information only)



CREATION

PEN: .

NOM: MACARI

DATE: JAN 17 1990

APPR.: .

|            |                                                        |          |           |
|------------|--------------------------------------------------------|----------|-----------|
| May 30, 16 | Protective sleeve $\varnothing$ 2.79/2.87 >>> 2.87 max | YON P.   | VIEIRA D. |
| AUG 29 06  | DIMENSION CONVERSION UPDATED                           | VALGRESY | L GARCIA  |
| Issue      | Revisions                                              | Name     | Approved  |

617340EN

RADIAL PROPRIETARY INFORMATION