
HAY. www.vishay.com

VS-MUR1020CTPbF, VS-MUR1020CT-N3

Vishay Semiconductors

Ultrafast Rectifier, 10 A FRED Pt®



PRODUCT SUMMARY						
Package	TO-220AB					
I _{F(AV)}	2 x 5 A					
V _R	200 V					
V _F at I _F	0.87 V					
t _{rr} typ.	See Recovery table					
T _J max.	175 °C					
Diode variation	Common cathode					

FEATURES

- Ultrafast recovery time
- Low forward voltage drop
- 175 °C operating junction temperature
- Low leakage current
- Designed and qualified according to JEDEC[®]-JESD 47
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

DESCRIPTION / APPLICATIONS

VS-MUR.. series are the state of the art ultrafast recovery rectifiers specifically designed with optimized performance of forward voltage drop and ultrafast recovery time.

The planar structure and the platinum doped life time control, guarantee the best overall performance, ruggedness and reliability characteristics.

These devices are intended for use in the output rectification stage of SMPS, UPS, DC/DC converters as well as freewheeling diode in low voltage inverters and chopper motor drives.

Their extremely optimized stored charge and low recovery current minimize the switching losses and reduce over dissipation in the switching element and snubbers.

ABSOLUTE MAXIMUM RATINGS								
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS				
Peak repetitive reverse voltage	V _{RRM}		200	V				
Average restified forward surrent			5					
Average rectified forward current total device	LF(AV)	Rated V _R , T _C = 149 °C	10					
Non-repetitive peak surge current per leg	I _{FSM}		50	A				
Peak repetitive forward current per leg	I _{FM}	Rated V _R , square wave, 20 kHz T _C = 149 °C	10					
Operating junction and storage temperatures	T _J , T _{Stg}		-65 to +175	°C				

ELECTRICAL SPECIFICATIONS ($T_J = 25$ °C unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS	
Breakdown voltage, blocking voltage	V _{BR} , V _R	I _R = 100 μA	200	-	-		
Forward voltage	V _F	I _F = 5 A, T _J = 125 °C	-	0.87	0.99	V	
		I _F = 10 A, T _J = 125 °C	-	1.02	1.20	ļ	
		I _F = 10 A	-	1.12	1.25		
Povoroo lookago ourront	I _R	V _R = V _R rated	-	-	10		
Reverse leakage current		$T_J = 150 \text{ °C}, V_R = V_R \text{ rated}$	-	-	250	μA	
Junction capacitance	CT	V _R = 200 V	-	8	-	pF	
Series inductance	L _S	Measured lead to lead 5 mm from package body	-	8.0	-	nH	





FREE



VS-MUR1020CTPbF, VS-MUR1020CT-N3

www.vishay.com

Vishay Semiconductors

DYNAMIC RECOVERY CHARACTERISTICS (T _J = 25 $^{\circ}$ C unless otherwise specified)								
PARAMETER	SYMBOL	TEST CO	MIN.	TYP.	MAX.	UNITS		
Reverse recovery time		$I_F = 1.0 \text{ A}, \text{ d}I_F/\text{d}t =$	50 A/µs, V _R = 30 V	-	-	35		
	+	I _F = 0.5 A, I _R = 1.0 A, I _{REC} = 0.25 A		-	-	25	ns	
	t _{rr}	T _J = 25 °C		-	24	-	115	
		T _J = 125 °C	I _F = 5 A dI _F /dt = 200 A/μs V _R = 160 V	-	35	-		
Doold recovery ourrent	I _{RRM}	T _J = 25 °C		-	3.3	-	А	
Peak recovery current		T _J = 125 °C		-	5.0	-	A	
Reverse recovery charge	0	T _J = 25 °C		-	33	-	nC	
	Q _{rr}	T _J = 125 °C		-	76	-		

THERMAL - MECHANICAL SPECIFICATIONS								
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS		
Maximum junction and storage temperature range	T _J , T _{Stg}		-65	-	175	°C		
Thermal resistance, junction to case per leg	R _{thJC}		-	-	5			
Thermal resistance, junction to ambient per leg	R _{thJA}		-	-	50	°C/W		
Thermal resistance, case to heatsink	R _{thCS}	Mounting surface, flat, smooth and greased	-	0.5	-			
Weight			-	2.0	-	g		
Weight			-	0.07	-	oz.		
Mounting torque			6.0 (5.0)	-	12 (10)	kgf · cm (lbf · in)		
Marking device		Case style TO-220AB		MUR1020CT				

VS-MUR1020CTPbF, VS-MUR1020CT-N3



Vishay Semiconductors




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. **Reverse Voltage**




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage





Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics

Revision: 10-Jul-15 Document Number: 94076 3 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000







Fig. 6 - Forward Power Loss Characteristics

Note



VS-MUR1020CTPbF, VS-MUR1020CT-N3

Vishay Semiconductors




Fig. 7 - Typical Reverse Recovery Time vs. dl_F/dt




Fig. 8 - Typical Stored Charge vs. dl_F/dt

 Revision: 10-Jul-15
 4
 Document Number: 94076

 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



VS-MUR1020CTPbF, VS-MUR1020CT-N3

Vishay Semiconductors





Fig. 9 - Reverse Recovery Parameter Test Circuit



(2) I_{RRM} - peak reverse recovery current

(3) t_{rr} - reverse recovery time measured from zero crossing point of negative going I_F to point where a line passing through 0.75 I_{RRM} and 0.50 I_{RRM} extrapolated to zero current. $Q_{rr} = \frac{t_{rr} \times I_{RRM}}{2}$ (5) dI_{(rec)M}/dt - peak rate of change of current during t_b portion of t_{rr}

Fig. 10 - Reverse Recovery Waveform and Definitions

www.vishay.com

VS-MUR1020CTPbF, VS-MUR1020CT-N3

Vishay Semiconductors

ORDERING INFORMATION TABLE

Device code	VS-	MUR	10	20	ст	PbF				
		2	3	4	5	6				
	 Vishay Semiconductors product Ultrafast MUR series 									
	3 -	Cur	rent rati	ng (10 =	= 10 A)					
	4	- Volt	age rati	ng (20 =	= 200 V))				
	5	CT	= centei	r tap (du	al) TO-	220/D ² F	PAK/TO-262			
	6	- Env	ironmer	ntal digit	:					
		PbF	= lead	(Pb)-fre	e and R	RoHS-co	ompliant			

-N3 = halogen-free, RoHS-compliant and totally lead (Pb)-free

ORDERING INFORMATION (Example)						
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION			
VS-MUR1020CTPbF	50	1000	Antistatic plastic tube			
VS-MUR1020CT-N3	50	1000	Antistatic plastic tube			


LINKS TO RELATED DOCUMENTS				
Dimensions		www.vishay.com/doc?95222		
Part marking information	TO-220ABPbF	www.vishay.com/doc?95225		
	TO-220AB-N3	www.vishay.com/doc?95028		




Vishay Semiconductors

TO-220AB

DIMENSIONS in millimeters and inches





Į	ᄂ	ea	ıu	as	S	gı	ш	п	eı	L	ι
						-					
	_										

<u>Diodes</u> 1. - Anode/open 2. - Cathode

2.	-	Cathode
3.	-	Anode

SYMBOL	MILLIM	IETERS	INC	NOTES	Γ	
	MIN.	MAX.	MIN.	MAX.	NOTES	
A	4.25	4.65	0.167	0.183		
A1	1.14	1.40	0.045	0.055		
A2	2.56	2.92	0.101	0.115]
b	0.69	1.01	0.027	0.040		1
b1	0.38	0.97	0.015	0.038	4	
b2	1.20	1.73	0.047	0.068		
b3	1.14	1.73	0.045	0.068	4]
С	0.36	0.61	0.014	0.024		
c1	0.36	0.56	0.014	0.022	4	
D	14.85	15.25	0.585	0.600	3	
D1	8.38	9.02	0.330	0.355		
D2	11.68	12.88	0.460	0.507	6	

Notes

- ⁽¹⁾ Dimensioning and tolerancing as per ASME Y14.5M-1994
- ⁽²⁾ Lead dimension and finish uncontrolled in L1
- ⁽³⁾ Dimension D, D1 and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- ⁽⁴⁾ Dimension b1, b3 and c1 apply to base metal only
- ⁽⁵⁾ Controlling dimensions: inches
- $^{\rm (6)}$ Thermal pad contour optional within dimensions E, H1, D2 and E1

MILLIMETERS INCHES SYMBOL NOTES MIN. MAX. MIN. MAX. 0.414 10.11 10.51 0.398 Е 3,6 E1 6.86 8.89 0.270 0.350 6 E2 0.76 0.030 7 --2.41 2.67 0.095 0.105 е 0.208 e1 4.88 5.28 0.192 H1 6.09 6.48 0.240 0.255 6,7 13.52 14.02 0.532 0.552 Т 3.32 3.82 0.131 0.150 2 L1 ØΡ 3.54 3.73 0.139 0.147 0.102 Q 2.60 3.00 0.118 90° to 93° 90° to 93° θ

Conforms to JEDEC outline TO-220AB

- $^{(7)}$ Dimensions E2 x H1 define a zone where stamping and singulation irregularities are allowed
- ⁽⁸⁾ Outline conforms to JEDEC TO-220, except A2 (maximum) and D2 (minimum) where dimensions are derived from the actual package outline



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.