
Vishay Semiconductors

High Voltage Surface Mount Input Rectifier Diode, 8 A



PRODUCT SUMMARY							
Package	TO-252AA (D-PAK)						
I _{F(AV)}	8 A						
V _R	800 V, 1200 V						
V_F at I_F	1.1 V						
I _{FSM}	150 A						
T _J max.	150 °C						
Diode variation	Single die						

FEATURES

- · Glass passivated pellet chip junction
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Input rectification
- Vishay Semiconductors switches and output rectifiers which are available in identical package outlines

DESCRIPTION

The 8EWS..SPbF rectifier high voltage series has been optimized for very low forward voltage drop, with moderate leakage. The glass passivation technology used has reliable operation up to 150 °C junction temperature.

The high reverse voltage range available allows design of input stage primary rectification with outstanding voltage surge capability.

OUTPUT CURRENT IN TYPICAL APPLICATIONS									
APPLICATIONS	SINGLE-PHASE BRIDGE	THREE-PHASE BRIDGE	UNITS						
NEMA FR-4 or G10 glass fabric-based epoxy with 4 oz. (140 µm) copper	1.2	1.6							
Aluminum IMS, R _{thCA} = 15 °C/W	2.5	2.8	А						
Aluminum IMS with heatsink, $R_{thCA} = 5 \text{ °C/W}$	5.5	6.5							

Note

T_A = 55 °C, T_J = 125 °C, footprint 300 mm²

MAJOR RATINGS AND CHARACTERISTICS									
SYMBOL	CHARACTERISTICS	VALUES	UNITS						
I _{F(AV)}	Sinusoidal waveform at $T_C = 116 \ ^{\circ}C$	8	A						
V _{RRM}		800/1200	V						
I _{FSM}		150	A						
V _F	8 A, T _J = 25 °C	1.10	V						
TJ		-55 to +150	°C						

VOLTAGE RATINGS									
PART NUMBER	V _{RRM} , MAXIMUM PEAK REVERSE VOLTAGE V	V _{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I _{RRM} AT 150 °C mA						
8EWS08SPbF	800	900	0.5						
8EWS12SPbF	1200	1300	0.5						

1 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000





Revision: 16-Jan-17

VS-8EWS..SPbF Series



Vishay Semiconductors

ABSOLUTE MAXIMUM RATINGS								
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS				
Maximum average forward current	I _{F(AV)}	T_C = 105 °C, 180° conduction half sine wave	8					
Maximum peak one cycle	I _{FSM}	10 ms sine pulse, rated V_{RRM} applied	125	А				
non-repetitive surge current		10 ms sine pulse, no voltage reapplied	150					
Maximum I ² t for fusing	l ² t	10 ms sine pulse, rated V _{RRM} applied	78	A ² s				
Maximum Ft for fusing	1-1	10 ms sine pulse, no voltage reapplied	110	A-s				
Maximum I ² \sqrt{t} for fusing	l²√t	t = 0.1 ms to 10 ms, no voltage reapplied	1100	A²√s				

ELECTRICAL SPECIFICATIONS									
PARAMETER	SYMBOL	TEST CO	TEST CONDITIONS						
Maximum forward voltage drop	V _{FM}	8 A, T _J = 25 °C	1.1	V					
Forward slope resistance	r _t	T _{.1} = 150 °C	20	mΩ					
Threshold voltage	V _{F(TO)}	1j = 150 C	0.82	V					
Maximum rayaraa laakaga aurrant		$T_J = 25 \ ^\circ C$	V - Roted V	0.05	mA				
Maximum reverse leakage current	IRM	T _J = 150 °C	V _R = Rated V _{RRM}	0.50					

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range	T _J , T _{Stg}		-55 to +150	°C
Maximum thermal resistance, junction to case	R _{thJC}	DC operation	2.5	°O (M)
Typical thermal resistance, junction to ambient (PCB mount)	R _{thJA (1)}		62	°C/W
Annyovimete weight			1	g
Approximate weight			0.03	oz.
Marking device		Case style TO-252AA (D-PAK)	8EWS12S	

Note

⁽¹⁾ When mounted on 1" square (650 mm²) PCB of FR-4 or G-10 material 4 oz. (140 µm) copper 40 °C/W For recommended footprint and soldering techniques refer to application note #AN-994






Fig. 1 - Current Rating Characteristics




Fig. 2 - Current Rating Characteristics




Fig. 3 - Forward Power Loss Characteristics

VS-8EWS..SPbF Series

Vishay Semiconductors





Fig. 4 - Forward Power Loss Characteristics



Half Cycle Current Pulses (N)






Fig. 6 - Maximum Non-Repetitive Surge Current

Revision: 16-Jan-17

3

Document Number: 94349

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Semiconductors




Fig. 7 - Forward Voltage Drop Characteristics





Fig. 8 - Thermal Impedance ZthJC Characteristics





LINKS TO RELATED DOCUMENTS							
Dimensions	www.vishay.com/doc?95016						
Part marking information	www.vishay.com/doc?95059						
Packaging information	www.vishay.com/doc?95033						




Vishay Semiconductors





D-PAK (TO-252AA)

DIMENSIONS in millimeters and inches



SYMBOL	MILLIMETERS		INC	HES	NOTES	NOTES	SYMBOL	MILLIN	IETERS	INC	HES	NOTES
STIVIDOL	MIN.	MAX.	MIN.	MAX.	NOTES	NOTES	STIVIDUL	MIN.	MAX.	MIN.	MAX.	NOTES
А	2.18	2.39	0.086	0.094			е	2.29	BSC	0.090	BSC	
A1	-	0.13	-	0.005			Н	9.40	10.41	0.370	0.410	
b	0.64	0.89	0.025	0.035			L	1.40	1.78	0.055	0.070	
b2	0.76	1.14	0.030	0.045			L1	2.74	BSC	0.108	REF.	
b3	4.95	5.46	0.195	0.215	3		L2	0.51	BSC	0.020	BSC	
С	0.46	0.61	0.018	0.024			L3	0.89	1.27	0.035	0.050	3
c2	0.46	0.89	0.018	0.035			L4	-	1.02	-	0.040	
D	5.97	6.22	0.235	0.245	5		L5	1.14	1.52	0.045	0.060	2
D1	5.21	-	0.205	-	3		Ø	0°	10°	0°	10°	
E	6.35	6.73	0.250	0.265	5		Ø1	0°	15°	0°	15°	
E1	4.32	-	0.170	-	3		Ø2	25°	35°	25°	35°	

Notes

⁽¹⁾ Dimensioning and tolerancing as per ASME Y14.5M-1994

(2) Lead dimension uncontrolled in L5

⁽³⁾ Dimension D1, E1, L3 and b3 establish a minimum mounting surface for thermal pad

(4) Section C - C dimension apply to the flat section of the lead between 0.13 and 0.25 mm (0.005 and 0.10") from the lead tip

(5) Dimension D, and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body

⁽⁶⁾ Dimension b1 and c1 applied to base metal only

⁽⁷⁾ Datum A and B to be determined at datum plane H

⁽⁸⁾ Outline conforms to JEDEC outline TO-252AA

Document Number: 95016



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.