


# SBG246



## Flow meter with integrated backflow prevention and display

SBG34IF0FRKG

Please note the changed housing design!



### Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	2...100 l/min	0.12...6 m <sup>3</sup> /h
Process connection	threaded connection G 3/4 internal thread	

### Application

Special feature	Gold-plated contacts
Application	for industrial applications
Media	Liquids; water; glycol solutions; coolants



## Flow meter with integrated backflow prevention and display

SBG34IF0FRKG

Note on media	oil 1 with viscosity: 10 mm <sup>2</sup> /s (40 °C)	
	oil 2 with viscosity: 46 mm <sup>2</sup> /s (40 °C)	
Medium temperature [°C]	-10...100	
Pressure rating	25 bar	2.5 MPa
MAWP for applications according to CRN [bar]	25	
<b>Electrical data</b>		
Operating voltage [V]	18...30 DC; (to SELV/PELV)	
Current consumption [mA]	< 50	
Protection class	III	
Reverse polarity protection	yes	
Power-on delay time [s]	< 3	
<b>Inputs / outputs</b>		
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
<b>Outputs</b>		
Total number of outputs	2	
Output signal	switching signal; analogue signal; frequency signal; IO-Link; (configurable)	
Number of digital outputs	2	
Output function	normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC [V]	2	
Permanent current rating of switching output DC [mA]	150; (per output 2 x 200 (...60 °C); 2 x 250 (...40 °C))	
Switching cycles (mechanical)	10 million	
Number of analogue outputs	1	
Analogue current output [mA]	4...20	
Max. load [Ω]	500	
Short-circuit protection	yes	
Overload protection	yes	
Frequency of the output [Hz]	0...10000	
<b>Measuring/setting range</b>		
Measuring range	2...100 l/min	0.12...6 m <sup>3</sup> /h
Display range	0...120 l/min	0...7.2 m <sup>3</sup> /h
Resolution	0.5 l/min	0.05 m <sup>3</sup> /h
Set point SP	1...100 l/min	0.05...6 m <sup>3</sup> /h
Reset point rP	0...99 l/min	0...5.95 m <sup>3</sup> /h
Frequency end point, FEP	6.5...100 l/min	0.4...6 m <sup>3</sup> /h
In steps of	0.5 l/min	0.05 m <sup>3</sup> /h
Frequency at the end point FRP [Hz]	10...10000	
Measuring dynamics	1:50	
<b>Temperature monitoring</b>		
Measuring range [°C]	-10...100	
Display range [°C]	-32...122	
Resolution [°C]	1	

# SBG246



## Flow meter with integrated backflow prevention and display

SBG34IF0FRKG

Set point SP	[°C]	-9...100
Reset point rP	[°C]	-10...99
In steps of	[°C]	1
Frequency start point, FSP	[°C]	-10...78
Frequency end point, FEP	[°C]	12...100
Frequency at the end point FRP	[Hz]	10...10000

### Accuracy / deviations

#### Flow monitoring

Accuracy (in the measuring range)	$\pm (4 \% MW + 1 \% MEW)$ ; ( $Q > 2 \text{ l/min}$ ; medium and operating temperature: $+22 \text{ °C} \pm 4\text{K}$ )
Repeatability	$\pm 1 \% MEW$

#### Temperature monitoring

Temperature drift	0,029 °C / K
Accuracy	[K] 3 K (25°C; $Q > 1 \text{ l/min}$ )

### Response times

#### Flow monitoring

Response time	[s]	0.01
Damping process value dAP	[s]	0...5
Damping for the analogue output dAA	[s]	0...5

#### Temperature monitoring

Dynamic response T05 / T09	[s]	T09 = 120 ( $Q > 1 \text{ l/min}$ )
----------------------------	-----	-------------------------------------

### Software / programming

Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current/frequency output; medium selection; damping for the switching output / analogue output; display can be rotated and switched off; standard unit of measurement; process value colour
---------------------------	--

### Interfaces

Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor - SSP 0	Generic Profiled Sensor
	Function	Device identification
	Function	Process data variable
	Function	Device diagnosis
SIO mode	yes	
Required master port type	A	
Process data analogue	2	
Process data binary	2	
Min. process cycle time	[ms]	3.2
Supported DeviceIDs	<b>Type of operation</b>	<b>DeviceID</b>
	default	563

### Operating conditions

Ambient temperature	[°C]	0...60
---------------------	------	--------

# SBG246



## Flow meter with integrated backflow prevention and display

SBG34IF0FRKG

Note on ambient temperature	medium temperature < 80 °C
	medium temperature < 100 °C: 0...40 °C
Storage temperature [°C]	-15...80
Protection	IP 65; IP 67

### Tests / approvals

EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF [years]		145
UL approval	UL approval no.	I006
	File number UL	E174189
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

### Mechanical data

Weight [g]	1488.75
Materials	stainless steel (316L/1.4404); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated
Materials (wetted parts)	stainless steel (316 / 1.4401); stainless steel (316L/1.4404); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM
Process connection	threaded connection G 3/4 internal thread

### Displays / operating elements

Display	Display unit	3 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, red/green 4-digit
	programming	alphanumeric display, 4-digit

### Remarks

Remarks	Recommendation: use a 200-micron filter.
	All data refer to water (20 °C).
	MW = measured value
	MEW = Final value of the measuring range
Notes	Please note the changed housing design!
Pack quantity	1 pcs.

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated






## Flow meter with integrated backflow prevention and display

SBG34IF0FRKG

### Connection



#### OUT1:

- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- frequency output volumetric flow quantity monitoring
- frequency output Temperature monitoring
- IO-Link

#### OUT2:


- switching output volumetric flow quantity monitoring
  - switching output Temperature monitoring
  - analogue output volumetric flow quantity monitoring
  - analogue output Temperature monitoring
- colours to DIN EN 60947-5-2

Core colours :

- BK = black
- BN = brown
- BU = blue
- WH = white

### Diagrams and graphs

#### Pressure loss



dP Pressure loss

Q volumetric flow quantity