

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Coupling connector, straight, shielded: yes, SPEEDCON locking, M23, Number of positions: 6, Type of contact: Male connector, Solder connection, Cable diameter: 4 mm ... 6 mm

Product Features

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires



Key Commercial Data

Packing unit	1 pc
Custom tariff number	85366990
Country of origin	Germany

Technical data

Temperature range

|--|

Data of the insulating body

Coding	Ν
Insulator material	РВТ
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles mechanical	100
Contact connection method	Solder connection
Type of contacts	Male connector
Number of positions	6
Contact diameter of power contacts	2 mm

04/05/2016 Page 1 / 4



Technical data

Data of the insulating body

Litz wire cross section of power contacts min.	0.08 mm ²
Litz wire cross section of power contacts max.	2.5 mm ²
Nominal current per power contact at 25°C	20 A
Nominal voltage, power contact	300 V
Overvoltage category	Ш
Degree of pollution	3

Housing data

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	SPEEDCON locking
Degree of protection (when plugged in)	IP67
Thread type	M23

Cable seal data

Min. cable diameter	4 mm
Max. cable diameter	6 mm
Sealing material	NBR

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	272607xx
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260702
eCl@ss 7.0	27440102
eCl@ss 8.0	27440102

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002635

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404



Classifications UNSPSC UNSPSC 13.2 43201404 Approvals Approvals Approvals UL Recognized / cUL Recognized / EAC / cULus Recognized Ex Approvals Approvals submitted Approval details UL Recognized 🔊 mm²/AWG/kcmil 14 20 A Nominal current IN Nominal voltage UN 300 V cUL Recognized 🔊 mm²/AWG/kcmil 14 Nominal current IN 10 A Nominal voltage UN 300 V EAC

cULus Recognized

04/05/2016 Page 3 / 4




Drawings

Schematic diagram

Dimensional drawing





Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com