

SU8000



Ultrasonic flow meter


SUR11HGBFRKG/W/US-100-IPF

phase-out article

Discontinuation date: 12/31/2025

Alternative articles: SU8030

When selecting an alternative article and accessories please note that technical data may differ!



installation length with pipe adapter E40152 / E40155: 205 mm
 installation length with pipe adapter E40153 / E40156: 215 mm



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	0...100 l/min	0...6 m³/h
Process connection	threaded connection G 1 external thread flat seal	

Application

Special feature	Gold-plated contacts	
Application	totaliser function; for industrial applications	
Installation	connection to pipe by means of an adapter	
Media	water; glycol solutions; coolants; oils	
Note on media	low-viscosity oils with viscosity: 7...40 mm²/s (40 °C) high-viscosity oils with viscosity: 30...68 mm²/s (40 °C)	
Medium temperature [°C]	-10...80	
Pressure rating	16 bar	1.6 MPa

Electrical data

Operating voltage [V]	19...30 DC; (to SELV/PELV)	
Current consumption [mA]	100	
Min. insulation resistance [MΩ]	100; (500 V DC)	
Protection class	III	
Reverse polarity protection	yes	

SU8000



Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF

Power-on delay time	[s]	10
Measuring principle		ultrasonic
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1
Inputs		
Inputs		counter reset
Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal; pulse signal; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250; (per output)
Number of analogue outputs		1
Analogue current output	[mA]	4...20; (scalable)
Max. load	[Ω]	500
Analogue voltage output	[V]	0...10; (scalable)
Min. load resistance	[Ω]	2000
Pulse output		flow rate meter
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Measuring range	0...100 l/min	0...6 m ³ /h
Display range	0...120 l/min	0...7.2 m ³ /h
Resolution	0.1 l/min	0.005 m ³ /h
Set point SP	0.2...100 l/min	0.01...6 m ³ /h
Reset point rP	0...99.8 l/min	0...5.99 m ³ /h
Analogue start point ASP	0...80 l/min	0...4.8 m ³ /h
Analogue end point AEP	20...100 l/min	1.2...6 m ³ /h
Max. flow rate	110 l/min	6.6 m ³ /h
In steps of	0.1 l/min	0.005 m ³ /h
Volumetric flow quantity monitoring		
Pulse value		0.1 l...1 000 000 m ³
Pulse length	[s]	0,025...2
Temperature monitoring		
Measuring range	[°C]	-10...80
Resolution	[°C]	0.2
Set point SP	[°C]	-9.8...80
Reset point rP	[°C]	-10...79.8
Analogue start point	[°C]	-10...62

SU8000



Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF

Analogue end point	[°C]	8...80
In steps of	[°C]	0.2

Accuracy / deviations

Flow monitoring		
Accuracy (in the measuring range)	water: $< \pm (3 \% MW + 0,2 \% MEW)$; glycol (35 %), oil (viscosity 68 mm ² /s at 40 °C): $< \pm (5 \% MW + 0,5 \% MEW)$	
Repeatability	0,2 l/min; 12 l/h; 0,012 m ³ /h	

Temperature monitoring		
Accuracy	[K]	$\pm 3 (Q > 1 \text{ l/min})$

Response times

Flow monitoring		
Response time	[s]	0.25; (dAP = 0)
Delay time programmable dS, dr	[s]	0...50
Damping process value dAP	[s]	0...1
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 70 (Q > 5 l/min); (water)

Software / programming

Parameter setting options	Flow monitoring; quantity meter; Preset counter; Temperature monitoring
---------------------------	-------------------------------------------------------------------------

Operating conditions

Ambient temperature	[°C]	-10...60
Storage temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
	EN 61000-4-3 HF radiated	10 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-5 Surge	0,5 kV	
	EN 61000-4-6 HF conducted	10 V	
CPA approval	model number	001US	
	accuracy class	3	
	maximum allowable error	-	
	Q (min)	0,3 m ³ /h	
Shock resistance	DIN IEC 68-2-27	20 g (11 ms)	
	Vibration resistance	DIN IEC 68-2-6	5 g (10...2000 Hz)
		MTTF	[years]
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request		

Mechanical data

Weight	[g]	1713.5
Housing		rectangular
Dimensions	[mm]	130 x 100 x 80.5
Materials		housing: AlMgSi0,5 anodised; Sealing: FKM; PA 6.6; cover film: PA

SU8000



Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF

Materials (wetted parts)	Pipe section: stainless steel (316L/1.4404); Process connection sealing: NBR reinforced fibre Flat seal; FKM; PES
Process connection	threaded connection G 1 external thread flat seal

Displays / operating elements		
Display	Display unit	6 x LED, green (l/min, m ³ /h, l, m ³ , 10 ³ , °C)
	switching status	2 x LED, yellow
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit

Accessories	
Items supplied	sealings: 2, Centellen
Accessories (optional)	adapter for pipe: 1 x R 1/2, stainless steel, E40179
	adapter for pipe: 1 x R 3/4, stainless steel, E40180
	adapter for pipe: 1 x R 1/2, brass, E40152
	adapter for pipe: 1 x R 3/4, brass, E40153


Remarks	
Remarks	MW = measured value MEW = Final value of the measuring range sealing: only with supplied Centellen seals
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Moulded body: brass, Optalloy-plated; Contacts: gold-plated



Connection



OUT1:	switching output volumetric flow quantity monitoring Pulse output quantity meter signal output Preset counter
OUT2/InD:	switching output volumetric flow quantity monitoring / Temperature monitoring analogue output volumetric flow quantity monitoring / Temperature monitoring input counter reset

SU8000


Ultrasonic flow meter

SUR11HGBFRKG/W/US-100-IPF



Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity