PQ033ES1MWP/PQ050ES1MWP

Low Output Current, Compact Surface Mount Type Low Power-Loss Voltage Regulators

Features

• Compact package: TO-92 type (Size(mold part): 5.2×5.5×4.2 mm)

• Small current output: MAX. 150mA

• Low dissipation current:

Quiescent current Iq=MAX. 350µA

• Low power-loss:

Dropout voltage: MAX. 0.26 V at Io=60 mA Dropout voltage: MAX. 0.4 V at Io=150 mA

• Built-in overcurrent, overheat protection functions


Taped package

Applications

- TV. VCR
- Air conditioners
- DVD players
- Audio equipment

Outline Dimensions

(Unit:mm)



Absolute Maximum Ratings

 $(T_a=25^{\circ}C)$

	_	(-,	0 0,
Parameter	Symbol	Rating	Unit
*1 Input voltage	Vin	16	V
Output current	Io	150	mA
*2 Power dissipation	PD	520	mW
*3 Junction temperature	Tj	150	°C
Operating temperature	Topr	-30 to +80	°C
Storage temperature	Tstg	–55 to +150	°C
Soldering temperature	Tsol	260(For 10s)	°C

^{*1} All are open except GND and applicable terminals.

· Please refer to the chapter " Handling Precautions ".

SHARP

^{*2} No heat sink

^{*3} Overheat protection may operate at 125≤T)≤150°C.

Electrical Characteristics

(Unless otherwise specified, V_{IN}=V_O(TYP.)+1.0V, I_O=30mA, Ta=25°C)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Output voltage	Vo	_	Refer to the table below		V	
	RegL1	Io=5mA to 60mA	_	10	50	mV
Load regulation	RegL2	Io=5mA to 100mA	-	20	100	mV
	RegL3	Io=5mA to 150mA	_	30	160	mV
Line regulation	RegI	V _{IN} =V _O (TYP.)+1V to V _O (TYP.)+6V	_	3.0	20	mV
Temperature coefficient of output voltage	TcVo	Io=10mA, Tj=25 to 75°C	-	0.05	_	mV/°C
Ripple rejection	RR	-	-	55	_	dB
Dropout voltage	VI-O	Io=60mA, V _{IN} =**4	-	0.11	0.26	V
	VI-O	Io=150mA, V _{IN} =**4	_	0.2	0.4	V
Quiescent current	I_{q}	Io=0mA	_	170	350	μA

^{*4} Dropout voltage when output voltage lowers 0.1V from the voltage at Vin=Vo+1V.

■ Output Voltage Line-up

(V_{IN}=Vo(TYP.)+1.0V, Io=30mA, Ta=25°C)

	Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Output voltage	PQ033ES1MWP	W _o	_	3.234	3.3	3.366	V
	PQ050ES1MWP	Vo		4.900	5.0	5.100	

NOTICE

- The circuit application examples in this publication are provided to explain representative applications of SHARP
 devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes
 no responsibility for any problems related to any intellectual property right of a third party resulting from the use of
 SHARP's devices.
- Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP
 reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents
 described herein at any time without notice in order to improve design or reliability. Manufacturing locations are
 also subject to change without notice.
- Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage
 caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used
 specified in the relevant specification sheet nor meet the following conditions:
 - (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - --- Personal computers
 - --- Office automation equipment
 - --- Telecommunication equipment [terminal]
 - --- Test and measurement equipment
 - --- Industrial control
 - --- Audio visual equipment
 - --- Consumer electronics
 - (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection with equipment that requires higher reliability such as:
 - --- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
 - --- Traffic signals
 - --- Gas leakage sensor breakers
 - --- Alarm equipment
 - --- Various safety devices, etc.
 - (iii)SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - --- Space applications
 - --- Telecommunication equipment [trunk lines]
 - --- Nuclear power control equipment
 - --- Medical and other life support equipment (e.g., scuba).
- Contact a SHARP representative in advance when intending to use SHARP devices for any "specific" applications
 other than those recommended by SHARP or when it is unclear which category mentioned above controls the
 intended use.
- If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Control Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this publication.