PCN Nun	PCN Number: 20200527000.1A PCN Date: Aug. 10, 2020						10, 2020				
Title: Add Cu as Alternative Wire Base Metal for Selected Device(s)											
Custome	r Contact	: PCN	Manager		Dept:	Quality Services					
Proposed 1 st Ship Date: Aug. 28			8,	2020 Estimated S			ample bility:		provid le requ		
Change 1	Гуре:										
	mbly Site				Design			Wafe	r Bumı	Site	
	mbly Proce				Data S					o Matei	
	mbly Mate			Щ	Part number change					Proce	:SS
	anical Spe			님	Test Site			Wafer Fab Site			
Раскі	ng/Shippi	ng/Labeli	ng	Ш	Test Pr	ocess	닏		Wafer Fab Materials Wafer Fab Process		
					DCN	Deteile		ware	r Fab F	rocess	
Descripti	ion of Ch				PCN	Details					
	ion of Cha										
notification first shipmed newly addresset of deverties. Texas Instantial for selected newly addressed newly newly addressed newly newl	Revision A is to announce the <u>addition</u> of new devices that were not included on the original PCN notification. These new devices are highlighted and bolded in the device list below. The expected first shipment date for these new devices will be 90 days from this notice (Nov 10, 2020) for these newly added devices only. The proposed 1 st ship date of Aug 28, 2020 still applies for the original set of devices. Texas Instruments is pleased to announce the qualification of Cu as an additional bond wire option for selected devices listed in "Product affected" section below. Devices will remain in current assembly facilities and there will be no other piece part changes:										
	ı	kg Fam	ily		С	urrent Wire		Additio	nal W	/ire	
	SOT-23, SOT-SC70, VSS0			ЭP	А	u, 0.9/1.0mil		Cu, C).96 m	il	
Reason f	or Chang	e:									
Continuity of supply. 1) To align with world technology trends and use wiring with enhanced mechanical and electrical properties 2) Maximize flexibility within our Assembly/Test production sites. 3) Cu is easier to obtain and stock											
Anticipated impact on Form, Fit, Function, Quality or Reliability (positive / negative):											
None											
Anticipated impact on Material Declaration											
	No Impact to the Material Declaration Material Declaration Material Declaration production data and will be available following the production release. Upon production release the revised reports can be obtained at the site link below http://www.ti.com/quality/docs/materialcontentsearch.tsp						tion be				
Changes to product identification resulting from this PCN:											
None	None										
											-

Product Affected:			
LM26CIM5-BPB/NOPB	LM27CIM5-1HJ/NOPB	LM86CIMM/NOPB	LM95241CIMM/NOPB
LM26CIM5-DPB/NOPB	LM27CIM5-2HJ/NOPB	LM86CIMMX/NOPB	LM95241CIMM-1/NOPB
LM26CIM5-HHD/NOPB	LM27CIM5X-1HJ/NOPB	LM89-1CIMM/NOPB	LM95241CIMM-2/NOPB
LM26CIM5-NPA/NOPB	LM27CIM5X-2HJ/NOPB	LM89-1CIMMX/NOPB	LM95241CIMMX/NOPB
LM26CIM5-PHA/NOPB	LM27CIM5-ZHJ/NOPB	LM89-1DIMM/NOPB	LM95245CIMM
LM26CIM5-RPA/NOPB	LM45BIM3	LM89-1DIMMX/NOPB	LM95245CIMM/NOPB
LM26CIM5-SHA/NOPB	LM45BIM3/NOPB	LM89CIMM/NOPB	LM95245CIMM-1/NOPB
LM26CIM5-SPA/NOPB	LM45BIM3X/NOPB	LM89CIMMX/NOPB	LM95245CIMMX/NOPB
LM26CIM5-TPA/NOPB	LM45CIM3/NOPB	LM90CIMM/NOPB	LM95245CIMMX-1/NOPB
LM26CIM5-VHA/NOPB	LM45CIM3/NOPB	LM90CIMMX/NOPB	LM99-1CIMM/NOPB
LM26CIM5-VPA/NOPB	LM45CIM3X/NOPB	LM94021BIMG/NOPB	LM99CIMM/J7002180
LM26CIM5X-DPB/NOPB	LM60BIM3	LM94021BIMGX/NOPB	LM99CIMM/NOPB
LM26CIM5-XHA/NOPB	LM60BIM3/NOPB	LM94022BIMG	LM99CIMMX/NOPB
LM26CIM5X-HHD/NOPB	LM60BIM3X	LM94022BIMG/NOPB	LMT84DCKR
LM26CIM5X-NPA/NOPB	LM60BIM3X/NOPB	LM94022BIMGX/NOPB	LMT84DCKT
LM26CIM5-XPA/NOPB	LM60CIM3	LM95010CIMM/NOPB	LMT85DCKR
LM26CIM5X-PHA/NOPB	LM60CIM3/NOPB	LM95071CIMF	LMT85DCKT
LM26CIM5X-SPA/NOPB	LM60CIM3X	LM95071CIMF/NOPB	LMT86DCKR
LM26CIM5X-TPA/NOPB	LM60CIM3X/NOPB	LM95071CIMFX	LMT86DCKT
LM26CIM5X-VHA/NOPB	LM61BIM3	LM95071CIMFX/NOPB	LMT87DCKR
LM26CIM5X-VPA/NOPB	LM61BIM3/NOPB	LM95221CIMM/NOPB	LMT87DCKT
LM26CIM5X-XHA/NOPB	LM61BIM3X/NOPB	LM95221CIMMX/NOPB	LMT88DCKR
LM26CIM5X-XPA/NOPB	LM61CIM3	LM95231BIMM-1/NOPB	LMT88DCKT
LM26CIM5X-YHA/NOPB	LM61CIM3/NOPB	LM95231CIMM/NOPB	LMT89DCKR
LM26CIM5X-YPA/NOPB	LM61CIM3X/NOPB	LM95231CIMM-1/NOPB	LMT89DCKT
LM26CIM5X-YPE/NOPB	LM62BIM3/NOPB	LM95231CIMM-2/NOPB	LMT90DBZR
LM26CIM5X-ZHA/NOPB	LM62BIM3X/NOPB	LM95231CIMMX/NOPB	LMT90DBZT
LM26CIM5-YHA/NOPB	LM62CIM3/NOPB	LM95235CIMM/NOPB	LPV801DBVR
LM26CIM5-YPA/NOPB	LM62CIM3X/NOPB	LM95235CIMMX/NOPB	LPV801DBVT
LM26CIM5-YPE/NOPB	LM71CIMF	LM95235DIMM/NOPB	TLV8801DBVR
LM26CIM5-ZHA	LM71CIMF/NOPB	LM95235DIMMX/NOPB	TLV8801DBVT
LM26CIM5-ZHA/NOPB	LM71CIMFX/NOPB	LM95235EIMM/NOPB	

Qualification Data

Approved on 08/17/2015

Qualification of 0.96 mils Cu wires on SOT-SC70 Package

Qualification Results Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition	Duration	Qual Device: LMV7275MG/NOPB	Supporting QBS: LM4041AIM3-1.2 (TL)	Supporting QBS: LM4041AIM3-1.2 (TL)
HAST	Biased HAST, 130C/85%RH	96 Hours	-	3/231/0	3/231/0
AC	Autoclave 121C	96 Hours	-	3/231/0	-
тс	Temperature Cycle, - 65/150C	500 Cycles	1/77/0	-	-
тс	Temperature Cycle, - 65/150C	1000 Cycles	-	3/231/0	-
HTSL	High Temp Storage Bake 150C	500 Hours	1/77/0	2/154/0	1/77/0
HTSL	High Temp Storage Bake 150C	1000 Hours	1/77/0	2/154/0	1/79/0
	Manufacturability (Assembly)		1/pass	1/pass	1/pass

- QBS: Qual By Similarity
- Qual Device LMV7275MG/NOPB is qualified at LEVEL1-260C
- Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable
- The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours
- The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours
- The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles Quality and Environmental data is available at Tl's external Web site: http://www.ti.com/

Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

Qualification Data

Qualification of 0.96 mils Cu wires on SOT23 Packages

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition	Duration	Qual Device: LM4041AIM3-1.2	Qual Device: LP3985IM5X-5.0	Qual Device: LMC7101AIM5NOPB	Qual Device: LM431CCM3NOPB
PC	PreCon Level 1	Level 1- 260C	3/693/0	3/462/0	3/693/0	3/462/0
HAST	Biased HAST, 130C/85%RH	96/hrs. @130C	3/231/0	-	3/231/0	-
AC	Autoclave 121C	96HRS	3/231/0	3/231/0	3/231/0	3/231/0
TC	Temperature Cycle, -65/150C	TMCL500X	3/231/0	3/231/0	3/231/0	3/231/0

HTSL	High Temp Storage Bake 150C	1000 hrs. @150C	1/77/0	-	1/77/0	1/77/0
MQ	Manufacturability (Assembly)	(per mfg. Site specification)	Pass	Pass	Pass	Pass
DPA	Destructive Physical Analysis Post 500 Temp Cycle	x-section and de process to examine assembly robustness, Check for stich bond and bond pad integrity	3/15/0	3/15/0	3/15/0	3/15/0
YLD	FTY and Bin Summary	Compare against baseline	Pass	Pass	Pass	Pass

⁻ Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable

Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

Qualification Data

Qualification of 0.96 mils Cu wires VSSOP Packages

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition	Duration	Qual Device: LMV852MMX	Qual Device: LMC6482IMM
PC	PreCon Level 1	Level 1-260C	3/462/0	3/462/0
HAST	Biased HAST, 130C/85%RH	96/hrs. @130C	-	-
AC	Autoclave 121C	96HRS	3/231/0	3/231/0
TC	Temperature Cycle, -65/150C	TMCL500X	3/231/0	3/231/0
HTSL	High Temp Storage Bake 150C	1000 hrs. @150C	-	-
MQ	Manufacturability (Assembly)	(per mfg. Site specification)	Pass	Pass
DPA	Destructive Physical Analysis Post 500 Temp Cycle	x-section and de process to examine assembly robustness, Check for stich bond and bond pad integrity	3/15/0	3/15/0
YLD	FTY and Bin Summary	Compare against baseline	Pass	Pass

⁻ Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable

⁻ The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours

⁻ The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours

⁻ The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles Quality and Environmental data is available at Tl's external Web site: http://www.ti.com/

⁻ The following are equivalent HTOL options based on an activation energy of 0.7eV : 125C/1k Hours, 140C/480 Hours, 150C/300 Hours, and 155C/240 Hours

⁻ The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours

⁻ The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles Quality and Environmental data is available at Tl's external Web site: http://www.ti.com/

Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

For questions regarding this notice, e-mails can be sent to the regional contacts shown below or your local Field Sales Representative.

Location	E-Mail				
USA	PCNAmericasContact@list.ti.com				
Europe	PCNEuropeContact@list.ti.com				
Asia Pacific	PCNAsiaContact@list.ti.com				
Japan	PCNJapanContact@list.ti.com				

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.