



Dome-Top® BT2M-M0 Barb Tie, Black, UV PA6.6, 7.9"L, 18lb, PK1000

BT2M-M0

The BT2M-M0 Dome-Top® barb tie, features a unique patented design with its round smooth edges. Paired with the stainless-steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Miniature cross section, 7.9" (201mm) length. Appropriate for Indoor/Outdoor use, made of Weather Resistant Nylon 6.6 with high resistance to ultraviolet light, are black in color and come in packages of 1000.

Specifications

Material Description	Nylon 6.6 (UV-Resistant, Weather-Resistant)
Product Type	Cable Tie
Sub Brand	Dome-Top®
Color	Black
Environment	Indoor/Outdoor
Material	Nylon 6.6
Resistance Properties	UV-Resistant, Weather-Resistant
Overall Length (In.)	7.9
Overall Length (mm)	201
Body Width (In.)	0.095
Body Width (mm)	2.4
Body Thickness (In.)	0.046
Body Thickness (mm)	1.2
Maximum Bundle Diameter (In.)	2
Maximum Bundle Diameter (mm)	51
Minimum Bundle Diameter (In.)	0.06
Minimum Bundle Diameter (mm)	1.5
Minimum Loop Tensile Strength (N)	80
Minimum Loop Tensile Strength (lb)	18
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Minimum Installation Temperature (°C)	-20
Minimum Installation Temperature (°F)	-4

Specifications (continued)

Standards Met	UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC 10CFR50, QPL-AS23190, CSA Certified, RoHS Compliant
For Use With	GTS-E, GS2B-E, PTS, PPTS, STS2

Packaging Detail

UPC	07498360289
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.0866
Std. Ctn. Qty.	25000
Std. Ctn. Volume (cf)	2.1638