3 mm Square SMT Trimmer Potentiometers (Carbon Composition, Dustproof Type)

EVM3YSX50B

Type: **EVN5E** (with rotation stopper) **EVN5C**

Alternative products EVN5ESX50B** EV EVM3VSX50B**

EVN5CSX50B**




■ Features

- No readjustment needed through Rotor protected Structure for careless slip
- Excellent mounting efficiency due to cubic shape suited to automatic pick-and-place assembly equipment
- Excellent reliability through dustproof Structure
- Rotation stopper featured type (EVN5E□)
- Conforms to JIS C5260-1:1999

■ Recommended Applications

- Audio/visual, office, and communication equipment
- General electronic equipment

■ Explanation of Part Numbers



*For part number details, refer to page ER137

(5E, 5C) Example : B52=500 Ω

Specifications

— -p		
Total Resistance Value Resistance Tolerance	200 Ω to 1 M Ω ±30 %	
Power Rating Maximum Operating Voltage	0.05 W (50 °C) 50 V	
Rotation Torque	1 to 15 mN·m	
Stopper Strength	20 mN·m (Stopper featured type)	
Temperature Coefficient of Resistance	$\pm 500 \times 10^{-6}$ /°C (25 to 85 °C) $\pm 750 \times 10^{-6}$ /°C (-25 to +25 °C)	


■ Minimum Quantity/Packing Unit


D N I	Taping		
Part Number	Quantity per reel	Packaging quantity	Dia. of reel (mm)
EVN5E EVN5C	2000	10000	φ178


The standard packaging methods for a reel is ϕ 178.

Please contact us, if you would like different packaging methods. (Bulk, Reel of \$\phi330\$, Reel of \$\phi380\$)

■ Dimensions in mm (not to scale)








Classification	Type	Symbol(1th to 5th)
	2 mm Open	EVM2T, EVM2N, EVM2W (low-profile)
Cermet	3 mm Open	EVM3Y, EVM3S EVM3R, EVM3W(low-profile) EVM3V(with rotation stopper)
	4 mm Open	EVM1D, EVM1E EVM1U
Carbon	3 mm Dustproof	EVN5E(with rotation stopper) EVN5C


Symbol	Resistance	EVM2T EVM2N EVM2W EVM3Y EVM3S EVM3W EVM3V EVM1D EVM1E EVM1U	EVM3R	EVN5E EVN5C
12	100 Ω	0	_	_
C2	150 Ω	0	_	_
22	200 Ω	0	_	0
E2	220 Ω	0	_	0
32	300 Ω	0	_	0
Y2	330 Ω	0	_	0
Q2	470 Ω	0	_	0
52	500 Ω	0	0	0
S2	680 Ω	0	0	0
13	1 kΩ	0	0	0
C3	1.5 kΩ	0	0	0
23	2 kΩ	0	0	0
E3	2.2 kΩ	0	0	0
33	3 kΩ	0	0	0
Y3	3.3 kΩ	0	0	0
Q3	4.7 kΩ	0	0	0
53	5 kΩ	0	0	0
S3	6.8 kΩ	0	0	0
14	10 kΩ	0	0	0
C4	15 kΩ	0	0	0
24	20 kΩ	0	0	0
E4	22 kΩ	0	0	0
34	30 kΩ	0	0	0
Y4	33 kΩ	0	0	0
Q4	47 kΩ	0	0	0
54	50 kΩ	0	0	0
S4	68 kΩ	0	0	0
15	100 kΩ	0	0	0
C5	150 kΩ	0	0	0
25	200 kΩ	0	0	0
E5	220 kΩ	0	0	0
35	300 kΩ	0	0	0
Y5	330 kΩ	0	0	0
Q5	470 kΩ	0	0	0
55	500 kΩ	0	0	0
S5	680 kΩ	0	0	0
16	1 ΜΩ	0	0	0



Alternative products

[3mm Square SMT Trimmer Potentiometers]

[3mm Square SMT Trimmer Potentiometers]		
Production discontinuance Parts No.	Туре	
	Carbon 3mm Square Dustproof (with the rotation stopper)	
EVN5CSX50B**	Carbon 3mm Square Dustproof	



[6mm Square Dustproof Ceramic Trimmer Potentiometers]

Production discontinuance Parts No.	Туре
EVMEASA00B**	Cermet 6mm Square Dustproof (Radial taping, with Knob Protection)
EVMEAGA00B**	Cermet 6mm Square Dustproof (Bulk, with Knob Protection)
EVMEESA00B**	Cermet 6mm Square Dustproof (Radial taping, with Knob Protection)
EVMEEGA00B**	Cermet 6mm Square Dustproof (Bulk, with Knob Protection)

