




Specification

Part No: MP11584



Product Description

Description:	43.9350MHz GSX-333/232AF SM Crystal
Product family:	GSX-333
Category:	SM Quartz Crystal
Order code:	MP11584

Features

- ▶ Metal lid can be grounded to minimise EMI
- ▶ Seam sealed for excellent long-term stability
- ▶ Ultra-miniature for maximum space saving

Additional Information

For further information regarding packaging, construction, material composition, soldering profile and environment, please refer to **GSX-333 Product Information sheet**

For dimensions, refer to package drawing: **D0262-A**

Electrical Specifications


Parameter	Value	Notes
Nominal frequency:	43.9350MHz	
Calibration tolerance:	±20ppm	@25°C
Temperature stability:	±30ppm	
Operating temperature range:	-20 to +70°C	
Storage temperature range:	-40 to +85°C	
Circuit condition (C _L):	10pF	
Oscillation mode:	Fundamental	
Equivalent series resistance:	50Ω max	
Test drive level:	10μW typ, 100μW max	
Static capacitance:	3.0pF max	
Ageing:	<±3ppm	First year





Product Information

GSX-333



Construction

- Ceramic body with gold-plated pads
- Metal lid, seam sealed

Composition



This product is lead-free, and is fully compliant with current RoHS directives



Packaging & Handling



Production quantities supplied on T&R, 3k pcs per reel. Small quantities may be supplied on tape (no reel), or in bulk.

Marking

FREQUENCY
DC


Marking type: Laser
DC = Date code

Tape & Reel Specification



Not to scale. Dimensional tolerances ±0.1mm unless otherwise stated.

Soldering Profile




Maximum solder resistance: 260°C x 10 secs x 2.





Package Drawing

D0262-A



Product Family

GSX-333

Construction

- ➡ Ceramic body with gold-plated pads
- ➡ Metal lid, seam sealed

Dimensions (mm)

