

LUMOTAST 75 IP40 - Illuminated pushbutton, flush lens, rectangular collar, latching, housing 1.15.108.152/0000



General information	
Form of lens	flat lens
Form of collar	rectangular
Color of collar	black
Dimensions	
Length of collar	24 mm
Width of collar	18 mm
Overall height	7.5 mm
Mounting depth	41.5/49.5/57.5 mm
Mounting hole	16.2 mm
Mechanical design	
Mounting	ring nut
Terminals	solder terminals
	·
Contact system Contact function	snap-action bridge contact
	latching 2 NC + 2 NO
Contact arrangement Contact materials	
Illumination	Ag LED
Lamp socket	<u>T 4.5</u>
Mechanical characteristics	
Operating force max.	3 6.5 N
Operating travel	2.7 mm
Switching travel NC	1.6 mm
Switching travel NO	0.9 mm
Robustness max.	100 N
Floatwicel characteristics	
Electrical characteristics	250.1/
Rated voltage AC max.	250 V
Rated voltage DC max.	230 V
Rated voltage AC/DC min.	12 V
Rated current PC may	4 A
Rated current AC/DC min	0.2 A
Rated current AC/DC min.	5 mA
Contact resistance acc. to life max.	200 mΩ
Protection class	14 127
ESD-strength min.	14 kV



Other specifications	
Operating life, at 250 V/2 A (operations)	200,000 (momentary) cycle
Operating life, at 250 V/4 A (operations)	60,000 (momentary), 10,000 (latching)
Degree of protection from front side	IP40 (DIN EN 60529)
Operation temperature min.	-25 °C
Ambient temp. operating max. without lamp / LED	+70 °C
Ambient temp. operating max. with lamp /LED	+55 °C
Storage temperature min.	-40 °C
Storage temperature max.	+80 °C
Environmental restistance	acc. to IEC 60068-2-14, -30, -33 and -78
Approvals	ENEC 25 T 55 (70), UL, CSA
Flame class acc. to UL 94	V 1
Hot wire ignition acc. to IEC 60695-2-1	yes
ROHS compliant	yes
REACH compliant	yes

Panel cut-out







