

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Cable connector, straight, Screw locking, M17, Number of positions: 8, Type of contact: Male connector, Crimp connection, shielded: yes, Cable diameter: 5 mm...8 mm

The figure shows the 17-pos. product version

#### **Product Features**

- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly
- Flexible use: reliably connect various cable diameters
- Molded designs with pre-assembled cables on one or both sides



### **Key Commercial Data**

Packing unit	1 pc
Weight per Piece (excluding packing)	70.0 g
Custom tariff number	85444290
Country of origin	Germany

#### Technical data

#### General

Note	Order information: Order crimp contacts Ø 1 mm separately
Type of locking	Screw locking
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Crimp connection
Type of contacts	Male connector
Number of positions	8
Contact diameter of power contacts	1 mm
Nominal current per power contact at 25°C	3.6 A



### Technical data

#### General

Conductor entry	5 mm 8 mm
Pg housing screw connection	none

#### Ambient conditions

Ambient temperature	-40 °C 125 °C
Degree of protection	IP67

### Specifications according to DIN EN 61984:2001

Installation height max.	3000 m
Nominal / operating voltage of power contacts	60 V
Rated surge voltage of power contacts	1.5 kV
Overvoltage category of power contacts	III
Degree of pollution of power contacts	3

## Classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260702
eCl@ss 7.0	27440102
eCl@ss 8.0	27440102

#### **ETIM**

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002641

#### **UNSPSC**

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

## Approvals

### Approvals



Approvals	
Approvals	
cUL Recognized / UL Recognized / EAC / cULus F	ecognized
Ex Approvals	
Approvals submitted	
Approval details	
cUL Recognized	
Nominal current IN	5 A
Nominal voltage UN	60 V
UL Recognized <b>\$1</b>	
No charles and IN	
Nominal current IN	5 A
Nominal voltage UN	60 V
EAC	
cULus Recognized • Sus	

Drawings




Schematic diagram



Connector pin assignment

Dimensional drawing



Dimensional drawing

Phoenix Contact 2016 @ - all rights reserved http://www.phoenixcontact.com