	$\begin{array}{c} L1 + 5.62 \\ L1 + 0.221^{*} \\ L1 + 0.217^{*} \\ \hline \\ \\ \hline \\$
General ordering data	4700700000
Order No.	1702730000
Part designation Version	BLZ 7.62/8/90 SN OR
Version	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 8, 90°, Box
EAN	4008190909215
Qty.	50 pc(s).
System parameters	
Conductor connection system	Clamping yoke connection
Outgoing direction of conductor	90°
Pitch	7.62 mm
Pitch in inch	0.3 inch
No. of poles	8
No. of rows	1
Screwdriver blade	0.6 x 3.5
Screwdriver blade standard	DIN 5264
Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.5 Nm
Clamping screw	M 2.5
Stripping length	7 mm
L1 in mm	53.34 mm
L1 in inch	2.1 inch
Electric shock protection to DIN VDE 0470	Safe from finger touch
Material data	
Insulating material	PBT
Colour	orange
colour chart	Similar to RAL 2000
Insulating material group	Illa
Flammability class UL 94	V-0
CTI	>= 200
Contact base material	Copper alloy
	Madalan (10) an 🔀



Material data	
Contact surface	tinned
Contact Sundce	
Connectable conductors	
Clamping range, min.	0.13 mm ²
Clamping range, max.	3.31 mm ²
AWG, min.	26
AWG, max.	12
Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	2.5 mm ²
Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	2.5 mm ²
With wire end ferrule, acc. to DIN 46 228/1, min.	0.2 mm ²
With wire end ferrule, acc. to DIN 46 228/1, max.	2.5 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.2 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, max.	2.5 mm ²
Gauge to EN 60999 a x b; \emptyset	2.8 mm x 2.0 mm; 2.4 mm
DIN IEC rating data	
Rated current, min. No. pins (Tu=20°C)	15 A
Rated current, max. No. pins (Tu=20°C)	13 A
Rated current, min. No. pins(Tu=40°C)	12.5 A
Rated current, max. No. pins (Tu=40°C)	11 A
Rated voltage for overvoltage class/pollution	800 V
severity II/2	
Rated voltage for overvoltage class/pollution	800 V
severity III/2	
Rated voltage for overvoltage class/pollution	500 V
severity III/3	
Rated impulse withstand voltage for overvoltage	8 kV
class/pollution severity II/2	
Rated impulse withstand voltage for overvoltage	8 kV
class/pollution severity III/2	
Rated impulse withstand voltage for overvoltage	6 kV
class/pollution severity III/3	
Short-time withstand current resistance	3 x 1s with 120 A
CSA rating data	
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A
AWG conductor (field wiring), min.	26
AWG conductor (field wiring), max.	12
UL 1059 rating data	
Rated voltage (Use group D)	300 V
Rated current (Use group D)	10 A
AWG conductor, min.	26
AWG conductor, max.	12



Approvals

Approvals institutes



Classifications

ETIM 2.0	NK
ETIM 3.0	EC001284
eClass 4.1	27-26-07-01
eClass 5.0	27-26-07-01
eClass 5.1	27-26-07-04

Similar products

1702670000	BLZ 7.62/2/90 SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 2, 90°, Box
1702680000	BLZ 7.62/3/90 SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 3, 90°, Box
1702690000	BLZ 7.62/4/90 SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 4, 90°, Box
1702700000	BLZ 7.62/5/90 SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 5, 90°, Box
1702710000	BLZ 7.62/6/90 SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 6, 90°, Box
1702720000	BLZ 7.62/7/90 SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 7, 90°, Box
1702740000	BLZ 7.62/9/90 SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 9, 90°, Box
1702750000	BLZ 7.62/10/90 SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 10, 90°, Box
1702760000	BLZ 7.62/11/90 SN OR	PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Pitch: 7.62 mm, No. of poles: 11, 90°, Box



1702770000 BLZ 7.62/12/90 SN OR

PCB plug-in connector, Female connectors, Clamping yoke connection, Clamping range, max.: 3.31 mm², Pitch: 7.62 mm, No. of poles: 12, 90°, Box

