


L7805CV

Three-terminal positive voltage regulator

TO-220

FEATURES

- Maximum Output Current I_{OM} : 1.5A
- Output Voltage V_O : 5V
- Continuous total dissipation
 P_D : 1.5W($T_A=25^\circ\text{C}$)
15W($T_C=25^\circ\text{C}$)



ABSOLUTE MAXIMUM RATINGS (Operating temperature range applies unless otherwise specified)


Parameter	Symbol	Value	UNIT
Input Voltage	V_i	35	V
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	83.3	$^\circ\text{C/W}$
Thermal Resistance from Junction to Case	$R_{\theta JC}$	8.3	$^\circ\text{C/W}$
Operating Junction Temperature Range	T_{OPR}	0 ~ +150	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 ~ +150	$^\circ\text{C}$

ELECTRICAL CHARACTERISTICS AT SPECIFIED VIRTUAL JUNCTION TEMPERATURE

($V_i=10\text{V}$, $I_O=500\text{mA}$, $C_i=0.33\mu\text{F}$, $C_O=0.1\mu\text{F}$, unless otherwise specified)







Parameter	Symbol	Test conditions		MIN	TYP	MAX	UNIT
Output Voltage	V_O		25 $^\circ\text{C}$	4.8	5.0	5.2	V
		$7\text{V} \leq V_i \leq 20\text{V}$, $I_O=5\text{mA}-1\text{A}$, $P \leq 15\text{W}$	0~125 $^\circ\text{C}$	4.75	5.00	5.25	
Load Regulation	ΔV_O	$I_O=5\text{mA}-1.5\text{A}$	25 $^\circ\text{C}$		9	100	mV
		$I_O=250\text{mA}-750\text{mA}$	25 $^\circ\text{C}$		4	50	
Line Regulation	ΔV_O	$7\text{V} \leq V_i \leq 25\text{V}$	25 $^\circ\text{C}$		4	100	mV
		$8\text{V} \leq V_i \leq 12\text{V}$	25 $^\circ\text{C}$		1.6	50	
Quiescent Current	I_Q		25 $^\circ\text{C}$		5	8	mA
Quiescent Current Change	ΔI_Q	$7\text{V} \leq V_i \leq 25\text{V}$	0~125 $^\circ\text{C}$		0.3	1.3	mA
		$5\text{mA} \leq I_O \leq 1\text{A}$	0~125 $^\circ\text{C}$		0.03	0.5	
Output Noise Voltage	V_N	$10\text{Hz} \leq F \leq 100\text{KHz}$	25 $^\circ\text{C}$		42		μV
Output Voltage Drift	$\Delta V_O/\Delta T$	$I_O=5\text{mA}$	0~125 $^\circ\text{C}$		-1.1		mV/ $^\circ\text{C}$
Ripple Rejection	RR	$8\text{V} \leq V_i \leq 18\text{V}$, $F=120\text{Hz}$	0~125 $^\circ\text{C}$	62	73		dB
Dropout Voltage	V_D	$I_O=1\text{A}$	25 $^\circ\text{C}$		2		V
Output Resistance	R_O	$F=1\text{KHz}$	25 $^\circ\text{C}$		10		m Ω
Short Circuit Current	I_{SC}		25 $^\circ\text{C}$		230		mA
Peak Current	I_{PK}		25 $^\circ\text{C}$		2.2		A

TYPICAL APPLICATION




All products, product specifications and data are subject to change without notice to improve reliability, function or design or otherwise.

TYPICAL CHARACTERISTICS



All products, product specifications and data are subject to change without notice to improve reliability, function or design or otherwise.

TO-220-3L Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	4.470	4.670	0.176	0.184
A1	2.520	2.820	0.099	0.111
b	0.710	0.910	0.028	0.036
b1	1.170	1.370	0.046	0.054
c	0.310	0.530	0.012	0.021
c1	1.170	1.370	0.046	0.054
D	10.010	10.310	0.394	0.406
E	8.500	8.900	0.335	0.350
E1	12.060	12.460	0.475	0.491
e	2.540 TYP		0.100 TYP	
e1	4.980	5.180	0.196	0.204
F	2.590	2.890	0.102	0.114
h	0.000	0.300	0.000	0.012
L	13.400	13.800	0.528	0.543
L1	3.560	3.960	0.140	0.156
Φ	3.735	3.935	0.147	0.155

All products, product specifications and data are subject to change without notice to improve reliability, function or design or otherwise.