

## L7806CV

Three-terminal positive voltage regulator

TO-220


### FEATURES

- Maximum Output Current  $I_{OM}$ : 1.5A
- Output Voltage  $V_O$ : 6V
- Continuous total dissipation  
 $P_D$ : 1.5W( $T_A=25^\circ\text{C}$ )

1.IN

2.GND

3.OUT



### ABSOLUTE MAXIMUM RATINGS (Operating temperature range applies unless otherwise specified)


Parameter	Symbol	Value	UNIT
Input Voltage	$V_i$	35	V
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	66.7	$^\circ\text{C}/\text{W}$
Operating Junction Temperature Range	$T_{OPR}$	-25 ~ +125	$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-65 ~ +150	$^\circ\text{C}$

### ELECTRICAL CHARACTERISTICS AT SPECIFIED VIRTUAL JUNCTION TEMPERATURE







( $V_i=11\text{V}$ ,  $I_o=500\text{mA}$ ,  $C_i=0.33\mu\text{F}$ ,  $C_o=0.1\mu\text{F}$ , unless otherwise specified)

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Output Voltage	$V_O$		25 $^\circ\text{C}$	5.75	6	6.25
		$8\text{V} \leq V_i \leq 21\text{V}$ , $I_o=5\text{mA}-1\text{A}$	-25~125 $^\circ\text{C}$	5.7	6	6.3
Load Regulation	$\Delta V_O$	$I_o=5\text{mA}-1.5\text{A}$	25 $^\circ\text{C}$		14	120
		$I_o=250\text{mA}-750\text{mA}$	25 $^\circ\text{C}$		4	60
Line Regulation	$\Delta V_O$	$8\text{V} \leq V_i \leq 25\text{V}$	25 $^\circ\text{C}$		5	120
		$9\text{V} \leq V_i \leq 13\text{V}$	25 $^\circ\text{C}$		1.5	60
Quiescent Current	$I_Q$		25 $^\circ\text{C}$		4.3	8
Quiescent Current Change	$\Delta I_Q$	$8\text{V} \leq V_i \leq 25\text{V}$	-25~125 $^\circ\text{C}$			1.3
		$5\text{mA} \leq I_o \leq 1\text{A}$	-25~125 $^\circ\text{C}$			0.5
Output Noise Voltage	$V_N$	$10\text{Hz} \leq F \leq 100\text{KHz}$	25 $^\circ\text{C}$		45	mV/ $V_O$
Output Voltage Drift	$\Delta V_O/\Delta T$	$I_o=5\text{mA}$	0~125 $^\circ\text{C}$		-0.8	mV/ $^\circ\text{C}$
Ripple Rejection	$RR$	$9\text{V} \leq V_i \leq 19\text{V}$ , $F=120\text{Hz}$	-25~125 $^\circ\text{C}$	59	75	dB
Dropout Voltage	$V_D$	$I_o=1\text{A}$	25 $^\circ\text{C}$		2	V
Output Resistance	$R_O$	$F=1\text{KHz}$	25 $^\circ\text{C}$		10	m $\Omega$
Short Circuit Current	$I_{SC}$		25 $^\circ\text{C}$		550	mA
Peak Current	$I_{PK}$		25 $^\circ\text{C}$		2.2	A

### TYPICAL APPLICATION




## Typical Characteristics



All products, product specifications and data are subject to change without notice to improve reliability, function or design or otherwise.

## TO-220-3L Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	4.470	4.670	0.176	0.184
A1	2.520	2.820	0.099	0.111
b	0.710	0.910	0.028	0.036
b1	1.170	1.370	0.046	0.054
c	0.310	0.530	0.012	0.021
c1	1.170	1.370	0.046	0.054
D	10.010	10.310	0.394	0.406
E	8.500	8.900	0.335	0.350
E1	12.060	12.460	0.475	0.491
e	2.540 TYP		0.100 TYP	
e1	4.980	5.180	0.196	0.204
F	2.590	2.890	0.102	0.114
h	0.000	0.300	0.000	0.012
L	13.400	13.800	0.528	0.543
L1	3.560	3.960	0.140	0.156
Φ	3.735	3.935	0.147	0.155

All products, product specifications and data are subject to change without notice to improve reliability, function or design or otherwise.