


L7905CV

Three-terminal negative voltage regulator

FEATURES

- Maximum Output Current I_{OM} : 1.5A
- Output Voltage V_O : -5V
- Continuous total dissipation
 P_D : 1.5W($T_A=25^\circ\text{C}$)



ABSOLUTE MAXIMUM RATINGS (Operating temperature range applies unless otherwise specified)


Parameter	Symbol	Value	UNIT
Input Voltage	V_i	-35	V
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	83.3	$^\circ\text{C}/\text{W}$
Operating Junction Temperature Range	T_{OPR}	0 ~ +150	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-65 ~ +150	$^\circ\text{C}$

ELECTRICAL CHARACTERISTICS AT SPECIFIED VIRTUAL JUNCTION TEMPERATURE







($V_i=-10\text{V}$, $I_O=500\text{mA}$, $C_i=2.2\mu\text{F}$, $C_o=1\mu\text{F}$, unless otherwise specified)

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Output Voltage	V_O	25°C	-4.8	-5	-5.2	V
		$-7\text{V} \leq V_i \leq -20\text{V}$, $I_O=5\text{mA}-1\text{A}$, $0 \sim 125^\circ\text{C}$	-4.75	-5	-5.25	
Load Regulation	ΔV_O	$I_O=5\text{mA}-1.5\text{A}$, 25°C		15	100	mV
		$I_O=250\text{mA}-750\text{mA}$, 25°C		5	50	
Line Regulation	ΔV_O	$-7\text{V} \leq V_i \leq -25\text{V}$, 25°C		12.5	50	mV
		$-8\text{V} \leq V_i \leq -12\text{V}$, 25°C		4	15	
Quiescent Current	I_Q	25°C		1.5	2	mA
Quiescent Current Change	ΔI_Q	$-7\text{V} \leq V_i \leq -25\text{V}$, $0 \sim 125^\circ\text{C}$			0.5	mA
		$5\text{mA} \leq I_O \leq 1\text{A}$, $0 \sim 125^\circ\text{C}$			0.5	
Output Noise Voltage	V_N	$10\text{Hz} \leq F \leq 100\text{KHz}$, 25°C		125		$\mu\text{V}/V_O$
Output Voltage Drift	$\Delta V_O/\Delta T$	$I_O=5\text{mA}$, $0 \sim 125^\circ\text{C}$		-0.4		$\text{mV}/^\circ\text{C}$
Ripple Rejection	RR	$-8\text{V} \leq V_i \leq -18\text{V}$, $F=120\text{Hz}$, $0 \sim 125^\circ\text{C}$	54	60		dB
Dropout Voltage	V_D	$I_O=1\text{A}$, 25°C		1.1		V
Peak Current	I_{PK}	25°C		2.1		A

TYPICAL APPLICATION




TYPICAL CHARACTERISTICS



All products, product specifications and data are subject to change without notice to improve reliability, function or design or otherwise.

TO-220-3L Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	4.470	4.670	0.176	0.184
A1	2.520	2.820	0.099	0.111
b	0.710	0.910	0.028	0.036
b1	1.170	1.370	0.046	0.054
c	0.310	0.530	0.012	0.021
c1	1.170	1.370	0.046	0.054
D	10.010	10.310	0.394	0.406
E	8.500	8.900	0.335	0.350
E1	12.060	12.460	0.475	0.491
e	2.540 TYP		0.100 TYP	
e1	4.980	5.180	0.196	0.204
F	2.590	2.890	0.102	0.114
h	0.000	0.300	0.000	0.012
L	13.400	13.800	0.528	0.543
L1	3.560	3.960	0.140	0.156
Φ	3.735	3.935	0.147	0.155

All products, product specifications and data are subject to change without notice to improve reliability, function or design or otherwise.