



General ordering data

Order No. Part designation Version

EAN Qty.

Note, ordering data

Note, technical data

Product description

Note, accessories

PT OKIECEx/ATEX rating data

EU-type examination certificate Download, German Download English IECEx Certificate of Conformity Download ATEX voltage ATEX current ATEX conductor cross-section IECEx voltage IECEx current IECEx conductor cross-section Voltage when using cross-connections Operating temperature range

Marking EN 60079-7

9537440000 WDU 4 SL Special terminal, special connections, 4 mm², Screw connection, Wemid, dark beige, TS 35 4032248037445 50 pc(s).

Are suitable for a rated voltage of 630 V with pollution degree 2 (no larger soiling appears). Note the max. current of the terminal (41 A) when using the cross-connector! Spring below clamping yoke ensures additional contact stability. Hook-shaped cable lugs 1-2.5mm² thin versionorderno. 9036300000 (100 pcs.)

SIRA02ATEX3242U

SIRA02ATEX3242U_e.pdf IECEXSIR05.0040U IECEXSIR05.0040U_e.pdf 275 V 28 A 4 mm² 275 V 28 A 4 mm² CrossConnectionGuide.pdf For operating temperature range see EC Design Test Certificate / IEC Ex-Certificate of Conformity Ex e II



2 clampable conductors (H05V/H07V) with	
equal cross-section (rated connection)	
Solid, min.	0.5 mm ²
Solid, max.	1.5 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	1.5 mm ²
Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	1.5 mm ²
Additional technical data	
Colour of insulating material	dark beige
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	∠ right
Operating temperature range	- 50 °C, + 120 °C
Product family	W-Series
Type of connection	Screwed
Type of mounting	Sciewed Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Feed-through terminal
Version	
CSA rating data	
Voltage (CSA)	300 V
CSA current	25 A
Min. cross-section (CSA)	AWG 22
Max. cross-section (CSA)	AWG 10
Conductors for clamping (additional	
connection)	
Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	4 mm ²
Conductors for clamping (rated connection)	0.00
Clamping range, min.	0.22 mm ²
Clamping range, max.	6 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	2
Stripping length	15 mm
Clamping screw	M 3
Blade size	0.6 x 3.5 mm
Tightening torque range	0.51.0 Nm
Torque level with DMS electric screwdriver	2
Gauge to IEC 60947-1	A4



Solid, min.	0.5 mm ²
Solid, max.	6 mm²
Stranded, min.	1.5 mm ²
Stranded, max.	6 mm²
Flexible, min.	0.5 mm²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm²
Flexible with ferrule, max. (DIN 46228/1)	4 mm ²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 10
AWG conductor size, min.	0.13 mm²
AWG conductor size, max.	5.26 mm ²
Dimensions	
Width	6.1 mm
Height of lowest version	47 mm
Length	60 mm
Weight	11.54 g
TS 35 offset	32 mm
Disconnect terminals	
Torque level with DMS electric screwdriver	2
Rating data	
Rated cross-section	4 mm²
Rated voltage	500 V
Rated impulse voltage	6 kV
Rated current	32 A
Standards	IEC 60947-7-1
Current with max. conductor	41 A
Pollution severity	3
UL rating data	
Voltage (UL)	600 V
Current (UL)	30 A
Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 10
Approvals	
Approvals institutes	



Classifications		
ETIM 2.0	EC000897	
ETIM 3.0	EC000897	
	- 3 -	Weidmüller 🌫

eClass 4.1		27-14-11-31	
eClass 5.0		27-14-11-31	
eClass 5.1		27-14-11-31	
Similar products			
Order No.		Version	
9537450000	WDU 4 SL/EN	Special terminal, special connections, 4 mm ² , Screw connection, Wemid, dark beige, TS 35 + TS 32	
9537510000	WDU 4 SL/EN SW	Special terminal, special connections, 4 mm ² , Screw connection, PA 66, black, TS 35 + TS 32	

