





PART NO.	A99000-100	REV	ECO	DATE	APP
		B	106302	03-31-2020	TLM

MATERIALS

- HOUSING:**
ALUMINUM 6061, NICKEL PLATE
(500 MICRONS MINIMUM) PER
SAE-AMS-2404
- INSULATOR:**
LIQUID CRYSTAL POLYMER (LCP)
PER ASTM D5138
- CONTACT/SOLDERCUP:**
COPPER ALLOY PER MIL-DTL-
83513, GOLD PLATED PER ASTM
B488, (HARD GOLD) TYPE II CODE
C CLASS 1.27
- INTERFACIAL SEAL:**
FLUOROSILICONE RUBBER PER A-
A-59588
- HARDWARE:**
AVAILABLE UPON REQUEST



RoHS

NOTE:
DIMENSIONS IN [] ARE IN
MILLIMETERS UNLESS
OTHERWISE NOTED AND ARE
FOR REFERENCE ONLY

MDCS	THIRD ANGLE ϕ ∇	THIS DRAWING CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION WHICH IS THE PROPERTY OF OMNETICS CONNECTOR CORP. THIS DOCUMENT MAY NOT, IN WHOLE OR IN PART, BE DUPLICATED, OR DISCLOSED FOR ANY PURPOSE, WITHOUT WRITTEN PERMISSION FROM OMNETICS CONNECTOR CORP.	DATE 01-30-17	TITLE: (100) SOCKET FEMALE MICRO-D CONNECTOR	CAGE CODE 61873	
	-TOLERANCES- UNLESS OTHERWISE NOTED					DWTM. ERB
SLDW	DIMENSIONS IN INCHES	2 PL DEC± .01	CHK'D.	APP'D.	SHEET 1 OF 1	REV B
	2 PL DEC± .01 3 PL DEC± .005 4 PL DEC± .0005 ANGLES ± 1°				SCALE: 3:2	

OMNETICS
CONNECTOR CORPORATION
7260 COMMERCE CIRCLE EAST
MINNEAPOLIS, MN 55432
WWW.OMNETICS.COM