



## Pan-Term® BSN14-C Butt Splice, Blue, Nylon, 14-16 AWG, PK100

BSN14-C

Panduit BSN14-C Nylon Insulated Butt Splice

### Specifications

Product Type	Butt Splice
Base Material	Copper
Barrel Type	Standard
Finish/Coating	Tin-Plated
Copper Conductor Size	16-14 AWG
Maximum Metric Conductor Size (mm <sup>2</sup> )	2.5
Minimum Metric Conductor Size (mm <sup>2</sup> )	1.5
Maximum Wire Insulation Diameter (In.)	1.15
Maximum Wire Insulation Diameter (mm)	29.21
Insulation Material	Nylon
Overall Length (In.)	1.15
Overall Length (mm)	29.2
Overall Width (In.)	0.2
Overall Width (mm)	5.1
Standards Met	UL 486C, CSA C22.2 No.65
UL Temperature Rating (°C)	150
UL Temperature Rating (°F)	221
CSA Temperature Rating (°C)	150
CSA Temperature Rating (°F)	221
Maximum Voltage (V)	600
Maximum Voltage (kV)	0.6
Color Code	Blue
Wire Strip Length (In.)	9/32
Wire Strip Length (mm)	7.1
For Use With	CT-310
Sub Brand	Pan-Term®
Part Features	<ul style="list-style-type: none"> <li>• Designed to splice two solid or stranded wires together to repair or lengthen wires</li> <li>• Butted configuration provides low profile for limited space applications</li> <li>• Internal wire stop assures proper length of insertion into terminal barrel</li> </ul>

**Packaging Detail**

UPC	07498383002
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0099
Std. Ctn. Qty.	1000
Std. Ctn. Volume (cf)	0.0985