



Dome-Top® BT2M-C Barb Tie, PA6.6, 7.9"L, 18lb, PK100

BT2M-C

The BT2M-C Dome-Top® barb tie, features a unique patented design with its round smooth edges. Paired with the stainless-steel locking barb, these cable ties provide consistent performance, reliability and infinite adjustability through the entire bundle range. Miniature cross section, 7.9" (201mm) length. Appropriate for Indoor use, made of Nylon 6.6, are natural in color and come in packages of 100.

Specifications

Material Description	Nylon 6.6
Product Type	Cable Tie
Sub Brand	Dome-Top®
Color	Natural
Environment	Indoor
Material	Nylon 6.6
Overall Length (In.)	7.9
Overall Length (mm)	201
Body Width (In.)	0.095
Body Width (mm)	2.4
Body Thickness (In.)	0.046
Body Thickness (mm)	1.2
Maximum Bundle Diameter (In.)	2
Maximum Bundle Diameter (mm)	51
Minimum Bundle Diameter (In.)	0.06
Minimum Bundle Diameter (mm)	1.5
Minimum Loop Tensile Strength (N)	80
Minimum Loop Tensile Strength (lb)	18
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Minimum Installation Temperature (°C)	-20
Minimum Installation Temperature (°F)	-4
Standards Met	UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC 10CFR50, QPL-AS23190, CSA Certified, RoHS Compliant
For Use With	GTS-E, GS2B-E, PTS, PPTS, STS2

Specifications (continued)

Part Features	High strength and low thread force
---------------	------------------------------------

Packaging Detail

UPC	07498360285
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0237
Std. Ctn. Qty.	1000
Std. Ctn. Volume (cf)	0.2370