


Vishay High Power Products

HEXFRED® Ultrafast Soft Recovery Diode, 8 A



TO-220AC

PRODUCT SUMMARY				
V _R	600 V			
V _F at 8 A at 25 °C	1.7 V			
I _{F(AV)}	8 A			
t _{rr} (typical)	18 ns			
T _J (maximum)	150 °C			
Q _{rr} (typical)	65 nC			
dI _{(rec)M} /dt (typical)	240 A/μs			
I _{RRM}	5.0 A			

FEATURES

- Ultrafast recovery
- · Ultrasoft recovery
- Very low I_{RRM}
- Very low Q_{rr}
- · Specified at operating conditions
- · Designed and qualified for industrial level

BENEFITS

- · Reduced RFI and EMI
- · Reduced power loss in diode and switching transistor
- · Higher frequency operation
- · Reduced snubbing
- · Reduced parts count

DESCRIPTION

HFA08TB60 is a state of the art ultrafast recovery diode. Employing the latest in epitaxial construction and advanced processing techniques it features a superb combination of characteristics which result in performance which is unsurpassed by any rectifier previously available. With basic ratings of 600 V and 8 A continuous current, the HFA08TB60 is especially well suited for use as the companion diode for IGBTs and MOSFETs. In addition to ultrafast recovery time, the HEXFRED® product line features extremely low values of peak recovery current (IRRM) and does not exhibit any tendency to "snap-off" during the t_b portion of recovery. The HEXFRED features combine to offer designers a rectifier with lower noise and significantly lower switching losses in both the diode and the switching transistor. These HEXFRED advantages can help to significantly reduce snubbing, component count and heatsink sizes. The HEXFRED HFA08TB60 is ideally suited for applications in power supplies and power conversion systems (such as inverters), motor drives, and many other similar applications where high speed, high efficiency is needed.

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS	
Cathode to anode voltage	V_R		600	V	
Maximum continuous forward current	l _F	T _C = 100 °C	8.0		
Single pulse forward current	I _{FSM}		60	Α	
Maximum repetitive forward current	I _{FRM}		24		
Maximum power dissipation	P_D	T _C = 25 °C	36	W	
Maximum power dissipation		T _C = 100 °C	14	VV	
Operating junction and storage temperature range	T _J , T _{Stg}		- 55 to + 150	°C	

HFA08TB60

Vishay High Power Products





Document Number: 93044 Revision: 30-Jul-08

ELECTRICAL SPECIFICATIONS (T _J = 25 °C unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNITS
Cathode to anode breakdown voltage	V _{BR}	Ι _R = 100 μΑ		600	-	-	
		I _F = 8.0 A		-	1.4	1.7	V
Maximum forward voltage V _{FM}	I _F = 16 A	See fig. 1	-	1.7	2.1		
		I _F = 8.0 A, T _J = 125 °C		-	1.4	1.7	
Maximum reverse		$V_R = V_R$ rated	See fig. 2	-	0.3	5.0	
leakage current	I _{RM}	$T_J = 125 ^{\circ}\text{C}, V_R = 0.8 \text{x} V_R \text{rated}$	See lig. 2	-	100	500	μΑ
Junction capacitance	C _T	V _R = 200 V	See fig. 3	=	10	25	pF
Series inductance	L _S	Measured lead to lead 5 mm from package body		-	8.0	-	nH

DYNAMIC RECOVERY CHARACTERISTICS (T _J = 25 °C unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNITS
	t _{rr}	$I_F = 1.0 \text{ A}, \text{ d}I_F/\text{d}t = 200 \text{ A}/\mu\text{s}, \text{ V}_R = 30 \text{ V}$		-	18	-	ns
Reverse recovery time	t _{rr1}	t _{rr1} T _J = 25 °C	-	37	55		
	t _{rr2}	T _J = 125 °C	I _F = 8.0 A dI _F /dt = 200 A/μs V _R = 200 V	-	55	90	
Peak recovery current	I _{RRM1}	T _J = 25 °C		-	3.5	5.0	Α
	I _{RRM2}	T _J = 125 °C		-	4.5	8.0	
Reverse recovery charge	Q _{rr1}	T _J = 25 °C		-	65	138	nC
neverse recovery charge	Q _{rr2}	T _J = 125 °C		-	124	360	110
Peak rate of fall of recovery current during t _b	dI _{(rec)M} /dt1	T _J = 25 °C		-	240	-	- A/μs
	dI _{(rec)M} /dt2	T _J = 125 °C		-	210	-	

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Lead temperature	T _{lead}	0.063" from case (1.6 mm) for 10 s	-	-	300	°C
Thermal resistance, junction to case	R _{thJC}		-	-	3.5	
Thermal resistance, junction to ambient	R _{thJA}	Typical socket mount	-	-	80	K/W
Thermal resistance, case to heatsink	R _{thCS}	Mounting surface, flat, smooth and greased	-	0.5	-	
Weight			-	2.0	-	g
vveigni			-	0.07	-	OZ.
Mounting torque			6.0 (5.0)	-	12 (10)	kgf · cm (lbf · in)
Marking device		Case style TO-220AC	HFA08TB60			



HEXFRED® Vishay High Power Products Ultrafast Soft Recovery Diode, 8 A




Fig. 1 - Maximum Forward Voltage Drop vs. Instantaneous Forward Current




Fig. 2 - Typical Reverse Current vs. Reverse Voltage




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics

Vishay High Power Products

HEXFRED® Ultrafast Soft Recovery Diode, 8 A






Fig. 5 - Typical Reverse Recovery Time vs. dI_F/dt




Fig. 7 - Typical Stored Charge vs. dl_F/dt




Fig. 6 - Typical Recovery Current vs. dI_F/dt




Fig. 8 - Typical $dl_{(rec)M}/dt$ vs. dl_F/dt



HEXFRED® Vishay High Power Products Ultrafast Soft Recovery Diode, 8 A





Fig. 9 - Reverse Recovery Parameter Test Circuit



- (1) dl_F/dt rate of change of current through zero crossing
- (2) I_{RRM} peak reverse recovery current
- (3) t_{rr} reverse recovery time measured from zero crossing point of negative going I_F to point where a line passing through 0.75 I_{RRM} and 0.50 I_{RRM} extrapolated to zero current.
- (4) $\mathbf{Q}_{\rm rr}$ area under curve defined by $\mathbf{t}_{\rm rr}$ and $\mathbf{I}_{\rm RRM}$

$$Q_{rr} = \frac{t_{rr} \times I_{RRM}}{2}$$

(5) dI_{(rec)M}/dt - peak rate of change of current during t_b portion of t_{rr}

Fig. 10 - Reverse Recovery Waveform and Definitions

LINKS TO RELATED DOCUMENTS					
Dimensions http://www.vishay.com/doc?95221					
Part marking information	http://www.vishay.com/doc?95224				



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Revision: 18-Jul-08

Document Number: 91000 www.vishay.com