International

SCHOTTKY RECTIFIER

Major Ratings and Characteristics

MBRD650CT MBRD660CT

6 Amp

I_{F(AV)} = 6.0Amp V_R = 50-60V

Units Characteristics Values I_{F(AV)} Rectangular 6 А waveform 50-60 V V_{RRM} I_{FSM} @ tp = 5 µs sine 490 А @3Apk, $T_J = 125^{\circ}C$ V_F 0.65 V (per leg) -40 to 150 °C T_J range

Description/ Features

The MBRD650CT, MBRD660CT surface mount, center tap, Schottky rectifier series has been designed for applications requiring low forward drop and small foot prints on PC board. Typical applications are in disk drives, switching power supplies, converters, free-wheeling diodes, battery charging, and reverse battery protection.

- Popular D-PAK outline
- Center tap configuration
- Small foot print, surface mountable
- Low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability



MBRD650CT, MBRD660CT

Bulletin PD-20755 rev. E 05/06

International **tor** Rectifier

Voltage Ratings

Part number	MBRD650CT	MBRD660CT
V _R Max. DC Reverse Voltage (V)	50	60
V _{RWM} Max. Working Peak Reverse Voltage (V)		

Absolute Maximum Ratings

	Parameters	Value	Units	Conditions	
I _{E(AV)}	Max. Average Forward (Per Leg)	3.0	A	50% duty cycle @ T _c = 128°C, r	ectangular wave form
	Current * See Fig. 5 (Per Device)	6		-	
I _{FSM}	Max. Peak One Cycle Non-Repetitive	490	Α	5µs Sine or 3µs Rect. pulse	Following any rated load condition and with
	Surge Current * See Fig. 7	75		10ms Sine or 6ms Rect. pulse	rated V _{RRM} applied
E _{AS}	Non-Repet. Aval. Energy (Per Leg)	6	mJ	$T_{J} = 25 \text{ °C}, I_{AS} = 1 \text{ Amp}, L = 12 \text{ mH}$	
I _{AR}	Repetitive Avalanche Current	0.6	A	Current decaying linearly to zero in 1 µsec	
	(PerLeg)			Frequency limited by $T_J max. V_j$	= 1.5 x V _R typical

Electrical Specifications

	Parameters	Value	Units	Conditions	
V _{FM}	Max. Forward Voltage Drop	0.7	V	\bigcirc 3A $T_1 = 25 °C$	
	(Per Leg) * See Fig. 1 (1)	0.9	V	@ 6A	
		0.65	V	@ 3A T = 125 °C	
		0.85	V	@ 6A T _J = 125 °C	
I _{RM}	Max. Reverse Leakage Current	0.1	mA	$T_J = 25 \text{ °C}$ $V_p = \text{rated } V_p$	
	(Per Leg) * See Fig. 2 (1)	15	mA	$T_J = 125 \text{ °C}$	
CT	Typ. Junction Capacitance (Per Leg)	145	pF	V_R = 5V _{DC} (test signal range 100Khz to 1Mhz) 25°C	
L _S	Typical Series Inductance (Per Leg)	5.0	nH	Measured lead to lead 5mm from package body	
dv/dt	Max. Voltage Rate of Change	10000	V/µs	(Rated V _R)	

(1) Pulse Width < 300µs, Duty Cycle <2%

Thermal-Mechanical Specifications


	Parameters		Value	Units	Conditions
TJ	Max. Junction Temperatur	eRange (*)	-40 to 150	°C	
T _{stg}	Max. Storage Temperature	e Range	-40 to 150	°C	
R_{thJC}	Max. Thermal Resistance	(PerLeg)	6	°C/W	DC operation * See Fig. 4
	Junction to Case	(Per Device)	3		
R _{thJA}	Max. Thermal Resistance J	unction	80	°C/W	
	to Ambient				
wt	Approximate Weight		0.3 (0.01)	g(oz.)	
	Case Style		D-Pa	k	Similar to TO-252AA
	Device Marking		MBRD66	50CT	

 $\frac{(^{*})}{dTj} \frac{dPtot}{dTj} < \frac{1}{Rth(j-a)} \quad \text{thermal runaway condition for a diode on its own heatsink}$

Document Number: 93463

International

MBRD650CT, MBRD660CT Bulletin PD-20755 rev. E 05/06



Document Number: 93463

www.vishay.com 3






Fig. 7 - Max. Non-Repetitive Surge Current (Per Leg)

www.vishay.com 4

Outline Table L3 & b3 ES MOLD FLASH SHALL NOT EXCEED .005 [0.13] F BASE WETAL ONLY. D AT DATUM PLANE H. TUNE TO-252AA. NOTATED BOT CH SCALE 201 N C €S .094 .095 .035 .031 .045 .024 .022 .035 .245 .245 .265 MAx, 2.39 0.13 0.89 0.79 1.14 5.46 0.61 0.56 0.89 6.22 -6.73 Vill, 2,18 -0,64 0,65 0,76 4,95 0,46 0,41 0,46 5,97 5,21 6,35 4,32 2,29 9,40 Min. .086 -.025 .025 .030 .195 .018 .018 .235 .205 .250 .170 L A A1 b b b b b c c1 c2 D D1 E E1 e H L L1 L2 L3 L4 L5 e e1 e2 7 LEAD AS 6 4 6 HEXFET 1.- GATE 2.- DRAIN 3.- SOURC 4.- DRAIN 10.4 1.40 2.74 0.51 0.89 -1.14 0' 0' 25' 1,78 BSC 1.27 1.02 1.52 10° 15° 35° .02 .035 -.045 0 0 25 .050 .040 .060 10* 15* IGBT & Col 由 Ð 2.- COLLECTOR 3.- EMITTER 4 - COLLECTOR Modified JEDEC outline TO-252AA Dimensions in millimeters and (inches)

Part Marking Information





Tape & Reel Information

Device Code	MBR D 6 60 CT TR -
	1 2 3 4 5 6 7
	 Schottky MBR Series D = D-Pak (TO-252AA) Currrent Rating (6 = 6A) Voltage Ratings Voltage Ratings CT = Center Tap (Dual) • none = Tube (50 pieces) • TR = Tape & Reel • TRL = Tape & Reel (Left Oriented) • TRR = Tape & Reel (Right Oriented) • TRR = Tape & Reel (Right Oriented) • PbF = Lead-Free

Ordering Information Table

Data and specifications subject to change without notice. This product has been designed and qualified for AEC Q101 Level. Qualification Standards can be found on IR's Web site.

International

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105 TAC Fax: (310) 252-7309 05/06

> www.vishay.com 7

Document Number: 93463



Vishay

Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier[®], IR[®], the IR logo, HEXFET[®], HEXSense[®], HEXDIP[®], DOL[®], INTERO[®], and POWIRTRAIN[®] are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.