

Vishay Semiconductors


# Schottky Rectifier, 2 x 40 A

Base

cathode

cathode


Anode





PRODUCT SUMMARY						
Package	TO-247AC					
I <sub>F(AV)</sub>	2 x 40 A					
V <sub>R</sub>	150 V					
V <sub>F</sub> at I <sub>F</sub>	0.71 V					
I <sub>RM</sub> max.	26 mA at 125 °C					
T <sub>J</sub> max.	175 °C					
Diode variation	Common cathode					
E <sub>AS</sub>	0.5 mJ					

#### **FEATURES**

- 175 °C T<sub>J</sub> operation
- · Low forward voltage drop
- · High frequency operation







· Material categorization: For definitions of compliance please see www.vishay.com/doc?99912







### **DESCRIPTION**

The VS-80CPQ150... center tap Schottky rectifier series has been optimized for low reverse leakage at high temperature. The proprietary barrier technology allows for reliable operation up to 175 °C junction temperature. Typical applications are in switching power supplies, converters freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS								
SYMBOL	CHARACTERISTICS VALUES UNITS							
I <sub>F(AV)</sub>	Rectangular waveform	80	A					
V <sub>RRM</sub>		150	V					
I <sub>FSM</sub>	t <sub>p</sub> = 5 μs sine	1930	A					
V <sub>F</sub>	40 A <sub>pk</sub> , T <sub>J</sub> = 125 °C (per leg)	0.71	V					
TJ		- 55 to 175	°C					

VOLTAGE RATINGS						
PARAMETER	SYMBOL	VS-80CPQ150PbF	VS-80CPQ150-N3	UNITS		
Maximum DC reverse voltage	V <sub>R</sub>	150	150	V		
Maximum working peak reverse voltage	$V_{RWM}$	150	150	V		

ABSOLUTE MAXIMUM RATINGS						
PARAMETER		SYMBOL	TEST CONDI	VALUES	UNITS	
Maximum average per leg			50.0/ dutu analy at T = 150.00 market and an area from		40	
See fig. 5	per device	I <sub>F(AV)</sub>	50 % duty cycle at T <sub>C</sub> = 150 °C, rectangular waveform		80	А
Maximum peak one cycle non-repetitive surge current per leg See fig. 7			5 μs sine or 3 μs rect. pulse	Following any rated load condition and with	1930	
		I <sub>FSM</sub>	10 ms sine or 6 ms rect. pulse	rated V <sub>RRM</sub> applied	500	
Non-repetitive avalanche energy per leg		E <sub>AS</sub>	T <sub>J</sub> = 25 °C, I <sub>AS</sub> = 1.0 A, L = 1 mH		0.5	mJ
Repetitive avalanche current per leg		I <sub>AR</sub>	Current decaying linearly to zero Frequency limited by T <sub>J</sub> maximu		1.0	Α



# VS-80CPQ150PbF, VS-80CPQ150-N3

# Vishay Semiconductors

ELECTRICAL SPECIFICATIONS							
PARAMETER	SYMBOL	TEST CONDITIONS		TYP.	MAX.	UNITS	
		40 A	T <sub>.1</sub> = 25 °C	0.82	0.86		
Maximum forward	V <sub>FM</sub> <sup>(1)</sup>	80 A	1] = 25 0	0.97	1.09	V	
voltage drop per leg See fig. 1	VFM (*)	40 A	- T <sub>J</sub> = 125 °C	0.67	0.71		
		80 A		0.80	0.85		
Maximum reverse leakage current per leg		T <sub>J</sub> = 25 °C	V Detect V	10	200	μΑ	
See fig. 2	I <sub>RM</sub>	T <sub>J</sub> = 125 °C	V <sub>R</sub> = Rated V <sub>R</sub>	12	26	mA	
Typical junction capacitance per leg	C <sub>T</sub>	$V_R = 5 V_{DC}$ (test signal range 100 kHz to 1 MHz) 25 °C		-	1100	pF	
Typical series inductance per leg	L <sub>S</sub>	Measured lead to lead 5 r	-	7.5	nH		
Maximum voltage rate of change	dV/dt	Rated V <sub>R</sub>	-	10 000	V/µs		

#### Note

 $<sup>^{(1)}\,</sup>$  Pulse width < 300 µs, duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER		SYMBOL	SYMBOL TEST CONDITIONS		UNITS	
Maximum junction and st temperature range	torage	T <sub>J</sub> , T <sub>Stg</sub>		- 55 to 175	°C	
Maximum thermal resistation to case per leg	ance,	Б	DC operation See fig. 4	0.6		
Maximum thermal resistation to case per pack	*	R <sub>thJC</sub>	DC operation	0.3	°C/W	
Typical thermal resistant case to heatsink	e,	R <sub>thCS</sub>	Mounting surface, smooth and greased	0.24		
Approximate weight				6	g	
Approximate weight				0.21	oz.	
Mounting torque	minimum			6 (5)	kgf · cm	
	maximum			12 (10)	(lbf ⋅ in)	
Marking device			Case style TO-247AC (JEDEC)	80CP	Q150	

### www.vishay.com

### Vishay Semiconductors




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics (Per Leg)



### www.vishay.com

## Vishay Semiconductors




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)




Fig. 8 - Unclamped Inductive Test Circuit

### Note


 $^{(1)}$  Formula used: T<sub>C</sub> = T<sub>J</sub> - (Pd + Pd<sub>REV</sub>) x R<sub>thJC</sub>; Pd = Forward power loss = I<sub>F(AV)</sub> x V<sub>FM</sub> at (I<sub>F(AV)</sub>/D) (see fig. 6); Pd<sub>REV</sub> = Inverse power loss = V<sub>R1</sub> x I<sub>R</sub> (1 - D); I<sub>R</sub> at V<sub>R1</sub> = 80 % rated V<sub>R</sub>

# VS-80CPQ150PbF, VS-80CPQ150-N3

Vishay Semiconductors

### **ORDERING INFORMATION TABLE**

**Device code** 



1 - Vishay Semiconductors product

- Current rating (80 = 80 A)

3 - Circuit configuration:

C = Common cathode

4 - Package:

P = TO-247

5 - Schottky "Q" series

6 - Voltage code (150 = 150 V)

7 - Environmental digit

• PbF = Lead (Pb)-free and RoHS compliant

• -N3 = Halogen-free, RoHS compliant, and totally lead (Pb)-free

ORDERING INFORMATION (Example)							
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION				
VS-80CPQ150PbF	25	500	Antistatic plastic tube				
VS-80CPQ150-N3	25	500	Antistatic plastic tube				


LINKS TO RELATED DOCUMENTS						
Dimensions <u>www.vishay.com/doc?95542</u>						
Dort marking information	TO-247AC PbF	www.vishay.com/doc?95226				
Part marking information	TO-247AC -N3	www.vishay.com/doc?95007				



Vishay Semiconductors

### TO-247AC - 50 mils L/F

### **DIMENSIONS** in millimeters and inches



SYMBOL	MILLIM	IETERS	INC	HES	NOTES
STWIDOL	MIN.	MAX.	MIN.	MAX.	NOTES
Α	4.65	5.31	0.183	0.209	
A1	2.21	2.59	0.087	0.102	
A2	1.17	1.37	0.046	0.054	
b	0.99	1.40	0.039	0.055	
b1	0.99	1.35	0.039	0.053	
b2	1.65	2.39	0.065	0.094	
b3	1.65	2.34	0.065	0.092	
b4	2.59	3.43	0.102	0.135	
b5	2.59	3.38	0.102	0.133	
С	0.38	0.89	0.015	0.035	
c1	0.38	0.84	0.015	0.033	
D	19.71	20.70	0.776	0.815	3
D1	13.08	-	0.515	-	4

SYMBOL	MILLIMETERS		INC	HES	NOTES
STWIDOL	MIN.	MAX.	MIN.	MAX.	NOTES
D2	0.51	1.35	0.020	0.053	
Е	15.29	15.87	0.602	0.625	3
E1	13.46	-	0.53	-	
е	5.46	BSC	0.215	BSC	
ØK	0.254		0.0	10	
L	14.20	16.10	0.559	0.634	
L1	3.71	4.29	0.146	0.169	
ØΡ	3.56	3.66	0.14	0.144	
Ø P1	-	7.39	-	0.291	
Q	5.31	5.69	0.209	0.224	
R	4.52	5.49	0.178	0.216	
S	5.51	BSC	0.217	BSC	

#### **Notes**

- (1) Dimensioning and tolerancing per ASME Y14.5M-1994
- (2) Contour of slot optional
- (3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- (5) Lead finish uncontrolled in L1
- (6) Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- $^{(7)}$  Outline conforms to JEDEC® outline TO-247 with exception of dimension c and Q



### **Legal Disclaimer Notice**

Vishay

### **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.