

WR/PG29-25M

Order No.: 1666854

The illustration shows the version WR/PG16-50M



http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1666854

Corrugated tube, for corrugated tube screw connection, packing volume 25 m, type Pg29

Commercial data	
EAN	4017918136901
Pack	1 pcs.
Customs tariff	39173900
Weight/Piece	3.00 KG
Catalog page information	Page 556 (PC-2009)

Product notes

WEEE/RoHS-compliant since: 01/01/2003



http://

www.download.phoenixcontact.com
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.


Technical data

General data

Pg screw connection	29
Material	PA
Inflammability class acc. to UL 94	НВ
Ambient temperature (operation)	-40 °C 110 °C

Diagrams/Drawings

Dimensioned drawing



Assembly instructions for Pg29 corrugated pipe


a = Corrugated screw connection

b = Corrugated pipe

c = Opener

Installation note:

Cut the corrugated pipe in the groove to retain a round shape for insertion. The lighter seal (not depicted in the illustration) is positioned in the corrugated pipe screw connection below the safety latch. The darker outer seal (not depicted in the illustration) is placed over the corrugated pipe screw connection from outside. The corrugated pipe is then pushed as far as possible into the corrugated pipe screw connection and clicks into place. The screw connection is opened by placing the yellow corrugated pipe opener with force between the safety latch and the corrugated tube and the corrugated pipe is then pulled out.



Assembly instructions for M32 corrugated pipe

a = Corrugated screw connection

B = Corrugated pipe

c = Opener

Installation note:

Cut the corrugated pipe in the groove to retain a round shape for insertion. The lighter seal (not depicted in the illustration) is positioned in the corrugated pipe screw connection below the safety latch. The darker outer seal (not depicted in the illustration) is placed over the corrugated pipe screw connection from outside. The corrugated pipe is then pushed as far as possible into the corrugated pipe screw connection and clicks into place. The screw connection is opened by placing the yellow corrugated pipe opener with force between the safety latch and the corrugated tube and the corrugated pipe is then pulled out.

Address

PHOENIX CONTACT Inc., USA 586 Fulling Mill Road Middletown, PA 17057,USA Phone (800) 888-7388 Fax (717) 944-1625 http://www.phoenixcon.com



© 2010 Phoenix Contact Technical modifications reserved;