



BRICKs

VI CHIP

PICOR

CONFIGURABLE PSUs

MIL-COTS

CUSTOM













# VICOR CORPORATION

### **Power Solutions**

Vicor's product line of modular power components and complete power systems includes thousands of combinations of input voltage, output voltage, and power levels, complete with accessory components that integrate other power system functions. Together, these products allow designers around the world to meet their unique power requirements by selecting and interconnecting standard modular parts. The benefits for you are rapid, flexible design of complete power systems at any power level.

If you don't find the converter you need from our thousands of predefined DC-DC converters, you can design your own custom product on the web using Vicor's PowerBench Design System. We offer a wide range of solutions with 1 - 20 outputs and autoranging, PFC, or three-phase inputs. There are several chassis sizes to choose from, both with and without integral cooling fans. Also available from Vicor is a strong offering of front ends and filters to complete your design. Our extensive MIL-COTS product line incorporates the technology and features of our commercial products into a cost-effective alternative for military, aerospace, and other high-reliability, harsh-environment applications. Standard inputs of 28, 48, 155, 270, and 375 Vdc are available.

Vicor is pioneering the second wave of the power component revolution with the introduction of flexible, high-performance power components. V•I Chip<sup>™</sup> Factorized Power Architecture provides the means to more efficient power distribution and the V•I Chips provide the building blocks with the right attributes of high density and efficiency, flexibility, and fast transient response that enable power architects to more easily design small, high-performance, cost-effective power system solutions. V•I Chip PRMs<sup>™</sup> (regulators), VTMs<sup>™</sup> (voltage transformers) and BCMs<sup>™</sup> (bus converters) are available for a wide range of DC-DC conversion and Intermediate Bus Architecture applications. MIL-COTS versions are also available.

New power options are available with Picor's first standard semiconductor solution – *Cool–ORing*<sup>™</sup> – that can substantially reduce power dissipation and size, while providing superior dynamic response for Active ORing applications in redundant power architectures. Another new option is the new modular power platform: VI BRICK. The new VI BRICK family is an advanced modular power platform that incorporates the superior technical attributes of V•I Chip technology and a robust packaging that facilitates thermal management and through-hole assembly. Models include high-current density / low-voltage DC-DC converters, a wide range of highly efficient bus converters (BCM), and individual modules – PRM and VTM – for both regulation and transformation.

Vicor Custom Power provides complete power solutions for communications, industrial, datacom, test equipment, medical diagnostics, and MIL-COTS. Using the extensive Vicor line of DC-DC converters in a modular, building-block design approach, Custom Power offers total solutions to unique power requirements in the shortest possible time.

All our products deliver agency-approved reliability and the predictable performance of field-proven power technology, including conformance to RoHS if desired. Vicor is ISO 9001:2000 certified and places heavy emphasis on the "Plan-Do-Check-Act" model (PDCA) to foster continuous improvement. This enables proactive actions to be undertaken to improve our technology, our products, our processes, and our service to our customers. Our new <u>Quality Center on vicorpower.com</u> enables quality managers, purchasing agents, and designers to see comprehensive video of our facilities as well as generate customized ISO 9001:2000 reports about our quality systems.

Be assured that Vicor is on a continuous quest for the best technical solution for you. Moreover, our commitment to the elegance and affordability of your design is backed up by our global staff of experienced applications engineers. Rely on Vicor as your dedicated design partner.



#### TABLE OF CONTENTS

Product Overview Chart	2 – 3
DC-DC V•I Chip <sup>™</sup> Advantage Power Conversions Using PRM, VTM & BCMs Bus Converter (BCM <sup>™</sup> ) Regulator (PRM <sup>™</sup> ) Voltage Transformer (VTM <sup>™</sup> )	
VI BRICKs PRM, VTM, BCM & DC-DC Converter	
DC-DC BRICKs	12 – 13
Power Path Management Solutions Cool-ORing <sup>™</sup> Series	
AC-DC Front Ends Harmonic Attenuator Module (HAM) AC-DC / DC-DC PFC FrontEnd Alternating Input Module (AIM) Autoranging Rectifier Module (ARM) Filter / Autoranging Rectifier Module (FARM) Modular AC Front-end System (ENMods)	
Brick BatMod Battery Charger Packaging Options	23
Filters Filter Input Attenuator Module (FIAM) Input Attenuator Module (IAM) Ripple Attenuator Module (RAM) Output Ripple Attenuator Module (MicroRAM) Active EMI Filters (QPI Family) Output Ripple Attenuators (QPO Family)	
AC-DC / DC-DC Configurable Power Solutions AC-DC FlatPAC Family AC-DC PFC FlatPAC AC-DC VIPAC Power System DC-DC VIPAC Arrays DC-DC ComPAC Family DC-DC MegaMod Family	
MIL-COTS Products	34 – 37
Westcor Configurable Power Solutions AC-DC / DC-DC LoPAC Family AC-DC / DC-DC FlatPAC-EN AC-DC / DC-DC MegaPAC Family DC-DC (only) ConverterPACs	
Custom Power Solutions	. 42 – 43
Custom Configurable Power Solutions DC-DC MegaPAC VME450 DC-DC Power Supply Badger AC-DC Power Supply Javelin AC-DC Power Supply PowerBank AC-DC Power Supply	44 44 45 45
Evaluation Boards	. 46 – 47
Accessories	. 48 – 52
Quality / RoHS Compliance	53
Vicorpower.com Technical	
PowerBench Tools	
Applications Support	
Customer Support	

# WHAT'S NEW

Vicor develops new products all the time, so, to keep everyone up-to-date, we've created a special area on vicorpower.com where you can always see "what's new." Just go to vicorpower.com and click on "What's New." It will take you to our new products page. From there you'll be able to link to detailed design information.

## Web ExpressCode

### Web ExpressCode provides quick access to detailed product information

Each product description in the Vicor catalog includes a unique Web ExpressCode. Each code provides direct access to the corresponding, information rich product pages on vicorpower.com. Just enter the Web ExpressCode into the Web ExpressCode search box on vicorpower.com's homepage. You'll be sent to the exact page you want with access to all related information such as product description, operating specifications, access to data sheets, outline drawings, and product configuration tools.



## PowerBench<sup>™</sup> You Design It ,We Build It

PowerBench is the most advanced suite of online power tools available. They can help you design, select and configure products whether you are just beginning or experienced in designing power, PowerBench can take you from beginning to end of any power project. All of this in real time.

See for yourself what Vicor can do for you on <u>Page 55</u> or go to the Vicor website, click PowerBench and start building.

RBENCH




Consult back cover for a complete list of contacts.

# **OVERVIEW**

#### V•I Chip & VI BRICK Solutions **DC-DC Products Bus Converter** 330 – 365 Vin BCM 10.3 - 11.4 Vdc, Up to 300 W; 41.25 - 45.6 Vdc, Up to 300 W **Bus Converter** 360 – 400 Vin \_ \_\_\_\_ всм 11.2 - 12.5 Vdc, Up to 300 W; 45 - 50 Vdc, Up to 330 W **Bus Converter** 38 – 55 Vin 1.2 – 55 V, Up to 300 W Regulator 38 – 55 Vin -Up to 320 W Regulator 36 – 75 Vin Voltage Transformer 0.8 – 55 V Up to 240 W VTM Up to 100 A or 300 W Regulator 18 – 36 Vin Up to 120 W MIL-COTS MIL-COTS Voltage Transformer 1 – 50 V м-утм **MIL-COTS** Regulator Up to 100 A or 120 W MQPI 16 – 50 Vin M-PRN Active ORing: (12 V bus or lower) Up to 120 W Active ORing: (48 V bus or lower) Discrete Controller **Discrete Controller & Full-Function** EMI Filter Solutions 24 Vdc. 48 Vdc QPI Hot-Swap Controller **Component Power Solutions: VI-200 & VI-J00 Series AC-DC Products DC-DC Products** Harmonic Attenuator Module DC-DC Converter Universal Unity Power Factor VI-200 / MI-200 85 – 264 Vac Up to 675 W per module 25 – 200 W per module – 95 Vdc More Power? Add a Booster. Output Ripple Attenuation Module Rectifier / EMI Filter Universal AIM / MI-AIM combines active and passive filtering. 85 - 264 Vac Up to 250 W RAM Autoranging 90 – 132 Vac 180 – 264 Vac Filter / Autoranging Rectifier Module VI-200 / MI-200 Up to 1,000 W QPO provides active filtering QPO Another Output? Add a Driver. to achieve differential noise Autoranging 90 – 132 Vac 180 – 264 Vac attenuation. Autoranging Rectifier Module ARM Up to 1.500 W Programmable Current Source BatMod


#### **DC-DC Products**

Consult back cover for a complete list of contacts.



#### Component Power Solutions: Maxi, Mini, Micro & VI BRICK Series AC-DC Products **DC-DC Products** Harmonic Attenuator Module Unity Power Factor HAM High-Bo **DC-DC** Converter Universal Single wire paralleling for 85 - 264 Vac Up to 675 W per module high power, fault tolerant arrays. ΜΑΧΙ Autoranging 90 – 132 Vac 180 – 264 Vac Filter / Autoranging Rectifier Module FARM Up to 600 W per module 1 – 54 Vdc Up to 1,000 W **Output Ripple Attenuation DC-DC** Converter Autoranging 90 – 132 Vac 180 – 264 Vac Module combines active and passive filtering. Autoranging Rectifier Module ARM Up to 1,500 W MIN Front-end System Autoranging 115 – 230 Vac Input QPO provides active filtering for EN Compliance Up to 300 W per module 1 – 48 Vdc QPO to achieve differential noise Up to 550 W attenuation. DC-DC Converter **DC-DC Products** MICRO Nominal Input 10 – 425 Vdc Up to 150 W per module 1 – 48 Vdc Transient Protection, Inrush Current Limiting EMI Filter FIAM / M-FIAM 28, 48, 270 Vdc = Up to 25 A VI BRICK Active ORing: (48 V bus or lower) Active ORing: (12 V bus or lower) Discrete Controller & Full-Function Active EMI Filter Discrete Controller Up to 220 W per module 1 – 48 Vdc 24, 28, 48 Vdc QPI Up to 576 W @ 48 V Solutions U.S. & CANADA: 800-735-6200 VICORPOWER.COM 2

## **OVERVIEW**



Consult back cover for a complete list of contacts.

# VI CHIP SOLUTIONS

#### 48 V BCM<sup>™</sup> Bus Converter



- ZVS / ZCS isolated Sine Amplitude Converter
- Input: 38 55 Vdc
- Output: Eleven models, 1.5 to 48 V
- Power: Up to 300 W (450 W for 1 ms)
- Efficiency: Up to 96.5%
- High density: Up to 1,036 W/in<sup>3</sup> (68 W/cm3)
- Small footprint: 1.1 in<sup>2</sup> (7.1 cm<sup>2</sup>)
- 125°C operation (Tj)
- Low weight: 0.5 oz (15 g)
- >3.5 million hours MTBF
- Low noise: No output filtering required
- J-Lead package pick & place / SMD compatible
- Through-hole pin option, full size

### High Voltage BCM Bus Converter

page 5



- ZVS / ZCS isolated Sine Amplitude Converter
- 330 365 Vdc to 11 Vdc @ 300 W
- 360 400 Vdc to 12 Vdc @ 300 W
- Efficiency: Up to 97%
- High density: Up to 1,034 W/in<sup>3</sup>
- Small footprint: 1.1 in<sup>2</sup> (7.1 cm<sup>2</sup>)
- 125°C operation (Tj)
- Isolation to 4,242 Vdc
- >2.6 million hours MTBF
- Low noise: No output filtering required
- Low weight: 0.5 oz (15 g)
- J-Lead package pick & place / SMD compatible
- Through-hole pin option





- 48 Vin ZVS buck / boost regulator
- Input: 36 - 75 Vdc or 38 - 55 Vdc
- Provides 26 55 Vdc output factorized bus for 48 Vin VTMs
- Efficiency: Up to 97%
- High density: Up to 1,105 W/in<sup>3</sup> (55 W/cm<sup>3</sup>)
- Small footprint: 1.1 in<sup>2</sup> (7.1 cm<sup>2</sup>)
- 125°C operation (Tj)
- Low weight: 0.5 oz (15 g)
- J-Lead package pick & place / SMD compatible
- Through-hole pin option

#### 24 V PRM Regulator



- 24 Vin ZVS buck / boost regulator
- Input: 18 36 Vdc
- Provides 26 55 Vdc output factorized bus for 48 Vin VTMs
- Efficiency: Up to 95%
- High density: Up to 414 W/in<sup>3</sup> (25 W/cm3)
- Small footprint: 1.1 in<sup>2</sup> (7.1 cm<sup>2</sup>)
- 125°C operation (Tj)
- Low weight: 0.5 oz (15 g)
- J-Lead package pick & place / SMD compatible
- Through-hole pin option

#### **VI BRICK**

Thermally enhanced packaging option available for PRM, VTM, BCM, Page 8 - 10



#### **VTM**<sup>™</sup> Voltage Transformer





RoHS

MIL-COTS Version **Available** Page 34

- 48 Vin Sine Amplitude Converter
- 26 55 Vdc input range
- 0.8 55 Vdc outputs
- Efficiency: Up to 97%
- High density: Up to 345 A/in<sup>3</sup>
- Up to 100 A or 300 W
- Small footprint: Up to 90 A/in<sup>2</sup>
- 125°C operation (Tj)
- Low weight: 0.5 oz (15 g)
- Isolation to 2,250 Vdc
- <1 µs transient response
- Low noise: No output filtering required
- J-Lead package pick & place / SMD compatible
- Through-hole pin option

#### **QPI for V-I Chips** Input Filter Module



- Support EN55022, Class B limits
- Compatible with 48 and 24 V V•I Chips
- Efficiency: >99%
- Up to 65 dB CM attenuation at 1 MHz
- Up to 80 dB DM attenuation at 1 MHz
- 7 A models, parallelable for up to 14 A
- Hot-Swap models available
- Supports AdvancedTCA® PICMG3.0 requirements
- 12,5 x 25 x 4,5 mm LGA package
- 25 x 25 x 4,5 mm package for Hot-Swap models

#### **Evaluation Boards Available**

Page 46





Version <u>Available</u>

page 6 MIL-COTS

page 6

Page 34

# **BRICK SOLUTIONS**

#### VI-200 / VI-J00 DC-DC Converter



- Input voltage ranges: 10 400 Vdc
- Output voltages: 1 95 Vdc
- Output power (per module): VI-200: 50 - 200 W • VI-J00: 25 - 100 W
- Parallelable for higher power
- 100°C operation: 85°C for VI-200
- Efficiency: Up to 90%
- Agency approvals: CE Marked cULus, cTÜVus

#### VI BRICK DC-DC Converter



- Input range: 36 75 Vdc
- Efficiency: Up to 93%
- Output voltages: 1 48 V
- Fast dynamic response
- Low noise
- Maximum case temperature: 100°C, no derating

#### **Front-end Modules**



- Up to 1,000 W power output
- 85 264 Vac input
- Efficiency: 90 98%
- Agency approvals: CE Marked, cTÜVus, cULus
- Operating temperature: -55°C to +100°C
- Inrush current limiting

#### Maxi / Mini / Micro DC-DC Converter





- Input voltages: 24, 28, 48, 72, 110, 150, 300, 375 Vdc
- Output power: 50 600 W
- 100°C, no derating
- High efficiency
- Low-noise ZCS / ZVS
- High power density: Up to 120 W/in<sup>3</sup>

#### **QPI Family** Active EMI Input Filters



- Up to 60 dB CM attenuation at 250 kHz

page 11

- DC-DC converters

#### **Input Filter Modules**



- 24, 48 and 300 V models
- Efficiency: Up to 98%
- Agency approvals: CE Marked, cTÜVus, cULus
- Operating temperature: -55°C to +100°C
- Designed to meet EN Class B, Bellcore and FCC transient and immunity

#### VI BRICK PRM / VTM / BCM



- Brick solution for Factorized Power
- Thermally enhanced package -baseplate and through-hole pin
- 100°C baseplate operation
- Small footprint: 2.08 in<sup>2</sup>
- Low profile: 0.37 inches above board
- Efficiency: Up to 97%
- High power density: Up to 390 W/in<sup>3</sup>

#### **QPO Family** Active Output Ripple Attenuators



- >30 dB PARD attenuation, 1 kHz to 500 kHz
- 3 30 Vdc and 0.3 5.5 Vdc input models
- Up to 20 A
- Supports precise point-of-load regulation
- Reduces required number of output capacitors to support dynamic loads
- Selectable optimization of attenuation, power dissipation, transient load response
- Compatible with most industry standard DC-DC converters

#### **Output Filter Modules**



- 5 50 V, Up to 20 A
- 3 30 V, Up to 30 A
- Efficiency: Up to 98%
- Up to 40 dB attenuation from 60 Hz to 1 MHz
- Operating temperature: -55°C to +100°C





- QuietPower™
- Up to 80 dB DM attenuation at 250 kHz
- Up to 14 A
- Efficiency: >99% at full load
- High density, low profile LGA package
- Designed to support EN Class B
- Integrated Hot-Swap in select models
- Current rating supports ATCA® blades
- -40°C to +100°C PCB temperature
- Compatible with most industry standard

# PICOR SOLUTIONS

#### **Cool-ORing™ Series** Controllers



- Fast dynamic response
- 4 A gate discharge current
- Accurate MOSFET voltage sensing
- Overtemperature fault detection
- Adjustable reverse current blanking timer
- Withstands 100 V transients in low-side applications
- Master / Slave I/O for paralleling
- Active low-fault flag output
- Compatible with bricks and V-I Chips

### **Cool-ORing<sup>™</sup> Series** Full-Function

Solutions



- Combines a high-speed ORing MOSFET controller anda very low on-state resistance ORing MOSFET
- Integrated high-performance MOSFET
   Pl2121: 8 V, 24 A, 1.5 mΩ
   Pl2122: 7 V, 12 A, 6 mΩ (back-to-back MOSFET)
   Pl2123: 15 V, 15 A, 3 mΩ
   Pl2125: 30 V, 12 A, 5.5 mΩ
- Very small, high density optimized solution
- Fast dynamic response
- Accurate sensing capability
- Compatible with bricks and V•I Chips

## **CONFIGURABLE POWER SUPPLIES**

VIPAC AC-DC or DC-DC Power Solution



- Input voltage ranges: 115/230 Vac, 28 Vdc (MIL-COTS)
- Output voltages: 2 48 Vdc
- Output power: Up to 900 W
- Single, dual, or triple outputs
- Efficiency: 80 90%
- Local or remote control

#### ComPAC Input Power Solution



- Input voltages: 24, 48 and 300 Vdc
- Output voltages: 1 95 Vdc
- Efficiency: 80 90%
- Power density: Up to 10 W/in<sup>3</sup>
- Low-noise FM control
- ZCS / ZVS power architecture

#### VIPAC Arrays DC Input Power System



- Input voltages: 24, 300, Vdc
- Output voltages: 2 54 Vdc
- Output power: 50 650 W
- Array power: Up to 750 W
- Single, dual, triple or quad outputs
- Rugged, low profile, coldplate chassis
- High-temperature capability

#### MegaMod Chassis-mount Converter



- Input voltage range:
   10 400 Vdc
- Output voltages: 1 95 Vdc
- Output power: Up to 600 W
- Single, dual, or triple outputs
- Efficiency: 80 90%
- Low-noise ZCS power architecture

#### FlatPAC AC-DC Power Solution



- Input voltage: 115/230 Vac input, autoranging
- Output voltages: 1 95 Vdc
- Output power: 50 600 W
- Single, dual, or triple outputs
- Low-noise ZCS / ZVS power technology
- Agency approvals: CE Marked, cTÜVus, cULus

#### PFC FrontEnd 384 Vdc Output Front End



- Input voltage ranges:
   85 264 Vac and 100 380 Vdc
- Output power: Up to 2,200 W
- Up to 4 non-isolated outputs
- Operating temperature:
   -20°C to +45°C (full power)
- DIN rail mountable





## **CONFIGURABLE POWER SUPPLIES**

#### **PFC FlatPAC** Single-Output Power System

page 29

page 39



- Input voltage range: 85 – 264 Vac
- Output power: Up to 575 W
   2 54 Vdc
- High efficiency
- Current limit
- Remote sense

#### FlatPAC-EN AC-DC Power Solution



- Input voltage ranges:
   90 132 / 180 264 Vac
   250 380 Vdc
- Output voltages: 2 95 Vdc
- Output power: Up to 500 W
- Up to 4 user-specifiable outputs

#### Javelin<sup>™</sup> MIL-COTS Power Supply



- Input voltage ranges: 85 254 Vac (PFC) / 85 – 380 Vdc
- Output voltages: Single output 2, 3.3,
   5, 12, 15, 24, 28, 48 Vdc
- Output power: 600 5,400 W



LoPAC Family Switcher Power Supplies

- Input voltage ranges:
   85 264 Vac and 100 380 Vdc
- Output voltages: 2 95 Vdc (higher voltage available with series arrays)
- Output power: 25 1,500 W
- Up to 6 user-specifiable outputs
- Power density: Up to 11 W/in<sup>3</sup>

#### DC MegaPAC<sup>™</sup> Power Switcher

page 45



- Input voltage range: 12 72 Vdc
- Output voltages: 2 95 Vdc
- Output power: Up to 1,600 W
- Up to 16 outputs

#### **PowerBank<sup>™</sup>** Low Profile Supply



- Input voltage: 115/230 Vac
- Output voltages: 1.8 52 V
- Output power: 1000 W @ 230 Vac input, 800 W @ 115 Vac input
- Operating temperature: -20°C to +50°C

## CUSTOM SOLUTIONS Don't see what you need...

page 44

Vicor Custom Power can design and manufacture a power supply built to your unique specifications. We specialize in turnkey custom power systems for electronic equipment manufacturers in the datacom, telecom, industrial, test equipment, medical, information technology, and MIL-COTS markets.

Utilizing Vicor component power modules in a building-block design approach offers low cost, quick turnaround, and reliable performance.

For more information on custom solutions, see pages 42 – 43.

#### MegaPAC Family User-Configured



- Input voltage ranges:
   85 264 Vac and 100 380 Vdc
- Output voltage: 2 95 Vdc (higher voltage available with series arrays)
- Output power: 25 4,000 W
- Up to 20 outputs
- High power density

#### VME450<sup>™</sup> Single-slot Power Supply



- Vin max range: 18 36 Vdc
- Input power: 650 W
- Output power: 550 W
- Temperature: -40 to +85°C
- Low profile: 0.670 in. max. height
- Utilizes Vicor's V•I Chips

#### Badger<sup>™</sup> MIL-COTS Power Supply



- Input voltage ranges: 85 264 Vac and 100 – 380 Vdc
- Output power: Up to 1,800 W
- Up to 12 non-isolated outputs
- Operating temperature: -55°C to +65°C





page 40

page 44

### The V·I Chip<sup>™</sup> Advantage Density, Efficiency, Flexibility, & Speed

Vicor's V-I Chips, new families of integrated power components, give the power architect new ways to create small, cost-effective, high-performance power system solutions.

V-I Chips increase power system flexibility by separating or factorizing a DC-DC converter into two components. One component provides a regulation function (PRM<sup>\*\*</sup>), and another provides transformation and isolation (VTM<sup>™</sup> / BCM<sup>™</sup>). This allows the power system designer to select only the functions that are needed, where they are needed.



Regulator



Voltage Transformer



Transformation & Isolation




всм

**Bus Converter** 

### **DC-DC Conversion Using PRM & VTM**

System solution with low component count

- VTM isolation and transformation at the point of load
- PRM regulation can be collocated with or remote from the VTM
- Efficiency: Up to 93%
- High power density: Up to 517 W/in<sup>3</sup>




#### VI BRICKs PRM, VTM, BCM models available Baseplate with through-hole pins <u>Page 8 – 10</u>

### **Bus Conversion Using BCMs**

Enable dense IBA Power Systems

- High density bus converter > 1,000 W/in<sup>3</sup>
- Efficiency: Up to 96.5%
- Minimize total system capacitance



...little or no capacitance needed here.

#### High Current Low Voltage Supply

- Enable twice the current in half the space
- Up to 295 W or 200 A


4

#### **High Voltage Outputs**

 Put VTM stages in series to achieve output voltages greater than 55 V

#### **High Power Arrays**

 Parallel PRMs and VTMs to create multi-kW power systems



Web ExpressCode: vichip

RoHS



Shown at actual size

#### BCM<sup>™</sup> Bus Converter Module

Web ExpressCode: **bcm** 

The BCM is a member of the new family of V•I Chips. It provides an isolated intermediate bus voltage to power non-isolated POL converters from a narrow range DC input, or it can be used as an independent DC source. The BCM offers superior performance and lower cost than conventional bus converters. BCMs are available in standard 48 V telecom as well as in high-voltage offline input ranges.

Due to the fast response time and low noise of the BCM, the need for limited life aluminum electrolytic or tantalum capacitors at the load is reduced – or eliminated – resulting in savings of board area, materials, and total system cost.

#### Features

- Fixed-ratio bus converter
- Available in 48, 352, and 384 V inputs
- High density: Up to 1,100 W/in<sup>3</sup>
- Isolation to 4,242 Vdc
- Efficiency: Up to 96.5%

- Output power: Up to 330 W
- Small footprint: 1.1in<sup>2</sup> (7.1 cm<sup>2</sup>)
- Pick & place / SMD compatible
- Through-hole pin option
- 125°C operation (Tj)
- >3.5 million hours MTBF



Heat Sinks

**Available** 

Page 48

VI BRICK BCM model Page 10

MIL-COTS Version Available Page 34

### Part Numbering

For a complete listing of our BCM model numbers, go to vicorpower.com/vichip

В	0	4 8	F	120	Τ	30
Bus Converter Module	Input Voltage Designator	<b>Configuration</b> F = J-Lead T = Through hole	Output Voltage Designator ( = Vout X10 )	Product Grade Storage T -40 to 125°C M -65 to 125°C	Operating (Tj) -40 to 125°C	Output Power Designator ( = Pout/10)
VI	В	x x x	X	T	F	J
Branding V•l Chip	FPA Family B = Bus Converter Module	Product Reference Reference Only	Product Grade Storage (Tst) T -40 to 125°C M -65 to 125°C	Temperatures Operating (Tj) -40 to 125°C -55 to 125°C	Package Size F = Full H = Half	Leadform J = J-Lead (SMT) T= Through Hole

Input Voltage	K Factor	1	Vout	Max Power	Pack Size	BCM Model No.
input voitage	KTACIO	@ 48 Vin	Range		Fack Size	BCIVI WIOdel NO.
	1/32	1.5 Vdc	1.19 – 1.71 Vdc	135 W	Full	B048F015T14
	1/16	3.0 Vdc	2.38 – 3.43 Vdc	210 W	Full	B048F030T21
	1/12	4.0 Vdc	3.17 – 4.58 Vdc	200 W	Full	B048F040T20
	1/8	6.0 Vdc	4.75 – 6.87 Vdc	240 W	Full	B048F060T24
	1/6	8.0 Vdc	6.34 – 9.16 Vdc	240 W	Full	B048F080T24
38 – 55 Vdc	1/5	9.6 Vdc	7.60 – 11.00 Vdc	240 W	Full	B048F096T24
	1/4	12.0 Vdc	9.50 – 13.75 Vdc	120 W	Half	VIB0101THJ
	1/4	12.0 Vdc	9.50 – 13.80 Vdc	300 W	Full	B048F120T30
	1/3	16.0 Vdc	12.70 – 18.30 Vdc	240 W	Full	B048F160T24
	1/2	24.0 Vdc	19.00 – 26.50 Vdc [b]	300 W	Full	B048F240T30
	2/3	32.0 Vdc	25.30 – 36.70 Vdc	300 W	Full	B048F320T30
	1	48.0 Vdc	38.00 – 55.00 Vdc	300 W	Full	B048F480T30

<sup>[b]</sup> Vin = 38 - 53 Vdc

Input Voltage K Factor	K Factor	V	out	Max Power	Pack Size	BCM Model No.	
input voltage	KTactor	@ Nom. Vin	Range		Fack Size	BCIVI MIODEI NO.	
360 – 400 Vdc	1/32	12.0 Vdc	11.30 – 12.50 Vdc	300 W	Full	B384F120T30	
330 – 365 Vdc	1/32	11.0 Vdc	10.30 – 11.40 Vdc	300 W	Full	VIB0001TFJ	
360 – 400 Vdc	1/8	48.0 Vdc	45.00 – 50.00 Vdc	325 W	Full	VIB0002TFJ	
330 – 365 Vdc	1/8	44.0 Vdc	41.25 – 45.63 Vdc	325 W	Full	VIB0003TFJ	

Consult back cover for a complete list of contacts.

#### **PRM™** Regulator

The PRM is a high-efficiency, non-isolated regulator capable of both boosting and bucking a wide-range input voltage. PRMs may be used independently, as stand-alone regulators, or together with downstream V•I Chip VTMs<sup>™</sup> — fast, efficient, isolated low-noise point-of-load (POL) converters.

PRMs feature unique "Adaptive Loop" compensation feedback: a single-wire alternative to traditional remote sensing and feedback loops that enables precise control of an isolated POL voltage without the need for either a direct connection to the POL or for noise sensitive, bandwidth limiting, isolation devices in the feedback path.

#### **Features**

- ZVS buck / boost regulator
- Provides factorized bus for 48 Vin VTMs
- Available in 24, 36 and 48 V models
- Efficiency: Up to 97%
- High density: Up to 1,105 W/in<sup>3</sup>
- Small footprint: 1.1in<sup>2</sup> (7.1 cm<sup>2</sup>)
- 125°C operation (Tj)
- J-Lead package
- Through-hole pin option
- Pick & place / SMD compatible

**Heat Sinks Available** 


#### Part Numbering For a complete listing of our PRM model numbers, go to vicorpower.com/vichip

Ρ	0	4 8	F	048	Τ	24	A L
Pre-Regulator Module	Input Voltage Designator	<b>Configuration</b> F = J-Lead T = Through Hole	Nominal Factorized Bus Voltage	Product Grade Storage T –40 to 125°C M –65 to 125°C	<b>Temperatures</b> Operating (Tj) -40 to 125°C -55 to 125°C	Output Power Designator ( = Pf/10)	Adaptive Loop

Input Voltage	Max Out	put	PRM Model No.	Trim / Vf Range	
input voltage	Power	Current	FRIM MODEL NO.	IIIII / VI Kalige	
36 – 75 Vdc	240 W	5.0 A	P048F048T24AL		
36 – 75 Vác	120 W	2.5 A	P048F048T12AL		
38 – 55 Vdc	320 W	6.6 A	P045F048T32AL	26 – 55 V	
38 - 55 VUC	170 W	3.5 A	P045F048T17AL	26 - 55 V	
18 – 36 Vdc	120 W	2.5 A	P024F048T12AL		
18 – 60 Vdc	120 W	2.5 A	P036F048T12AL		


Note: See individual data sheets for additional model specifications and configurations.

#### **Application Examples**



Regulator

6



DC-DC Converter

**VI BRICK** 

PRM model Page 8

**MIL-COTS Version** <u>Available</u> Page 34

4111 41

Page 48



RoHS

### VTM<sup>™</sup> Voltage Transformer

The VTM provides an isolated voltage to the point of load. Utilizing a Sine Amplitude Converter (SAC), it offers unprecedented performance in the critical areas of speed, noise, efficiency and density. VTMs address output requirements from 0.8 – 55 Vdc at up to 100 A, all in a surface-mount package only one-quarter of a cubic inch in volume. VTMs operate over an input voltage range of 26 - 55 Vdc - the "factorized bus"- and are a fixed-ratio device that requires a PRM or other stabilized voltage source for regulation.

#### **Features**

- Fixed ratio DC-DC converter
- Output: Up to 100 A / 300 W
- High density: Up to 345 A/in<sup>3</sup>
- Small footprint: 1.1in<sup>2</sup> (7.1 cm<sup>2</sup>)
- Low weight: 0.5 oz (15 g)
- Pick & place / SMD compatible
- Efficiency: Up to 97%

- 125°C operation (Tj)
- 1 µs transient response
- >3.5 million hours MTBF
- J-Lead package
- Through-hole pin option
- Isolation to 2,250 Vdc




Web ExpressCode: vtm

**Heat Sinks Available** Page 48

**MIL-COTS Version Available** Page 34

#### Part Numbering For a complete listing of our VTM model numbers, go to vicorpower.com/vichip



Input Voltage	K Factor	۱.	/out	Output Current	VTM Model No.
input voltage	K Factor	@ 48 Vin	Range	Output current	v nivi iviodei no.
	1/32	1.5 Vdc	0.82 – 1.71 Vdc	100 A	V048F015T100
	1/24	2.0 Vdc	1.09 – 2.29 Vdc	80 A	V048F020T080
	1/16	3.0 Vdc	1.63 – 3.43 Vdc	70 A	V048F030T070
	1/12	4.0 Vdc	2.17 – 4.58 Vdc	50 A	V048F040T050
	1/8	6.0 Vdc	3.25 – 6.87 Vdc	40 A	V048F060T040
26 – 55 Vdc	1/6	8.0 Vdc	4.34 – 9.16 Vdc	30 A	V048F080T030
	1/5	9.6 Vdc	6.40 – 11.00 Vdc	25 A	V048F096T025 [a]
	1/4	12.0 Vdc	6.50 – 13.80 Vdc	25 A	V048F120T025
	1/3	16.0 Vdc	8.67 – 18.30 Vdc	15 A	V048F160T015
	1/2	24.0 Vdc	13.80 – 26.50 Vdc	12 A	V048F240T012 [b
	2/3	32.0 Vdc	17.30 – 36.70 Vdc	9 A	V048F320T009
	1	48.0 Vdc	26.00 – 55.00 Vdc	6 A	V048F480T006

[a] Vout = 6.4 Vdc @ 32 Vin

<sup>[b]</sup> Vout = 14.0 Vdc @ 28 Vin

7

### VI BRICK PRM Thermally Enhanced Package

The VI BRICK PRM is a very efficient non-isolated regulator designed to provide a controlled Factorized Bus distribution voltage for powering downstream VI BRICK or V•I Chip Voltage Transformation Modules. In combination, VI BRICK PRMs and VTMs form a complete DC-DC Converter subsystem offering all of the unique benefits of Vicor's Factorized Power Architecture (FPA): high density and efficiency; low noise operation; architectural flexibility; extremely fast transient response; elimination of bulk capacitance at the point of load (POL); in a brick style package.

#### Features

- 100°C baseplate operation
- Input voltages: 24, 36, 45 and 48 Vdc
- Low profile: 0.37 in. (9.5 mm)
- Low weight: 1.07 oz (30.3 g)
- Small footprint: 2.08 in<sup>2</sup>
- ZVS buck-boost regulator

- Efficiency: Up to 97%
- Fast transient response
- Low noise operation
- Rugged robust package
- Lead free wave solder compatible
- Agency approvals

#### Part Numbering Ordering, see back cover for contacts




PR	0	48	<b>A</b>	4 8 0	Τ	024	F	Ρ
Pre-Regulator Module	Input Voltage Designator	Package Size	Output Voltage Designator ( = Vout X 10 )	Product Grade Storage T –40 to 125°C M –65 to 125°C	Temperatures Operating -40 to 100°C -55 to 100°C	Output Power Designator ( = Pout / 10)	<b>Baseplate</b> F = Slotted flange P = Pin-fin heat sink <sup>[a]</sup>	<b>Pin Style</b> P = Through hole

[a] Contact factory

Input Voltage	Max Out	out	PRM Model No.	Trim / Vf Range	
input voltage	Power	Current	FRW Woder No.	IIIII / VI Kalige	
36 – 75 Vdc	240 W	5.0 A	PR048A480T024FP		
30 - 75 VUC	120 W	2.5 A	PR048A480T012FP		
38 – 55 Vdc	320 W	6.6 A	PR045A480T032FP	26 – 55 V	
38 - 33 VUC	170 W	3.5 A	PR045A480T017FP	20 – 55 V	
18 – 36 Vdc	120 W	2.5 A	PR024A480T012FP		
18 – 60 Vdc	120 W	2.5 A	PR036A480T012FP		

Note: See individual data sheets for additional model specifications and configurations.

Regulation



Web ExpressCode: vibprm

RoHS

### VI BRICK VTM Thermally Enhanced Package

Part Numbering Ordering, see back cover for contacts

Web ExpressCode: vibvtm

RoHS

The VI BRICK VTM current multiplier excels at speed, density and efficiency to meet the demands of advanced power applications. Combined with the VI BRICK or V•I Chip PRM regulator the VI BRICK VTM creates a DC-DC converter with flexibility to provide isolation and regulation where needed. The PRM can be located with the VTM at the point of load or remotely in the back plane or on a daughtercard.




#### Features

- 100°C baseplate operation
- Up to 100 A or 300 W
- High density: Up to 390 W/in<sup>3</sup>
- Small footprint: 2.08 in<sup>2</sup>
- Low profile: 0.37 in. (9.5 mm)
- Low weight: 1.10 oz (31.3 g)

- ZVS / ZCS isolated sine amplitude converter
- Efficiency: Up to 97%
- <1 µs transient response
- Isolated output
- No output filtering required
- Lead free wave solder compatible
- Agency approvals

#### MIL-COTS Version Available Page 34




[a] Contact factory

Input Voltage	K Factor	V	/out	Output Current	VTM Model No.
input voitage	K Factor	@ 48 Vin	Range	Output Current	v Hvi wouei wo.
	1/32	1.5 Vdc	0.82 – 1.71 Vdc	100 A	VT048A015T100FP
	1/24	2.0 Vdc	1.09 – 2.29 Vdc	80 A	VT048A020T080FP
	1/16	3.0 Vdc	1.63 – 3.43 Vdc	70 A	VT048A030T070FP
	1/12	4.0 Vdc	2.17 – 4.58 Vdc	50 A	VT048A040T050FP
	1/8	6.0 Vdc	3.25 – 6.87 Vdc	40 A	VT048A060T040FP
26 – 55 Vdc	1/6	8.0 Vdc	4.34 – 9.16 Vdc	30 A	VT048A080T030FP
	1/5	9.6 Vdc	6.40 – 11.00 Vdc	25 A	VT048A096T025FP [
	1/4	12.0 Vdc	6.50 – 13.80 Vdc	25 A	VT048A120T025FP
	1/3	16.0 Vdc	8.67 – 18.30 Vdc	15 A	VT048A160T015FP
	1/2	24.0 Vdc	13.80 – 26.50 Vdc	12 A	VT048A240T012FP [
	2/3	32.0 Vdc	17.30 – 36.70 Vdc	9 A	VT048A320T009FP
	1	48.0 Vdc	26.00 – 55.00 Vdc	6 A	VT048A480T006FP

Note: See individual data sheets for additional model specifications and configurations.

<sup>[b]</sup> Vout = 6.4 Vdc @ 32 Vin <sup>[c]</sup> Vout = 14.0 Vdc @ 28 Vin



#### Transformation / Isolation

### VI BRICK BCM Thermally Enhanced Package

VI BRICK BCM modules use advanced Sine Amplitude Converter<sup>™</sup> (SAC) technology, thermally enhanced packaging technologies, and advanced manufacturing processes to provide high power density and efficiency, superior transient response, and improved thermal management. These modules can be used to provide an isolated intermediate bus to power non-isolated POL converters and due to the fast response time and low noise of the BCM, capacitance can be reduced or eliminated near the load.

#### **Features**

- 100°C baseplate operation
- 48 V, 352, and 384 V Bus Converters
- High density: Up to 390 W/in<sup>3</sup>
- Small footprint: 2.08 in<sup>2</sup>
- Height above board: 0.37 in (9.5 mm)
- Efficiency: Up to 96%

#### Part Numbering Ordering, see back cover for contacts

- Isolated output
- No output filtering required
- <1 µs transient response
- Fast transient response
- Lead free wave solder compatible
- Agency approvals






B C	0	4 8	<b>A</b>	0 1 5	Τ	0 1 4	F	Ρ
Bus Converter Module	Input Voltage Designator	Package Size	Output Voltage Designator ( = Vout X 10 )	Product Grade Storage T –40 to 125°C M –65 to 125°C	Temperatures Operating -40 to 100°C -55 to 100°C	Output Power Designator ( = Pout/10)	<b>Baseplate</b> F = Slotted flange P = Pin-fin heat sink <sup>[a]</sup>	<b>Pin Style</b> P = Through hole

[a] Contact factory

Input Voltage	K Factor	Ve	out	Max Power	BCM Model No.
input voltage	K Factor	@ 48 Vin	Range	wax Power	BCIVI IVIOUEI INO.
	1/32	1.5 Vdc	1.19 – 1.71 Vdc	135 W	BC048A015T014FP
	1/16	3.0 Vdc	2.38 – 3.43 Vdc	210 W	BC048A030T021FP
	1/12	4.0 Vdc	3.17 – 4.58 Vdc	200 W	BC048A040T020FP
	1/8	6.0 Vdc	4.75 – 6.87 Vdc	240 W	BC048A060T024FP
	1/6	8.0 Vdc	6.34 – 9.16 Vdc	240 W	BC048A080T024FP
38 – 55 Vdc	1/5	9.6 Vdc	7.60 – 11.00 Vdc	240 W	BC048A096T024FP
	1/4	12.0 Vdc	9.50 – 13.80 Vdc	300 W	BC048A120T030FP
	1/3	16.0 Vdc	12.70 – 18.30 Vdc	240 W	BC048A160T024FP
	1/2	24.0 Vdc	19.00 – 26.50 Vdc <sup>[b]</sup>	300 W	BC048A240T030FP
	2/3	32.0 Vdc	25.30 – 36.70 Vdc	300 W	BC048A320T030FP
	1	48.0 Vdc	38.00 – 55.00 Vdc	300 W	BC048A480T030FP
330 – 365 Vdc	1/32	11.0 Vdc	10.3 – 11.4 Vdc	240 W	BC352A110T024FP
330 – 365 Vdc	1/32	11.0 Vdc	10.3 – 11.4 Vdc	300 W	BC352A110T030FP
360 – 400 Vdc	1/32	12.0 Vdc	11.3 – 12.5 Vdc	300 W	BC384A120T030FP

Note: See individual data sheets for additional model specifications and configurations. <sup>[b]</sup> Vin = 38 - 53 Vdc

### **Typical Application**



10 U.S. & CANADA: 800-735-6200 VICORPOWER.COM Web ExpressCode: vibbcm

RoHS

### VI BRICK DC-DC Converter

VI BRICK DC-DC converters use advanced Sine Amplitude Converter (SAC) technology, thermally enhanced packaging technologies, and advanced CIM processes to provide high power density and efficiency, superior transient response, and improved thermal management. The high speed 3.5 MHz, zero-current switching / zero-voltage switching (ZCS / ZVS) design enables efficient and low noise operation throughout the entire operating range.

#### Features

- DC input range: 36 75 V
- Efficiency: Up to 93%
- DC output: 1 48 V
- Maximum operating temp: 100°C, full load
- Isolated output
- Low noise: Sine Amplitude Converter (SAC) technology

#### Part Numbering Ordering, see back cover for contacts

- Highly efficient: ZCS / ZVS switching
- Fast dynamic response
- Low profile: 0.37 in. (9.5 mm)
- Power density: Up to 145 W/in<sup>3</sup>
- Lead free wave solder compatible
- Agency approvals



D C	0	4 8	B	0 5 0	Τ	0 1 8	F	Ρ
DC-DC Converter Module	Input Voltage Designator	Package Size	Output Voltage Designator ( = Vout X 10 )	Product Grade Storage T –40 to 125°C M –65 to 125°C	Temperatures Operating -40 to 100°C -55 to 100°C	Output Power Designator ( = Pout / 10)	<b>Baseplate</b> F = Slotted flange P = Pin-fin heat sink <sup>[a]</sup>	<b>Pin Style</b> P = Through hole

<sup>[a]</sup> Contact factory

Output Voltage	Output Power (W)	Current (A)	Efficiency (%)	Part Numbering
1.0 Vdc	100	100	85	DC048B010T010FP
1.5 Vdc	120	80	87	DC048B015T012FP
1.8 Vdc	144	80	89	DC048B018T014FP
2.5 Vdc	175	70	90	DC048B025T017FP
3.0 Vdc	180	60	91	DC048B030T018FP
3.3 Vdc	165	50	91	DC048B033T016FP
5 Vdc	180	36	91	DC048B050T018FP
10 Vdc	180	18	92	DC048B100T018FP
12 Vdc	220	18.33	92	DC048B120T022FP
15 vdc	200	13.33	92	DC048B150T020FP
24 Vdc	220	9.17	92	DC048B240T022FP
28 Vdc	190	6.79	92	DC048B280T019FP
48 Vdc	220	4.58	93	DC048B480T022FP

## VI-200 & VI-J00 Series Converter Modules

VI-200 and VI-J00 converters feature wide input voltage ranges, remote sense, enhanced output programmability, logic disable, and low quiescent current. VI-200 product series feature output overvoltage protection and thermal shut down. VI-J00 product series, at half the size of VI-200 converters, operate to 100°C. Both product series are safety agency approved, accelerating your time to market.

### Features

- Input voltage range: 10 400 Vdc
- Output voltages: 1 95 Vdc
- Output power (per module): VI-200 Series: 50 – 200 W • VI-J00 Series: 25 – 100 W
- Parallelable for higher power (VI-200)
- 3,000 Vrms isolation
- 100°C operation: (85°C for VI-200 Series)
- Output voltage trim range: 50 110%
- Efficiency: Up to 90%
- Agency approvals: cULus, cTÜVus, CE Marked

Dimensions: VI-200 Series: 4.6" x 2.4" x 0.5" (116,9 x 61,0 x 12,7 mm)

VI-J00 Series: 2.28" x 2.4" x 0.5" (57,9 x 61,0 x 12,7 mm)

Visit

vicorpower.com <u>& get your</u> <u>Design Guide</u>

 Weight: VI-200 Series: 6.0 oz / 170 g VI-J00 Series: 3.0 oz / 85 g

- Low-noise ZCS / ZVS power architecture
- 4 temperature grades

MIL-COTS Version Available Page 35

Battery Charging & Packaging Options
Page 23

**General Performance** Refer to data sheet for detailed specifications

Parameter	C-, I-, M-Grade	E-Grade
Input voltage and output voltage	See chart on page 13	
Set point accuracy	0.5%	1.0%
Load / line regulation (max)	0.2%	0.5%
Output temperature drift	0.01%/°C	0.02%/°C
Peak-to-peak output ripple (max)	1.5%	3%
Trim range <sup>[a]</sup>	50 – 110%	50 – 110%
Total remote sense compensation	0.5 V	0.5 V
OVP set point (VI-200 Series only)	125%	125%
Current limit	105 – 125%	105 – 135%
Efficiency (output ≥5 V)	80 – 90%	78 – 88%
Power sharing accuracy (VI-200 Series only)	±5%	±5%
Input reflected ripple current	10%	10%
No-load power dissipation	1.35 W	1.35 W
Isolation		
Input to output	3,000 Vrms	3,000 Vrms
Input to baseplate	1,500 Vrms	1,500 Vrms
Output to baseplate	500 Vrms	500 Vrms
Max. baseplate temperature: VI-200 Series (VI-J00 Series)	85°C (100°C)	85°C (100°C)

 $^{[a]}$  10 V, 12 V and 15 V outputs, standard trim range  $\pm 10$  %. Consult factory for wider trim range.

95 V outputs cannot be trimmed up.



RoHS




## Part Number Configuration Chart VI-200 & VI-J00

#### **IMPORTANT NOTICE: PLEASE READ BEFORE STARTING**

The part numbering format below is for Vicor VI-200 and VI-J00 DC-DC converters and configurables. The power levels shown are the maximum available for every input and output voltage combination. If you need more power than a VI-200 ("driver"), add parallel "booster" modules (of the same power level). For lower power versions use PowerBench at **Configure Your BRICK Online** ERBENCH

vicorpower.com/powerbench

PO



#### Designators VI-200 & VI-J00 Family and Accessory Modules

						ſ	Иах	imu	m P			vaila t Vol			VI-2	2(B)>	(х-х	x					
Vin	Input	2	3.3	5	5.2	5.5	5.8	6.5	7.5	10	· ·	13.8	-		24	28	36	40	48	52	72	85	95
Designator	Voltage	Ζ	Y	0	Х	W	V	Т	R	Μ	1	Р	2	Ν	3	L	J	Κ	4	Н	F	D	В
0	12 (10-20)	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х
V	24 (10-36)		Х	Υ	Υ	Υ	Υ	Υ	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х				
1	24 (21-32)	U	U	U	U	U	U	V	V	U	U	U	U	U	U	U	U	U	U	U	U	U	U
w	24 (18-36)	V	V	V	V	V	V	W	W	V	V	V	V	V	V	V	V	V	V	V	V	V	V
2	36 (21-56)	W	V	W	W	W	W	W	W	W	W	W	W	W	W	W	W	W	W	W			
3	48 (42-60)	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U
N	48 (36-76)	V	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U	U
4	72 (55-100)	U	U	U	U	U	U	V	V	U	U	U	U	U	U	U	U	U	U	U	U	U	U
т	110 (66-160)	V	V	V	V	V	V	W	W	V	V	V	V	V	V	V	V	V	V	V	V		
5	150 (100-200)	U	U	V	V	V	V	V	V	U	U	U	U	U	U	U	U	U	U	U	U	U	U
	150 (100-375)	W	W	Υ	Υ	Υ	Υ	W	W	W	W	W	W	W	W	W	W	W	W	W			
6	300 (200-400)	U	U	U	U	U	U	V	V	U	U	U	U	U	U	U	U	U	U	U	U	U	U
						r	Иах	imu	m P			/aila t Vol			VI-J	хх-х	x						
Vin	Input	2	3.3	5	52	5.5	5.8	6.5	7.5	10		13.8	-		24	28	36	40	48	52	72	85	95
Designator	Voltage	Z	Y	0	<u>у.г</u> Х	W	V.	т	R	M	1	P	2	N	3	20	50	K	4	H	F	D	B
-	5	_					-				v				-	2	, ,					-	-
0	12 (10-20)	Х	Х	Y	Y	Y	Y	Y	Y	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х	Х
V	24 (10-36)		Y	Y	Y	Y	Y W	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y W	W			
1 W	24 (21-32) 24 (18-36)	W	W	W	W	W	W	Х	Х	W W	W	W	W	W	W	W	W	W W	W	W	W	W	W
	24 (18-36) 36 (21-56)	Y	VV Y	Y	Y	Y	Y	X Y	X Y				W	W		W	W				W	W	VV
2 3	48 (42-60)	Y W	r W	Ŵ	Ŵ	ř W	ĭ W	ř X	r X	X W	X W	X W	X W	X W	X W	X W	X W	X W	X W	X W	W	W	W
N	48 (42-60) 48 (36-76)	W	W	X	X	X	X	X	X	W	W	W	W	W	W	W	W	W	W	W	W	W	W
4	48 (36-76) 72 (55-100)	W	W	Ŵ	W	Ŵ	Ŵ	X	X	W	W	W	W	W	W	W	W	W	W	W	W	W	W
4 T	110 (66-160)	W	W	X	X	X	X	X	X	W	W	W	W	W	W	W	W	W	W	W	W	vv	~~
-	150 (100-200)	W	W	Ŵ	Ŵ	Ŵ	Ŵ	X	X	W	W	W	W	W	W	W	W	W	W	W	W	W	W
	150 (100-200)	Y	Y	Y	Y	Y	Y	Ŷ	Ŷ	X	X	X	X	X	X	X	X	X	X	X		vv	vv

Note: See Design Guide & Applications Manual for VI-200 & VI-J00 Family, DC-DC Converters & Configurable Power Supplies

Consult back cover for a complete list of contacts.

### Maxi, Mini, Micro Series Converter Modules

Maxi, Mini, Micro Series DC-DC converter modules use advanced power processing, control, and packaging technologies to provide the performance, flexibility, and cost effectiveness expected of a mature power component. High-frequency ZCS / ZVS switching, advanced power semiconductor packaging, and thermal management provide high power density with low noise and high efficiency.

#### Features

- 24 V input: 18 36 Vdc 28 V input: 10 – 36 Vdc 48 V input: 36 – 75 Vdc 72 V input: 43 – 110 Vdc 110 V input: 66 – 154 Vdc 150 V input: 100 – 200 Vdc 300 V input: 180 – 375 Vdc 375 V input: 250 – 425 Vdc
- 100°C, no derating
- High efficiency
- Low-noise ZCS / ZVS
- Up to 120 W/in<sup>3</sup>
- 3.000 Vac isolation

- Single-wire paralleling
- Input undervoltage lockout
- Output overvoltage protection
- Overtemperature shut down
- Module fault alarm
- ZCS / ZVS power architecture
- Output voltage trim: 10 110% Bias supply to power .
- external circuitry Logic enable / disable
- 5 temperature grades .



**Module Mounting & Interconnect Options** <u>Page 50</u>

<u>Visit</u>

vicorpower.com

& get your **Design Guide**  **MIL-COTS Version Available** Page 35

### **Configure Your BRICK Online** RBENCH vicorpower.com/powerbench

**General Performance** Refer to data sheet for detailed specifications

Parameter	Specifications	Notes
Set point accuracy	±1% Vout nom.	Nominal input; full load; 25°C
Line regulation	±0.02% Vout nom.	Low line to high line; full load
Load regulation	±0.02% Vout nom.	No load to full load; nominal input
Temperature regulation	±0.002% Vout/°C	–20 to 100°C (C-Grade)
Remote sense compensation	0.5 V	Maxi and Mini only
Overvoltage set point	115% Vout nom.	
Current limit	115% lout typ.	Vout 95% of nominal
Short-circuit current	115% lout typ.	Output voltage <250 mV
Efficiency	Up to 90%	Nominal input; 80% load; 25°C
Programming range	10 – 110% Vout nom.	
Isolation voltage	3,000 Vrms	Input to output
Dimensions		
Maxi full-brick	4.6" x 2.2" x 0.5" (117 x 55,9 x 12,7 mm)	Up to 600 W
Mini half-brick	2.28" x 2.2" x 0.5" (57,9 x 55,9 x 12,7 mm)	Up to 300 W
Micro quarter-brick	2.28" x 1.45" x 0.5" (57,9 x 36,8 x 12,7 mm)	Up to 150 W
Agency approvals	culus cTÜVus CE Marked	

Agency approvals

cULus, cTUVus, CE Marked

#### Design Guide & Applications Manual Maxi, Mini, Micro Family DC-DC Converters & Accessory Modules

- High density DC-DC converter technology
- Control pin functions & applications
- Design requirements
- EMC considerations
- Current sharing in power arrays
- Thermal performance information

- Filter / autoranging rectifiers
- Modular AC front-end system
- High Boost HAM
- Filter Input Attenuator Module •
- MIL-COTS Filter Input Attenuator
- Output ripple attenuator



### Web ExpressCode: bricks2

#### Part Numbering Maxi, Mini & Micro Series Converters

Web ExpressCode: prodselect





Mini example: V48B28C250BG 48 Vin, Mini, 28 Vout @ 250 W, long RoHS pins, slotted baseplate



Output Power

 $M = -55 \text{ to } +100^{\circ}\text{C}$ 



Micro example: V375C24C150BG 375 Vin, Micro, 24 Vout @ 150 W, long RoHS pins, slotted baseplate



**Pin Style** Blank = Short tin / lead L = Long tin / lead S = Short ModuMate N = Long ModuMate F = Short gold (RoHS) G = Long gold (RoHS)



Blank = Slotted 2 = Threaded 3 = Through hole

<sup>[a]</sup> Consult factory for other input / output / power models.

#### Designators Maxi, Mini, Micro Family

Input				ſ	Maximu		r availat Output V	ole for Ma oltages	axi (Full	Brick)			
Voltage	2 V	3.3 V	5 V	6.5 V	8 V	12 V	15 V	24 V	28 V	32 V	36 V	48 V	54 V
<b>24</b> (18-36)		264 W	400 W	400 W	300 W	400 W	400 W	400 W	400 W		400 W	400 W	
<b>28</b> (10-36)		150 W	175 W	200 W	200 W	200 W	200 W	200 W	200 W		200 W	200 W	
<b>48</b> (36-75)		264 W	400 W			500 W	500 W	500 W	500 W		500 W	500 W	
<b>72</b> (43-110)		264 W	300 W			400 W	400 W	400 W	400 W		400 W	400 W	
<b>110</b> (66-154)		200 W	300 W		300 W	400 W	400 W	400 W	400 W		400 W	400 W	
<b>150</b> (100-200)		264 W	400 W		400 W	500 W	500 W	500 W	500 W		500 W	500 W	
<b>300</b> (180-375)	160 W	264 W	400 W		400 W	500 W	500 W	500 W	500 W		500 W	500 W	
<b>375</b> (250-425)	160 W	264 W	400 W		400 W	600 W	600 W	600 W	600 W	600 W	600 W	600 W	600 V
				Ма	ximum			for Mini	(Half Bri	ck)			
	2.14	2.2.1/	<b>F</b> 1/	6 5 14	0.14		out Voltag		20.1/	22.14	26.14	40.14	<b>FA</b> 14
34 (10.20)	2 V	<b>3.3 V</b> 150 W	<b>5 V</b> 200 W	6.5 V	<b>8 V</b> 200 W	<b>12 V</b> 200 W	<b>15 V</b> 200 W	<b>24 V</b> 200 W	<b>28 V</b> 200 W	32 V	<b>36 V</b> 200 W	<b>48 V</b> 200 W	54 V
<b>24</b> (18-36)		150 W							200 W 250 W				
<b>48</b> (36-75)	100 W	150 W	200 W 150 W		 150 W	250 W 250 W	250 W 250 W	250 W 250 W	250 W		250 W 250 W	250 W 250 W	
<b>72</b> (43-110)		100 W			150 W	250 W		250 W	250 W		250 W		
<b>110</b> (66-154)			150 W				200 W		200 W 250 W			200 W 250 W	
<b>150</b> (100-200)		150 W 150 W	200 W 200 W		200 W 200 W	250 W 250 W	250 W 250 W	250 W 250 W	250 W		250 W 250 W	250 W	
<b>300</b> (180-375)													
<b>375</b> (250-425)	100 W	150 W	200 W		200 W	300 W	300 W	300 W	300 W		300 W	300 W	
				Maxi	mum Po		ailable fo out Voltag	or Micro (	Quarter	Brick)			
	2 V	3.3 V	5 V	6.5 V	8 V	12 V	15 V	24 V	28 V	32 V	36 V	48 V	54 V
<b>24</b> (18-36)		75 W	100 W		100 W	100 W	100 W	100 W	100 W		100 W	100 W	
<b>28</b> (9-36)		50 W	50 W			100 W	100 W	100 W	100 W		100 W	100 W	
<b>48</b> (36-75)	50 W	75 W	100 W			150 W	150 W	150 W	150 W		150 W	150 W	
<b>72</b> (43-110)		75 W	100 W		100 W	150 W	150 W	150 W	150 W		150 W	150 W	
<b>110</b> (66-154)		50 W	75 W		75 W	100 W	100 W	100 W	100 W		100 W	100 W	
<b>150</b> (100-200)		75 W	100 W		100 W	150 W	150 W	150 W	150 W		150 W	150 W	
<b>300</b> (180-375)	50 W	75 W	100 W		100 W	150 W	150 W	150 W	150 W		150 W	150 W	
<b>375</b> (250-425)	50 W	75 W	100 W		100 W	150 W	150 W	150 W	150 W		150 W	150 W	

See Vicor PowerBench Online for intermediate power modules and to customize a solution. See Data Sheet for detailed electrical specifications and intermediate power modules.

U.S. & CANADA: 800-735-6200 VICORPOWER.COM 15

# **Cool-ORing<sup>™</sup> Series** Universal Active ORing Controllers

#### Web ExpressCode: oring

### PI2001 / PI2002 / PI2003

The Cool-ORing PI2001/2/3 are universal high-speed Active ORing controller IC solutions designed for use with N-channel MOSFETs in redundant power system architectures. The PI2001/2/3 Cool-ORing controllers enable an extremely low power loss solution with fast dynamic response to fault conditions, critical for high availability systems. The PI2001/3 control single or parallel MOSFETs to address Active ORing applications protecting against power source failures. The PI2003 is optimized for low side -48V Active ORing applications. An internal VC shunt regulator enables biasing of the controller directly from -48 V (GND). The PI2002 includes a load disconnect feature for use with back-to-back N-channel MOSFETs in redundant power architectures.

The gate drive output turns the MOSFET on in normal steady state operation, while achieving high-speed turn-off during input power source fault conditions, which cause reverse current flow, with auto-reset once the fault clears. The PI2002 has the added benefit of being able to protect against output load fault conditions that may induce excessive forward current and device over-temperature by removing gate drive from the back-to-back MOSFETs with an auto-retry programmable off-time.



#### Features


- Fast dynamic response to power source failures, with 160 ns reverse current turn-off delay time
- 4 A gate discharge current
- Accurate MOSFET drain-to-source voltage sensing to indicate system level fault conditions
- Programmable under and overvoltage detection
- Overtemperature fault detection
- Adjustable reverse current blanking timer
- Withstands 100 V transients in low-side applications
- Master / Slave I/O for paralleling (TDFN package only)
- Active-low fault flag output


Part Number	Package	Target Application	Bias Supply	MOSFET Gate Drive Voltage	MOSFET Gate Discharge Current	Turn-off Delay Time	Shipment Packaging
PI2001-00-QEIG		Universal Low Voltage Active ORing		8.5 V – 10.5 V		160 ns (typ.)	
PI2002-00-QEIG	3 x 3 mm 10 Lead TDFN	Active ORing w/ Load Disconnect	4.5 V – 13.2 V	9.0 V – 11.0 V	_	Reverse Fault, 120 ns (typ.)	
PI2003-00-QEIG		48 V Optimized Low Side Active ORing	Internal VC Clamp 10 V – 12 V	VC – 0.25 V		Forward Overcurrent, 150 ns (typ.)	Tape and
PI2001-00-SOIG		Universal Low Voltage Active ORing		8.5 V – 10.5 V	4 A (typ)	160 ns (typ.)	Reel
PI2002-00-SOIG	8 Lead SOIC	Active ORing w/ Load Disconnect	4.5 V – 13.2 V	9.0 V – 11.0 V	_	Reverse Fault, 120 ns (typ.)	
PI2003-00-SOIG		48 V Optimized Low Side Active ORing	Internal VC Clamp 10 V – 12 V	VC – 0.25 V	_	Forward Overcurrent, 150 ns (typ.)	

#### **Evaluation Boards**

PI2001-EVAL1PI2001 Evaluation Board using 3 x 3 mm TDFN package and SO-8 MOSFET in high-side configuration. (pg. 47)PI2002-EVAL1PI2002 Evaluation Board using 3 x 3 mm TDFN package and back-to-back SO-8 MOSFETs in high-side configuration. (pg. 47)PI2003-EVAL1PI2003 Evaluation Board using 3 x 3 mm TDFN package and 100 V SO-8 MOSFET in low-side configuration. (pg. 47)


#### **Typical Application**





Low-side Active ORing

#### PI2001 performance



Typical dynamic response of the PI2001 to an input power source short circuit fault condition

# Part Numbering

#### 16 U.S. & CANADA: 800-735-6200 VICORPOWER.COM

# **Cool-ORing<sup>™</sup> Series** Full-Function Active ORing Solutions

### PI2121 / PI2122 / PI2123 / PI2125

The Cool-ORing PI2121/3/5 are complete full-function Active ORing solutions each with a high-speed ORing MOSFET controller and a very low on-state resistance MOSFET designed for use in redundant power system architectures. The PI2121/3/5 Cool-ORing solutions are offered in an extremely small, thermally enhanced 5 x 7 mm LGA package and can be used in low voltage ( $\leq$ 5 V bus,  $\leq$ 9.6 V bus and  $\leq$ 12 V bus respectively) high side Active ORing applications. The PI2121/3/5 enable extremely low power loss with fast dynamic response to fault conditions, critical for high-availability systems. A master / slave feature allows the paralleling of PI2121/3/5 solutions for high-current, Active ORing requirements.

The PI2121/3/5 provide very high efficiency and low power loss during steady state operation, while achieving high-speed turn-off of the internal MOSFET during input power source fault conditions, which cause reverse current flow. The PI2121/3/5 provide an active low fault flag output to the system during excessive forward current, light load, reverse current, overvoltage, undervoltage and overtemperature fault conditions.

The PI2122 is configured with back-to-back MOSFETs designed for use in  $\leq$ 5 V bus redundant power system architectures where added protection against load fault conditions is required. The back-to-back MOSFET provides a true bi-directional switch capability to disconnect load fault conditions that may induce excessive forward current and device over-temperature.

5 mm x 7 mm x 2 mm Thermally Enhanced LGA

#### Features

- Combines a high-speed ORing MOSFET controller and low on-state resistance MOSFET
- Integrated high-performance MOSFET PI2121: 8 V, 24 A, 1.5 mΩ
   PI2122: 7 V, 12 A, 6 mΩ (back-to-back MOSFET)
   PI2123: 15 V, 15 A, 3 mΩ
   PI2125: 30 V, 12 A, 5.5 mΩ
- Very small, high density fully optimized solution
- Fast dynamic response to power source failures, with 160 ns reverse current turn-off delay time
- Accurate sensing capability to indicate system fault conditions
- Programmable under and overvoltage functions
- Overtemperature fault detection
- Adjustable reverse current blanking timer
- Master / Slave I/O for paralleling
- Active-low fault flag output

Part Number	Package	Voltage Rating	Current Handling	Target Application	Internal MOSFET On-State Resistance	Bias Supply	Turn-off Delay Time	Shipment Packaging
PI2121-00-LGIZ		8 V (max)	24 A (max)	≤5 V Bus	1.5 mΩ (typ)			Tana
PI2122-00-LGIZ	5 x 7 mm	7 V (max)	12 A (max)	≤5 V Bus	6.0 mΩ (typ)	4.5 V – 13.2 V	160 ns (tvp.)	Tape and
PI2123-00-LGIZ	LGA	15 V (max)	15 A (max)	≤9.6 V Bus	3.0 mΩ (typ)	4.5 V = 15.2 V	100 HS (typ.)	Reel
PI2125-00-LGIZ		30 V (max)	12 A (max)	≤12 V Bus	5.5 mΩ (typ)			neer

#### **Evaluation Boards**

Part Numbering


PI2121-EVAL1PI2121 Evaluation Board configured for a high-side ground referenced application. (pg. 47)

PI2122-EVAL1PI2122 Evaluation Board configured for a high-side application. (pg. 47)


PI2125-EVAL2PI2125 Evaluation Board configured for a high-side floating application. (pg. 47)

Note: Both PI2121-EVAL1 and PI2125-EVAL2 are compatible with the PI2123 solution.

#### **Typical Applications**




PI2121: High-side Active ORing



Pl2122: High-side Active ORing with Load Disconnect

#### PI2121 / PI2123 / PI2125 Performance



Power dissipation comparison between Picor's Cool-ORing solutions versus industry standard Schottky diode solutions

### Web ExpressCode: oring2

RoHS

### **HAM** Input Harmonic Attenuator Module


Web ExpressCode: ham

RoHS

The Harmonic Attenuator Module (HAM) accepts an input of 85 – 264 Vac. The "M" version provides a DC output compatible with Vicor's 26x, J6x and user-defined Maxi, Mini and Micro DC-DC converters. The "L" version is compatible with V375 series DC-DC converters. The combination of a HAM, one or more Vicor DC-DC converters, and the 30205 <u>line filter, listed on</u> <u>Page 51</u>, offers a high-density power solution meeting EN61000-3-2.

#### Features

- Power output: Up to 675 W
- Input: 85 264 Vac
- Meets EN61000-3-2
- 0.99 Power Factor
- Short-circuit protection
- High efficiency
- Input-surge limiting
- Dimensions:
   4.6" x 2.4" x 0.5"
   (117 x 61,0 x 12,7 mm)
- cULus, cTÜVus, CE Marked



<sup>[a]</sup> Compatible with V375 Maxi, Mini, Micro Series


**Note:** If power requirements exceed the capability of one HAM, use a HAMD and one or more BAMDs, with an external bridge rectifier. HAM, HAMD, and BAMD modules require three surge suppressors in series directly across the input. These surge suppressors are already contained in the EMI filter P/N 30205. Also, use a 10 A, 3AG fast-blow fuse ahead of the line filter.

General Performance Refer to data sheet for detailed specifications

Parameter	Specifications	Notes
AC line input	85 – 264 Vac	Continuous operation
Ac line input	47 – 63 Hz	
Output power	Up to 675 W	
Efficiency	92%	
Power factor	0.99	
Total harmonic distortion <sup>[b]</sup>	<8.5%	
Output ripple	7 Vр-р	Cout = 1000 µF, 600 W
Inrush current	20 A peak	No external circuitry
Hold-up capacitance	500 – 3,000 μF	Power dependent
Isolation voltage		
Input to output	None	Provided by DC-DC converters
Input / output to baseplate	1,500 Vrms	
Auxiliary output	19 – 23 Vdc @ ≤3 mA	
Thermal shut down	90 to 100°C baseplate	
Short-circuit protection	Yes	
Weight	6 oz (170 g)	

<sup>[b]</sup> With sinusoidal input voltage ITHD - VTHD = THD

Typical Configuration Not for design use; see data sheet for more information



## **PFC FrontEnd** 384 V Output

The PFC FrontEnd from Westcor is a low-profile, 1 RU enclosed chassismount AC front end that may be used with any 375 Vin Vicor module, VIPAC Array, BCM, or other module to create a complete, high-density AC-DC power supply. Accepting universal input voltages of 85 – 264 Vac, and 100 – 380 Vdc, the PFC FrontEnd can deliver up to 2,200 Watts from four non-isolated outputs. With an extremely compact package size of 1.72 " x 6.4 " x 7" (43,6 x 162,6 x 177,8 mm), the PFC FrontEnd can provide >28 W/in<sup>3</sup>.

Besides meeting the UL, cTÜVus and CE Marked safety agency approvals, the PFC FrontEnd complies with harmonic current limits per EN61000-3-2, Electrical Fast Transient / burst EN61000-4-5. It also meets MIL-STD-810E for vibration.


#### Features

- Power Factor Corrected (PFC)
- Low profile: 1.72 " (43,6 mm)
- Output power: Up to 2,200 Watts
- High power density
- Up to four non-isolated outputs
- Output voltage: 384 V
- Integral cooling fans
- Meets MIL-STD-810E for vibration
- DIN rail mountable
- Safety agency approvals: cTÜVus, CE Marked

### General Performance Refer to data sheet for detailed specifications

Product	Dimensions	Input Voltage	Output Power	Number of Outputs
	1 72" x 6 4" x 7"	85 – 264 Vac	2,200 W @ 230 Vac	4 (non-isolated)
PFC FrontEnd	(43.6 x 162.6 x 177.8 mm)	47 – 800 Hz		
	(43,6 × 162,6 × 177,6 mm)	100 – 380 Vdc	1,100 W @ 115 Vac	

#### Typical Configuration With VIPAC Array; see data sheet for more information







VICOR Westcor Division Part Number F E 3 7 5 - 1

U.S. & CANADA: 800-735-6200 VICORPOWER.COM 19

### **AIM** AC Input Module


The AIM (Alternating Input Module) is an AC front-end module which interfaces directly with worldwide AC mains. The AIM provides line rectification, EMI/RFI filtering, transient protection, and inrush limiting in a half-brick package measuring 2.28" x 2.4" x 0.5"(57,9 x 61,0 x 12,7 mm).

The AIM is used in conjunction with Vicor VI-200 or VI-J00 DC-DC converters to realize a universal AC input, high-density, low-profile switching power supply with outputs from 1-95 Vdc and a total power rating up to 200 W. An external capacitor is used to satisfy system hold-up requirements. Internal EMI filtering meets EN55022 and FCC Part 15, Class A emissions limits.

#### Features

- Universal input: 85 264 Vac
- Output power: 250 W
- Operating temperature up to 100°C baseplate (no derating)
- Efficiency: 97%
- Integral EMI filtering
- Input transient protection
- Inrush limiting
- cULus, cTÜVus, CE Marked






#### General Performance Refer to data sheet for detailed specifications

Parameter	Specifications	Notes
AC line input	85 – 264 Vac	No strapping
Ac inc input	47 – 440 Hz	No damage below low line
Output power	Up to 250 W	
Efficiency	97%	
Power factor	0.62	
Inrush current	<40 A peak	No external circuitry
Hold-up capacitance	270 – 1,200 μF	Power dependent
Isolation voltage		
Input to output	None	Provided by DC-DC converters
Input / output to baseplate	1,500 Vrms	
Short-circuit protection	No	
Weight	3 oz (85 g)	

#### Typical Configuration Not for design use; see data sheet for more information



### Web ExpressCode: aim

RoHS



<u>Page 35</u>

### Autoranging Rectifier Module ARM

The Autoranging Rectifier Module (ARM) is the front end of a switching power supply and uses a microprocessor to control strapping of the voltage doubler. The user only needs to add an input filter, hold-up capacitor and appropriate DC-DC converters to realize an autoranging, high-density, low-profile switching power supply.

### Features

- Efficiency: 96 98%
- Operating temperature: Up to 100°C baseplate (no derating)
- Agency approvals: cTÜVus, cULus, CE Marked
- AC Bus OK, module enable
- Inrush limiting (no external circuitry) -
- Autoranging input: 90 132 / 180 264 Vac

<sup>[b]</sup> Valid combination with **Type 2** only <sup>[c]</sup> T-Grade storage temp. is -40°C; H-Grade storage temp. is -55°C

## Filter / Autoranging Rectifier Module FARM

The FARM (Filter / Autoranging Rectifier Module) is an AC front-end module which provides EMI filtering, autoranging line rectification, transient protection, and inrush current limiting.

**Part Numbering** Ordering, see back cover for contacts

Part Numbering Ordering, see back cover for contacts

M

Product Grade

= -10 to +100°C

= -20 to +100°C

 $H = -40 \text{ to } +100^{\circ}\text{C}$ 

 $M = -55 \text{ to } +100^{\circ}\text{C}$ 

= -40 to +100°C [c]

R

F

С

Т


Blank =

 $500 \, W$  /  $750 \, W^{[a]}$ 

B =

750 W / 1,500 W <sup>[b]</sup>

<sup>[a]</sup> Valid combination with **Type 1** only



<sup>[d]</sup> T-Grade storage temp. is -40°C; H-Grade storage temp. is -55°C

### General Performance for ARM & FARM Refer to data sheet for detailed specifications

Product

Parameter	ARM-( )12	ARMB-( )22	FARM1( )21	FARM2( )21			
Input voltage	90 – 1	32 Vac	90 – 13	32 Vac			
input voltage	180 - 2	264 Vac	180 – 264 Vac				
Input frequency (C & E-Grade)	47 -	63 Hz	47 – 63 Hz				
Input frequency (T & H-Grade)	47 – 8	80 Hz	47 – 8	80 Hz			
Output power							
115 Vac input	500 Watts	750 Watts	500 Watts	750 Watts			
230 Vac input	750 Watts	1,500 Watts	750 Watts	1,000 Watts			
Compatible DC-DC converter	26x, J6	x, V300	26x, J6>	x, V300			
Efficiency (typical)	97	%	96%				
Inrush current (peak line. Cold start)	<30 A @ 264 Vac	<60 A @264 Vac	<30 A @ 264 Vac	<60 A @264 Vac			
Dielectric withstand: Input /output	Provided by DC	-DC converters	Provided by DC-DC converters				
I/O to baseplate	1,500	Vrms	1,500	Vrms			
Package	Mi	cro	Mi	ni			
Dimensions	2.28" x 1.45" x 0.5" (	57,9 x 36,8 x 12,7 mm)	2.28" x 2.2" x 0.5" (57	7,9 x 55,9 x 12,7 mm)			
Operating temperature (C-Grade)	-20 to -	+100°C	–20 to -	-100°C			
Operating temperature (T-Grade)	-40 to	+100°C	-40 to +100°C				
Weight	2.1 oz	(60 g)	3.1 oz (87.9 g)				

#### Web ExpressCode: arm

2

Type

500 W / 750 W

2 =

750 W / 1,500 W

3

Pin Style 1 = Short

2 = Long S = Short ModuMate

N = Long ModuMate

Web ExpressCode: farm

F = Short RoHS

G = Long RoHS

RoHS

Baseplate

3 = Through hole

RoHS

Blank = Slotted

2 = Threaded

### **ENMods** Modular AC Front-end System

The ENMod system is an AC front-end solution providing compliance to electromagnetic compatibility (EMC) standards. It consists of the MiniHAM passive harmonic attenuation module and the FARM3 autoranging AC-DC front-end module. Combined with filtering and hold-up capacitors, the ENMod system provides full compliance to EN61000-3-2 Harmonic Current, EN55022, Level B Conducted Emissions, EN61000-4-5 Surge Immunity, EN61000-4-11 Line Disturbances, and EN61000-3-3 Inrush Current. Unlike active PFC solutions, the MiniHAM generates no EMI, greatly simplifying and reducing system noise filtering requirements. It is also smaller and more efficient than active alternatives. Optimized for operation on the DC bus (provided by the FARM3) rather than directly on the AC line, it will provide harmonic current compliance at up to 600 W of input power at 230 Vac.


The FARM3 is a filter and autoranging module that has been optimized for use as the front end for the MiniHAM. Both modules are in Vicor's standard Mini half-brick package.



#### Features

- Passive harmonic current attenuation to EN61000-3-2
- 575 W rated power output
- Autoranging 115/230 Vac Input
- Inrush current limiting

#### Part Numbering Ordering, see back cover for contacts




<sup>[a]</sup> EN1 product includes one each MiniHAM and FARM3, same product grade, pin and baseplate style. <sup>[b]</sup> Pin styles S & N are compatible with ModuMate interconnect systems for socketing and surface mounting. <sup>[c]</sup> T-Grade storage temp. is -40°C; H-Grade storage temp. is -55°C

#### **General Performance** Refer to data sheet for detailed specifications

Parameter	Specification	Notes		
Operating input voltage	90 – 132 Vac	Autoranging (doubler-mode)		
Operating input voltage	180 – 264 Vac	Autoranging (bridge-mode)		
Output power (max)	575 Watts			
Harmonic currents	EN61000-3-2	50 – 600 W, 230 Vac input		
Transient surge immunity	EN61000-4-5	2 kV – 50 µs line to earth		
	LINO 1000-4-5	1 kV – 50 μs line to line		
Conducted emissions	EN55022, Class B			
Safety	EN60950			
Dimensions				
MiniHAM	2.28" x 2.2" x 0.5" (57,9 x 55,9 x 12,7 mm)			
FARM3	2.28" x 2.2" x 0.5″ (57,9 x 55,9 x 12,7 mm)			

#### Typical Configuration Not for design use; see data sheet for more information



#### Web ExpressCode: enmods

RoHS

#### Web ExpressCode: batmod

#### **BatMod** Battery Charger

The fully-programmable BatMod current source module is based on the VI-200 Series of DC-DC converters. It accepts 48, 150, or 300 V inputs, provides programmable output current, and is well-suited for such applications as battery chargers, metal platers, and laser diodes. The BatMod is compatible with all major battery types, and is available in booster versions for higher output current applications.

#### **Features**

- Input voltages: 48, 150 or 300 V
- Programmable output current
- Booster versions for higher output current applications
- Agency approvals: cULus, cTÜVus, CE Marked
- Dimensions: 4.6" x 2.4" x 0.5" (116,9 x 61,0 x 12,7 mm)



#### Part Numbering Ordering, see back cover for contacts B М Product Grade Family Module Input Voltage **Output Voltage** VI = Non-RoHS 2 = Driver Nominal $E = -10 \text{ to } +85^{\circ}\text{C}$ Range Nominal Range $1 = 12 \text{ V} \quad 11.25 - 16.5 \text{ V} \\ 3 = 24 \text{ V}^{[a]} \quad 22.5 - 33.0 \text{ V}$ = -25 to +85°C VE = RoHS 3 = 48 V 5 = 150 V 42 – 60 V B = Booster

100 – 200 V

200 – 400 V

6 = 300 V

<sup>[a]</sup> Available in 300 V input only.

#### Packaging Options Chassis-mount housing VI-200 & VI-J00 Series, page 33

SlimMod

Flangeless package



2.28"L x 1.80"W x 0.50"H (57,9 x 45,7 x 12,7 mm)



4.60"L x 1.80"W x 0.50"H (116,8 x 45,7 x 12,7 mm)

To order the SlimMod configuration add the suffix "-S" to the standard module part number as shown on Page 13

#### FinMod

Flangeless package with integral heat sink



Longitudinal, 0.25" fins — add suffix "-F1" Longitudinal, 0.50" fins — add suffix "-F2"





Transverse, 0.25" fins — add suffix "-F3" Transverse, 0.50" fins — add suffix "-F4"

Available with longitudinal or transverse fins of 0.25" or 0.50" height. Add the appropriate suffix to the module part number as shown on Page 13.

#### BusMod

4 = 48 V 45.0 - 66.0 V

Chassis mount housing with screw / lug wiring interface

L

= -40 to +85°C

M = -55 to +85°C



2.28"L x 2.40"W x 1.08"H (57,9 x 61,0 x 27,4 mm)



4.60"L x 2.40"W x 1.08"H (116,8 x 61,0 x 27,4 mm)

To order the BusMod fully assembled, add suffix "-B1" to the standard module part number as shown on Page 1

To order the BusMod separately: Half-sized BusMod — P/N 18952 Full-sized BusMod — P/N 06322

## **DC-DC** Filters

#### **FIAM** Filter Input Attenuator Module \_

A DC input, front-end module providing transient protection, inrush current limiting and EMI filtering. The FIAM enables designers using Vicor Maxi, Mini, and Micro 48 Vin DC-DC converters to meet the transient immunity and EMI requirements of Telcordia, FCC, ETSI and European Norms.

#### **Features**


- EMI filtering Class A
- Inrush current limiting
- Transient protection
- Input: 36 76 Vdc
- 10 and 20 Amp versions .
- Agency approvals: cULus, cTÜVus, CE Marked

Parameter	Specification		
Input voltage	36 – 76 Vdc		
Output current			
FIAM1xxx / FIAM2xxx	10 A / 20 A		
Inrush limiting	0.014 Amp/µF		
EMI/REI	Telcordia GR-1089-Core Issue 2,		
	EN55022, Class A, FCC Part 15, Class B		
Transient immunity	Telcordia GR-499-Core, Section 13-2,		
	ETS 300 386-1, Class 2		
Mini package	2.28" x 2.2" x 0.5"		
dimensions	(57,9 x 55,9 x 12,7 mm)		

#### General Performance Not for design use; see data sheet Part Numbering Ordering, see back cover for contacts

INIL-COTS	versi
<u>Available</u>	
Page 36	

<u>rsion</u>



<sup>[a]</sup> T-Grade storage temp. is -40°C; H-Grade storage temp. is -55°C

#### Web ExpressCode: iam

RoHS

### Input Attenuator Module IAM

The IAM provides EMI filtering and transient protection for industrial and communications applications, using VI-200 and VI-J00 Series modules.

#### **Features**

- Meets Telcordia & British Telecom standards for EMI/RFI
- Meets Telcordia, IEC and British Telecom standards for transients
- Agency approvals: cULus, cTÜVus, CE Marked
- Efficiency: 97%
- Input reverse polarity protection
- Dimensions: 2.28" x 2.4" x 0.5" (57,9 x 61,0 x 12,7 mm)

#### IAM Models & General Performance

		Input Voltage			
Model	Min.	Тур.	Max.	Output Power	
VI-A11-CU	21 Vdc	24 Vdc	32 Vdc	200 W	
VI-AWW-CU	18 Vdc	24 Vdc	36 Vdc	200 W	
VI-A33-CQ	42 Vdc	48 Vdc	60 Vdc	400 W	
VI-ANN-CQ	36 Vdc	48 Vdc	76 Vdc	400 W	
VI-A66-CQ	200 Vdc	300 Vdc	400 Vdc	400 W	

. . .

RoHS compliant versions begin with "VE-". For example: VE-A33-CQ

24 U.S. & CANADA: 800-735-6200 VICORPOWER.COM

Consult back cover for a complete list of contacts.



**MIL-COTS Version Available** Page 36

Web ExpressCode: fiam

RoHS





## **DC-DC** Filters


### **RAM** Ripple Attenuator Module

Combining active and passive filtering, the RAM attenuates both low-frequency input power source fundamental and harmonics, and high-frequency switching components in the frequency range of DC to 20 MHz, while exhibiting efficiencies of 93 – 99%. No adjustments are required, and remote sense and output voltage trim features are retained.


### Features

- Reduces output ripple to <3 mV pp (VI-200)</li>
- Compatible with VI-200 / VI-J00 based products: 5 50 Vdc output
- Full attenuation up to 20 A
- No adjustments required .
- Efficiency: 93 99%
- Converter sense, trim, overvoltage, and overcurrent retained .
- Dimensions: 2.28" x 2.4" x 0.5" (57,9 x 61,0 x 12,7 mm)
- CE Marked


Typical Configuration Not for design use; see data sheet







#### Part Numbering Ordering, see back cover for contacts




## Output Ripple Attenuator Module MicroRAM

Combines both active and passive filtering to achieve greater than 40 dB of noise attenuation from 60 Hz to 1 MHz.

#### **Features**


- Integrated ORing diode supports N+1 redundancy
- >40 dB ripple attenuation from 60 Hz to 1 MHz
- Significantly improves load transient response .
- Reduces ripple to less than 10 mV peak to peak .
- Efficiency: Up to 98% .
- 20 and 30 Amp ratings
- 3 30 Vdc input range .
- Dimensions: 2.28" x 1.45" x 0.5" (57,9 x 36,8 x 12,7 mm) .
- Compatible with Vicor's DC-DC converters

Typical Configuration Not for design use; see data sheet





**Part Numbering** Ordering, see back cover for contacts





#### Web ExpressCode: uram

RoHS

25 U.S. & CANADA: 800-735-6200 VICORPOWER COM

Consult back cover for a complete list of contacts.

Web ExpressCode: ram

## Active Filters QPI Family

### QPI-3LZ through QPI-12LZ Active EMI Filters

The QPI family of active EMI filters provides conducted common-mode (CM) and differentialmode (DM) attenuation from 150 kHz to 30 MHz (CISPR22 range). The proprietary active filtering circuit provides superior attenuation at low frequencies intended to support EN Class B limits, including PICMG<sup>®</sup> 3.0 for ATCA.

Models QPI-3LZ through QPI-8LZ are designed to work with most switch-mode power supplies. The QPI-9LZ through QPI-12LZ products are designed specifically for use with Vicor's V•I Chip power conversion products.

The QPI series are SiP (System-in-Package) solutions with Land Grid Array (LGA) mounting. The QPI-3LZ through QPI-10LZ are full size  $25 \times 25 \times 4,5$  mm packages and the QPI-11LZ and QPI-12LZ are half-size  $12,5 \times 25 \times 4,5$  mm packages. The QPI series is also available in an open frame SiP platform by ordering with the "-01" suffix.

#### Features

- 24/28 V and 48/60 V models
- Efficiency: >99% at full load
- High density, low profile surface mount LGA package
- Integrated Hot-Swap in selected models

# Supports PICMG<sup>®</sup> 3.0 ATCA requirements Compatible with most DC-DC converters

- –40°C to +100°C PCB temperature
- TÜV approved







QPI Evaluation Boards Available pg. 47

For more information, go to picorpower.com


#### **Part Numbering**

	5						
Part Number (-01 = Open Frame) <sup>[a]</sup>	Input Voltage	Nominal Range	Current Rating	CM Attenuation @ 250 kHz	DM Attenuation @ 250 kHz	Hipot	Hot-Swap
QPI-3LZ	24/28 Vdc	10 – 40 Vdc	7 A	60 dB	80 dB	707 Vdc	N/A
QPI-3LZ-01	24/28 Vdc	10 – 40 Vdc	7 A	60 dB	80 dB	707 Vdc	N/A
QPI-4LZ	48/60 Vdc	30 – 80 Vdc	7 A	40 dB	70 dB	1,500 Vdc	N/A
QPI-4LZ-01	48/60 Vdc	30 – 80 Vdc	7 A	40 dB	70 dB	1,500 Vdc	N/A
QPI-5LZ	24/28 Vdc	10 – 40 Vdc	14 A	60 dB	80 dB	707 Vdc	N/A
QPI-5LZ-01	24/28 Vdc	10 – 40 Vdc	14 A	60 dB	80 dB	707 Vdc	N/A
QPI-6LZ	48/60 Vdc	30 – 80 Vdc	14 A	40 dB	80 dB	1,500 Vdc	N/A
QPI-6LZ-01	48/60 Vdc	30 – 80 Vdc	14 A	40 dB	80 dB	1,500 Vdc	N/A
QPI-7LZ	24/28 Vdc	18 – 38 Vdc	6 A	50 dB	80 dB	707 Vdc	Yes
QPI-7LZ-01	24/28 Vdc	18 – 38 Vdc	6 A	50 dB	80 dB	707 Vdc	Yes
QPI-8LZ	48/60 Vdc	32 – 76 Vdc	6 A	40 dB	70 dB	1,500 Vdc	Yes
QPI-8LZ-01	48/60 Vdc	32 – 76 Vdc	6 A	40 dB	70 dB	1,500 Vdc	Yes
V•I Chip Specific Mode	ls		@ 1 MHz	@ 1 MHz			
QPI-9LZ	24/28 Vdc	18 – 38 Vdc	6 A	65 dB	80 dB	707 Vdc	Yes
QPI-9LZ-01	24/28 Vdc	18 – 38 Vdc	6 A	65 dB	80 dB	707 Vdc	Yes
QPI-10LZ	48/60 Vdc	32 – 76 Vdc	6 A	45 dB	70 dB	1,500 Vdc	Yes
QPI-10LZ-01	48/60 Vdc	32 – 76 Vdc	6 A	45 dB	70 dB	1,500 Vdc	Yes
QPI-11LZ	24/28 Vdc	5 – 50 Vdc	7 A <sup>[b]</sup>	65 dB	80 dB	707 Vdc	N/A
QPI-11LZ-01	24/28 Vdc	5 – 50 Vdc	7 A <sup>[b]</sup>	65 dB	80 dB	707 Vdc	N/A
QPI-12LZ	48/60 Vdc	10 – 80 Vdc	7 A <sup>[b]</sup>	45 dB	70 dB	1,500 Vdc	N/A
QPI-12LZ-01	48/60 Vdc	10 – 80 Vdc	7 A <sup>[b]</sup>	45 dB	70 dB	1,500 Vdc	N/A

<sup>(a)</sup> Open-frame units are compatible with aqueous cleaning processes.

<sup>[b]</sup> Parallelable for up to 12 A.


#### Typical Configuration Not for design use; see data sheet



26 U.S. & CANADA: 800-735-6200 VICORPOWER.COM

Consult back cover for a complete list of contacts.

### Performance



Conducted EMI scans showing QPI performance. Blue trace = no QPI; Red trace = with QPI.

## Active Filters QPO Family

### **QPO-1LZ / QPO-2LZ** Output Ripple Attenuator

The QPO output ripple attenuator products use proprietary active filtering to reduce power supply output ripple and noise (PARD) over 30 dB from 1 kHz to 500 kHz. QPOs improve transient response and ensure quiet point-of-load regulation. They also reduce the number of output capacitors to support dynamic loads. QPOs work with most DC-DC converters and switching power supplies. Output regulation is maintained using remote sensing or the trim input of the power supply.

#### Features


- >30 dB PARD attenuation, 1 kHz to 500 kHz
- Supports precise point-of-load regulation
- Efficiency: Up to 99%
- High density, low profile LGA package
- Reduces required number of output capacitors to support dynamic loads
- User selectable optimization of attenuation, power dissipation, and transient load response
- Compatible with most DC-DC converters

#### **Part Numbering**

Part Number (-01 = Open Frame) <sup>[a]</sup>	Input Voltage	Current Rating	Attenuation
QPO-1LZ	3 – 30 Vdc	10 A	> 30 dB PARD attenuation, 1 kHz to 500 kHz
QPO-1LZ-01	3 – 30 Vdc	10 A	> 30 dB PARD attenuation, 1 kHz to 500 kHz
QPO-2LZ	0.3 – 5.5 Vdc	20 A	> 20 dB PARD attenuation, 1 kHz to 500 kHz, Aux. Bus biased
QPO-2LZ-01	0.3 – 5.5 Vdc	20 A	> 20 dB PARD attenuation, 1 kHz to 500 kHz, Aux. Bus biased

<sup>[a]</sup> Open-frame units are compatible with aqueous cleaning processes.


#### **Typical Application**







#### Performance



Web ExpressCode: **qpo** 

U.S. & CANADA: 800-735-6200 VICORPOWER.COM 27 Consult back cover for a complete list of contacts.

## AC-DC Configurable Power Supplies

### FlatPAC Family 50 – 600 Watt Power System

The FlatPAC is a complete, low-profile, agency-approved switching power supply. It combines Vicor's VI-200 Series of DC-DC converters and frontend subassemblies to provide from 50 – 600 W of output power from one to three outputs.

The FlatPAC design provides rapid turnaround on standard models. FlatPAC is available with <u>BatMod current source module, Page 23</u>.

#### Features

- Microprocessor-controlled front end
- Inputs: 115/230 Vac, autorangingFCC Part 15, Class B,
- EN55022, Class B
- 40 ms hold up
- Agency approvals: cULus, cTÜVus, CE Marked
- Module disable
- BUS OK and AC OK

- Finned or conduction-cooled package
- 22 Standard output voltages from 1 – 95 Vdc
- Low-noise ZCS / ZVS power topology
- Transient surge: EN61000-4-5
- Low profile only 1.37" (34,7 mm)
- Custom output voltages also available
- BatMod current-source option available

#### General Performance Refer to data sheet for specifications

Parameter	Specification			
Number of outputs	1 to 3			
Output power	Up to 600 W			
Input voltage	90 – 132 Vac / 180 – 264 Vac			
input voltage	47 – 63 Hz (400 Hz available; contact factory)			
Conducted EMI	EN/FCC "B"			
Set point	±1% max. (E-Grade 2%)			
Load / line regulation	0.2% max. (E-Grade 0.5%)			
Output ripple (pp)	150 mV or 3% max. (E-Grade 5%)			
Trim range <sup>[a]</sup>	50 – 110%			
Remote sense range	0.5 Vdc max.			
OVP set point	125% typical			
Current limit	115%			
Maximum temperature	0 to 85°C baseplate			
[a] 10, 12 and 15 V outputs, standar	d trim range $\pm 10\%$			

<sup>[a]</sup> 10, 12 and 15 V outputs, standard trim range  $\pm$  10%.

Consult factory for wider trim range.

## Part Numbering

VI – (VE) = RoHS Compliant	Μ	U	3		-	С	Q		
•	Family	Input	Out 1	Out 2 <sup>[b]</sup>	Out 3 <sup>[c]</sup>	Grade	Power 1	Power 2 [b]	Power 3 <sup>[c]</sup>
	L = Single	U = Autoranging	Z = 2 V	M = 10 V	K = 40 V	E = 0°C	M = 600 W	U = 200 W	U = 200 W
	M = Single	90 – 132 and	Y = 3.3 V	1 = 12 V	4 = 48 V	$C = 0^{\circ}C$	P = 450 W	V = 150 W	V = 150 W
	N = Single	180 – 264 Vac	0 = 5 V	P = 13.8 V	H = 52 V	I = -30°C	Q = 400 W	W = 100 W	W = 100 W
	P = Dual		X = 5.2 V	2 = 15 V	F = 72 V		S = 300 W	X = 75 W	X = 75 W
	Q = Dual		W = 5.5 V	N = 18.5 V	D = 85 V		U = 200 W	Y = 50 W	Y = 50 W
	R = Triple		V = 5.8 V	3 = 24 V	B = 95 V		V = 150 W		
			T = 6.5 V	L = 28 V			W = 100 W		
			R = 7.5 V	J = 36 V			X = 75 W		
			All voltages a	vailable for out	put 1, 2, or 3		Y = 50 W		

For conduction-cooled package add –CC to the part number. For example, VI–LU0–CV–CC. <sup>[b]</sup> For P, Q, R, PJ, and RJ only. Refer to output configuration chart above. <sup>[c]</sup> For R and RJ only. Refer to output configuration chart above.



### **Chassis Configurations**

- Single output
- 50 200 Watts
- 9.25" x 2.5" x 1.37" (234,8 x 63,5 x 34,8 mm)



- Single or dual outputs
- 100 400 Watts
- 9.25" x 4.9" x 1.37"
   (234,8 x 124,5 x 34,8 mm)



- Single, dual or triple outputs
- 150 600 Watts
- 9.25" x 7.3" x 1.37" (234,8 x 185,4 x 34,8 mm)

28 U.S. & CANADA: 800-735-6200 VICORPOWER.COM

Web ExpressCode: flatpac

## AC-DC Configurable Power Supplies

### PFC FlatPAC Single Output Power System \_

The PFC FlatPAC uses Vicor's field-proven VI-HAM and Maxi DC-DC converters to deliver up to 575 watts of clean, reliable power. The PFC FlatPAC is a single-output power supply available with standard output voltages from 3.3 – 54 Vdc. It operates from an input of 85 – 264 Vac, includes active power factor correction (0.99 power factor), and meets EN61000-3-2 harmonic current limits. Internal filtering provides compliance to EN55022-A conducted EMI. It is available in Vicor's low profile 1.37" (34,8 mm) FlatPAC chassis, in either finned or conduction-cooled (CC) versions.

#### **Features**

- Input: 85 264 Vac
- Power factor: 0.99
- Single output: Up to 80 A or 575 W, 3.3 – 54 Vdc
- Low profile package: 1.37" x 4.9" x 9.25" (34,8 x 124,4 x 235 mm)
- Safety agency approvals: cULus, cTÜVus, CE Marked
- High efficiency
- Remote sense
- Current limit
- Thermal shut down
- OVP

#### Web ExpressCode: pfcflatpac

RoHS



<b>General Performance</b>	Refer to data sheet for detailed specifications
----------------------------	---

Parameter	Rating	Unit	Notes	
Input				
Voltage	85 – 264	Vac		
Frequency	47 – 63	Hz		
Trequency	47 – 440	Hz	I-Grade	
Regulation line / load	0.5	%	10 to 100% load	
Mechanical				
Weight	44.8 (1,304)	oz (g)		
Dimensions	1.37 x 4.9 x 9.25	inches		
Dimensions	24,8 x 1,244 x 235	mm		
Operating temperature (case)				
C-Grade and E-Grade	0 to +85	°C		
I-Grade	-30 to +85	°C		
Storage temperature (case)				
E-Grade	-10 to +100	°C		
C-Grade	-30 to +100	°C		
I-Grade	-55 to +100	°C		

#### Part Numbering Ordering, see back cover for contacts

I - C	M U 3	- C	<b>M</b> -	
<b>Input</b> Universal 85 – 264 Vac	$\begin{array}{c c} \textbf{Output Voltage} \\ Y = 3.3 \ V & 3 = 24 \ V \\ 0 = 5.0 \ V & L = 28 \ V \\ 1 = 12 \ V & J = 36 \ V \\ 2 = 15 \ V & 4 = 48 \ V \\ G = 54 \ V \end{array}$	<b>Product Grade (°C)</b> E = 0 to 85°C case C = 0 to 85°C case I = −30 to 85°C case	Output Power           Vout = ≤5 V         Vout ≥12 V           Q = 80 A         M = 575 W	Options -CC = Conduction Cooled

## **AC-DC** Configurable Power Supplies

### **VIPAC Power System** Choice of Chassis Configurations

The VIPAC is an integrated power system leveraging the latest advances in DC-DC converter technology and modular front ends. VIPAC combines application-specific power processing units (PPU), a choice of chassis styles and remotely located hold-up capacitors to provide fast, flexible, and highly reliable power solutions for a wide range of demanding applications.

The PPU is the core element of the system and incorporates Vicor's autoranging FARM modular front end to provide transient protection, EMI filtering, and inrush current limiting. The PowerBench VIPAC Design Center enables designers to configure the PPU with up to three independently regulated outputs having power levels from 50 – 500 W and with as much as 900 W total output power.

#### Features

- AC input: 115/230 Vac autoranging, 47 – 440 Hz
- Output voltages: 2 48 Vdc 50 - 900 Watts total; 1, 2, or 3 outputs
- Protective features: Inrush current limiting Input transient protection EMI filtering

 Local or remote control Package style:

LugMate or PlugMate

Choice of output terminations:

- Low-profile coldplate Optional finned heat sink Agency approvals:
- cULus, cTÜVus, CE Marked

Configure Your VIPAC Power System Online PO ERBENCH


vicorpower.com/vcad

#### Chassis Configurations Dimensions vary with specific model configurations

3 Micros

- Dual or triple output
- Up to 450 W
- 4.96" x 6.8" x 0.75"<sup>[a]</sup>
- (126,0 x 172,7 x 19,0 mm)





2 Minis

2 Maxis

Up to 900 W

- Single or dual output
- Up to 500 W
- 4.96" x 6.8" x 0.75"<sup>[a]</sup> (126,0 x 172,7 x 19,0 mm)

Single or dual output

■ 4.96" x 9.15" x 0.75"<sup>[a]</sup>

(126,0 x 232,4 x 19,0 mm)







- 2 Micros
- Single or dual output Up to 300 W
- 3.15" x 6.8" x 0.75"<sup>[a]</sup> (80,0 x 172,7 x 19,0 mm)

#### 1 Mini

- Single output
- Up to 250 W
- 3.15" x 6.8" x 0.75"<sup>[a]</sup> (80,0 x 172,7 x 19,0 mm)

#### 1 Maxi

- Single output
- Up to 500 W
- 3.15" x 9.15" x 0.75"<sup>[a]</sup> (80,0 x 232,4 x 19,0 mm)

#### 1 Micro

- Single output
- Up to 150 W
- 3.15" x 6.8" x 0.75"<sup>[a]</sup>
- (80,0 x 172,7 x 19,0 mm)

<sup>[a]</sup> PluaMate version is 0.81" (20,5 mm) in height

Web ExpressCode: vipac



### **DC-DC** Configurable Power Supplies

#### VIPAC Arrays DC Input Power System • 1 – 4 Outputs

The VIPAC Arrays are a highly flexible system of DC input power building blocks which can be configured with as many as four user-definable outputs on a low-profile, coldplate chassis. Using Vicor's VCAD design tool (vicorpower.com/vcad), designers are able to specify VIPAC Arrays with inputs of 24, 28, 48, 72, 110, 150, 300, 375 Vdc and outputs from 2 to 54 Vdc at power levels up to 600 watts per output. VIPAC Arrays are ideal for use in distributed and modular power systems where power density and reliable operation are critical. A current share option is available on single output models enabling them to be used in applications requiring high power / redundancy. Fully connectorized input and output terminations speed system installation and a versatile coldplate chassis simplifies thermal management.

#### Features

- Input voltage: 24, 28, 48, 72, 110, 150, 300 or 375 V
- Booster versions for higher output current applications
- Agency approvals: cTÜVus, CE Marked (300, 375 Vdc inputs only)

MIL-COTS Version Available

<u>Page 37</u>

RoHS-compliant versions can be selected with the VIPAC Design Tool.

Web ExpressCode: vipacarray

RoHS

Configure Your VIPAC Array Power System Online

Chassis Configurations Dimensions vary with specific model configurations

	<ul> <li>2 Minis</li> <li>Single or dual outputs</li> <li>Up to 600 W total</li> <li>3.62 " x 6.69 " x 0.78"<sup>[a]</sup> (92,0 x 170,0 x 19,8 mm)</li> </ul>	<ul> <li>1 Micro, 2 Minis</li> <li>Dual or triple outputs</li> <li>Up to 750 W total</li> <li>3.62 " x 7.52 " x 0.78 "<sup>[a]</sup> (92,0 x 191,0 x 19,8 mm)</li> </ul>
	<ol> <li>Mini, 2 Micros</li> <li>Single, dual or triple outputs</li> <li>Up to 600 W total</li> <li>3.62" x 6.69" x 0.78"<sup>[a]</sup> (92,0 x 170,0 x 19,8 mm)</li> </ol>	<ul> <li>4 Micros</li> <li>Dual, triple or quad outputs</li> <li>Up to 600 W total</li> <li>3.62" x 7.52" x 0.76"<sup>[a]</sup> (92,0 x 191,0 x 19,3 mm)</li> </ul>
	<ul> <li>3 Micros</li> <li>Dual or triple outputs</li> <li>Up to 450 W total</li> <li>3.62" x 6.69" x 0.76"<sup>[a]</sup> (92,0 x 170,0 x 19,3 mm)</li> </ul>	<ol> <li>Mini</li> <li>Single output</li> <li>Up to 300 W</li> <li>Current share option</li> <li>3.62" x 4.39" x 0.78"<sup>[a]</sup> (92,0 x 112,0 x 19,8 mm)</li> </ol>
(a) PlugMate version is 0.81" (20,5 mm) in height	<ol> <li>Maxi</li> <li>Single output</li> <li>Up to 600 W</li> <li>Current share option</li> <li>3.62 " x 6.69 " x 0.78"<sup>[a]</sup> (92,0 x 170,0 x 19,8 mm)</li> </ol>	<ul> <li>2 Micros</li> <li>Single or dual outputs</li> <li>Up to 300 W total</li> <li>3.62" x 4.39" x 0.78"<sup>[a]</sup> (92,0 x 112,0 x 19,8 mm)</li> </ul>

U.S. & CANADA: 800-735-6200 VICORPOWER.COM 31

### **DC-DC** Configurable Power Supplies

#### ComPAC Family 50 – 600 Watt Input Power System

ComPAC delivers up to 600 W from one, two, or three outputs in a package just 0.99" (25,2 mm) in height with the field proven performance, high efficiency and high reliability inherent in Vicor's component level power converters. ComPAC meets British Telecom and European Norms for input surge withstand and meets conducted emissions of EN55022, Class B. ComPAC is offered with input voltage ranges optimized for industrial and telecommunication applications and provides extended input overvoltage capability, input reverse polarity protection, undervoltage lockout, and master disable. ComPAC is available with <u>BatMod current source module, Page 23</u>.

#### Features

- Inputs: 24, 48, and 300 Vdc
- Any output: 1 95 Vdc
- Agency approvals: cULus, cTÜVus, CE Marked
- Efficiency: 80 90%
- Up to 10 W/in<sup>3</sup>
- EMI / RFI specifications: Telcordia TR-TSY-000513, British Telecom BTR 2511
- EN55022, Class B: Conducted emissions
- Input surge withstand: British Telecom BTR 2511, EN61000-4-5
- Low-noise ZCS / ZVS power topology
- Optional high-performance heat sink
- Finned or conduction-cooled package



MIL-COTS Version Available Page 37

Web ExpressCode: **compac** 

#### **Chassis Configurations**

Single output50 – 200 Watts

#### **General Performance** Refer to data sheet for specifications

Parameter	Designator	Rating	Unit
	1	21 – 32	Vdc
	W	18 – 36	Vdc
Input voltage range	3	42 – 60	Vdc
	Ν	36 – 76	Vdc
	6	200 - 400	Vdc
Outputs		1, 2 or 3	
Output power		50 - 600	Watts
Output voltage(s)		1 – 95	Vdc
Operating temperature (case)			
E-Grade		-10 to +85	°C
C-Grade		–25 to +85	°C
I-Grade		-40 to +85	°C
M-Grade		–55 to +85	°C



9.25" x 2.5" x 0.99" (234,8 x 63,5 x 25,2 mm)

- Single or dual outputs
- 100 400 Watts
- 9.25" x 4.9" x 0.99"
   (234,8 x 124,5 x 25,2 mm)



- Single, dual, or triple outputs
- 150 600 Watts
- 9.25" x 7.3" x 0.99" (234,8 x 185,4 x 25,2 mm)

#### Part Numbering

VI-	Ν	C 3	4		-	С	Μ			
(VE) = RoHS	Family	Input	Out 1	Out 2 [a]	Out 3 [b]	Grade	Power 1	Power 2 <sup>[a]</sup>	Power 3 [b]	
Compliant	L = Single	$1 = 24 V^{[c]}$	Z = 2 V	M = 10 V	K = 40 V	E = -10°C	M = 600 W	U = 200 W	U = 200 W	
	M = Single	W = 24 V	Y = 3.3 V	1 = 12 V	4 = 48 V	C = -25°C	P = 450 W	V = 150 W	V = 150 W	
	N = Single	3 = 48 V	0 = 5 V	P = 13.8 V	H = 52 V	$I = -40^{\circ}C$	Q = 400 W	W = 100 W	W = 100 W	
	P = Dual	N = 48 V	X = 5.2 V	2 = 15 V	F = 72 V	$M = -55^{\circ}C$	S = 300 W	X = 75 W	X = 75 W	
	Q = Dual	6 = 300 V	W = 5.5 V	N = 18.5 V	D = 85 V		U = 200 W	Y = 50 W	Y = 50 W	
	R = Triple		V = 5.8 V	3 = 24 V	B = 95 V		V = 150 W			l
			T = 6.5 V	L = 28 V			W = 100 W			
			R = 7.5 V	J = 36 V			X = 75 W			[]
			All voltages a	vailable for out	put 1, 2, or 3		Y = 50 W			[0

Note: For conduction-cooled package add -CC to the part number. For example, VI-LWX-CV-CC.

- <sup>[a]</sup> For P, Q, R, PJ, and RJ only. Refer to output configuration chart.
- <sup>[b]</sup> For R and RJ only. Refer to output

configuration chart . <sup>[c]</sup> Max output power / module 150 W.

# **DC-DC** Configurable Power Supplies

### MegaMod Family Chassis–Mount VI-200 / VI-J00 Converters

MegaMod and MegaMod Jr. DC-DC converters incorporate one, two, or three Vicor VI-200 or VI-J00 converters in a modular package to provide a chassis-mounted alternative to board-mounted power supplies. MegaMods offer 50 – 600 W of power from 1 – 3 outputs. MegaMod Jrs. offer a total of 25 – 300 W from 1 – 3 outputs. Each output may be independently sensed, adjusted, and sequenced using the procedures outlined for VI-200 and VI-J00 converters in the Vicor Applications Manual. Download a PDF of the manual from the library section of vicorpower.com.

#### **Features**

- Inputs: 10 400 Vdc
- Any output: 1 95 Vdc
- Agency approvals: cULus, cTÜVus, CE Marked
- Efficiency: 80 90% (typical)
- Up to 27 W/in<sup>3</sup>
- Low profile: 0.62 " (15,7 mm) high

#### **Chassis Configurations**

#### Input Selection

12

18

24

36

48


72

110

150

300

150/300




- Temperature grades (MegaMod Jr.):  $E = -10 \text{ to } +85^{\circ}C (+100^{\circ}C)$  $C = -25 \text{ to } +85^{\circ}C (+100^{\circ}C)$  $I = -40 \text{ to } +85^{\circ}\text{C} (+100^{\circ}\text{C})$  $M = -55 \text{ to } +85^{\circ}\text{C} (+100^{\circ}\text{C})$
- ZCS power architecture

Package

Booster versions available for expanded output power (MegaMod only)



**MIL-COTS Version Available** Page 37



#### **Output Power**

- Single output
- 50 200 Watts MegaMod: L
- 25 100 Watts MegaMod Jr.: LJ
- Single or dual outputs
- 100 400 Watts MegaMod: M, P
- 50 200 Watts MegaMod Jr.: PJ
- Single, dual or triple outputs
- 100 600 Watts MegaMod: N, Q, R
- 75 300 Watts MegaMod Jr.: RJ

#### Part Numbering

VI -	L	1	3			- <b>E</b>	V			
(VE) = RoHS	Family	Input Voltage	Out 1	Out 2 <sup>[a]</sup>	Out 3 <sup>[b]</sup>	Grade	Power 1	Power 2 [a]	Power 3 [b]	
Compliant	L = Single	0 = 12 (10-20)	Z = 2 V	M = 10 V	K = 40 V	E = -10°C	M = 600 W	U = 200 W	U = 200 W	
	M = Single	V = 24 (10-36)	Y = 3.3 V	1 = 12 V	4 = 48 V	C = -25°C	P = 450 W	V = 150 W	V = 150 W	
	N = Single	1 = 24 (21-32) <sup>[c]</sup>	0 = 5 V	P = 13.8 V	H = 52 V	I = -40°C	Q = 400 W	W = 100 W	W = 100 W	
	P = Dual	W = 24 (18-36)	X = 5.2 V	2 = 15 V	F = 72 V	M= -55°C	S = 300 W	X = 75 W	X = 75 W	
	Q = Dual	2 = 36 (21-56)	W = 5.5 V	N = 18.5 V	D = 85 V		U = 200 W	Y = 50 W	Y = 50 W	
	R = Triple	3 = 48 (42-60)	V = 5.8 V	3 = 24 V	B = 95 V		V = 150 W	Z = 25 W	Z = 25 W	
	LJ = Single	N = 48 (36-76)	T = 6.5 V	L = 28 V			W = 100 W			
	PJ = Dual	4 = 72 (55-100)	R = 7.5 V	J = 36 V			X = 75 W			<sup>[a]</sup> For P, Q, R, PJ, and RJ only. Re
	RJ = Triple	T = 110 (66-160)					Y = 50 W			output configuration chart.
		5 = 150 (100-200)					Z = 25 W			<sup>[b]</sup> For R and RJ only. Refer to out
		6 = 300 (200-400)								configuration chart.
		7 = 150 (100-375)	All voltages a	available for out	put 1, 2, or 3					<sup>[c]</sup> Max output power / module 1

#### Web ExpressCode: megamod

### MIL-COTS V-I Chips

#### Web ExpressCode: mvichips DC-DC V-I Chip Modules 28 V Regulator, Voltage Transformer, & Bus Converter \_

VTMs put isolated current multiplication and voltage division directly at the point of load (POL), and an upstream PRM (Regulator) controls the factorized bus voltage supplied to the VTM to provide line and load regulation. Together, the PRM and VTM chip set provides the full functionality of a DC-DC converter, but with breakthrough performance and flexibility in a rugged, miniature package. The BCM (Bus Converter Module) functions as a fixed-ratio DC-DC transformer and provides an isolated bus voltage to power the PRM and VTM chip set or other loads.

The MIL-COTS PRM operates from a wide input range of 16 – 50 Vdc, meeting many of the ground vehicle and airborne requirements of MIL-STD-1275 and MIL-STD-704. Rated for 120 W, the 28 V PRM produces a nominal factorized bus voltage of 36 Vdc, controllable over the range of 26 – 50 Vdc. The downstream isolated VTM is available with twelve voltage division ratios from 1:1 to 1:32 and provides the user with flexibility to supply up to 100 A or 120 W at any output voltage from 1 – 50 Vdc in a surface-mount package occupying only 1 in<sup>2</sup>. The MIL-COTS BCM is a high efficiency Sine Amplitude Converter (SAC) operating from a 240 to 330 Vdc primary bus to deliver an isolated 30 – 41.2 V nominal, unregulated secondary.

#### **Features for PRM**

- Input range: 16 50 Vdc
- 1.3 MHz switching frequency
- Efficiency: 95%
- -55°C to +125°C operation (Tj)
- ZVS buck-boost regulator

#### **Features for VTM**

- Isolated 1–50 Vdc output
- 1 µs transient response
- 3 MHz switching frequency
- Efficiency: Up to 96.5%
- –55 to +125°C operation (Tj)

#### **Features for BCM**

- Input range: 240 330 Vdc
- Output range: 30.0 41.2 Vdc
- MIL-STD-704E/F Compliant
- Efficiency: >95%
- –55 to +125°C operation (Tj)

#### Web ExpressCode: mvib

### MIL-COTS VI BRICKS PRM / VTM Thermally Enhanced Package

The **PRM** Regulator Module is a very efficient non-isolated regulator specifically designed to provide a controlled Factorized Bus distribution voltage for powering downstream VI BRICK Voltage Transformation Modules. In combination, VI BRICK PRMs and VTMs form a complete DC-DC converter subsystem offering all of the unique benefits of Vicor's Factorized Power Architecture (FPA): high density and efficiency; low noise operation; architectural flexibility; extremely fast transient response; elimination of bulk capacitance at the point of load (POL); in a thermally enhanced package.

#### MQPI-18 Input EMI Filter

34

The MQPI-18 is a surface mount DC front-end filter that provides EMI filtering for Vicor's 28 V DC-DC V-I Chip or VI BRICK modules. The MQPI-18 enables designers to meet conducted emission / conducted susceptibility per MIL-STD-461E. The MQPI-18 accepts an input voltage of 10 – 80 Vdc and delivers output current up to 7 A.



The thermally enhanced **VTM** voltage transformer excels at speed, density and efficiency to meet the demands of advanced power applications. Combined with the PRM regulator they create a DC-DC converter with flexibility to provide isolation and regulation where needed. The PRM

can be located with the VTM at the point of load or remotely in the back plane or on a daughtercard.




### **MIL-COTS Product Catalog**

This document provides in-depth information on Vicor's line of MIL-COTS standard products, including DC-DC converters, custom solutions, and technical support.

- Environmental stress screening and MTBF
- Environmental gualification
- Custom configured modules
- Field tested... proven reliability

#### Visit vicorpower.com

to view the Military Catalog online. This will give you instant access to all technical documentation for a MIL-COTS product.









### MIL-COTS BRICKs / Front ends

#### Maxi, Mini & Micro Series DC-DC Converter Modules

Web ExpressCode: mbricks2

These high-density DC-DC power converters are available in three rugged packages with output power up to 600 W. Standard inputs of 24, 28, 48, 72, 110, 150, 300, and 375 Vdc; and outputs from 1 - 48 Vdc, make these converters extremely flexible for MIL-COTS applications.

#### Features

- Inputs: 24, 48, 300, and 375 Vdc
   NEW: 72, 110, 150, and wide input 28 Vdc
- Two operating temperature ratings: -40 to +100°C and -55 to +100°C
- MIL-STD-810 and MIL-STD-202 qualified
- Environmental stress screening

Final test data available at

#### vicorquality.com

#### Web ExpressCode: mbricks1

MI-200 & MI-JOO Series DC-DC Converter Modules

Vicor's field-proven MIL-COTS power components have gained a reputation for quality and reliability among military power system designers. With thousands of standard models available, designers can rapidly meet performance, schedule, and budget objectives for just about any power solution.

#### Features

- Inputs per MIL-STD-704D/E/F: 28 and 270 Vdc
- Input per MIL-STD-1399A: 155 Vdc
- Output voltages: 2 48 Vdc
- Output power: 10 100 W
- MIL-STD-810 and MIL STD-202 qualified
- NAVMAT component derating guidelines
- Power density: Up to 25 W/in<sup>3</sup>
- 75 and 100 W booster modules available

#### MI-AIM AC Front-end Module

The MI-AIM works in conjunction with Vicor's MI-x7x module family and is ideal for systems requiring AC rectification and transient protection.

#### Features

- 115 Vac nom, 60/400 Hz operation
- MIL-STD-461D EMI (CE102) @ 60 Hz
- MIL-STD-704A transient protection
- MIL-STD-810 and MIL-STD-202 qualified



### MIL-COTS Filters

#### MicroRAM Output Ripple Attenuator Module \_

Vicor's MicroRAM output ripple attenuation module combines both active and passive filtering to achieve greater than 40 dB of noise attenuation from 60 Hz to 1 MHz. The MicroRAM operates over a range of 3 - 30 Vdc, is available in either 20 or 30 A models, and is compatible with all Vicor DC-DC converters.

#### Features

- >40 dB ripple attenuation from 60 Hz to 1 MHz
- 20 and 30 Amp ratings
- Operation: –55°C
- Input: 3 30 Vdc

#### M-FIAM Filter Input Attenuator Module

The M-FIAM is a DC front-end module that provides EMI filtering and transient protection. The M-FIAM3 and 5B enables designers using Vicor 24 and 300 V Maxi, Mini and Micro DC-DC converters to meet conducted emission / susceptibility per MIL-STD-461E and input transients per MIL-STD-704E/F. The M-FIAM7, compatible with 28 Vdc V•I Chip modules, and the M-FIAM9, compatible with Vicor's V24 and V28 DC-DC converters, are compliant to MIL-STD-461E, MIL-STD-704A-F, MIL-STD-1275A/B/D and DO-160E.

#### Features

#### M-FIAM3, M-FIAM5B & M-FIAM9

- MIL-STD-461E conducted emissions / susceptibility
- MIL-STD-704E/F transient protection
- MIL-STD-704A-F & MIL-STD-1275A/B/D transient protection (M-FIAM9)
- Compatible with 24, 28 & 300 Vdc input Maxi, Mini & Micro DC-DC converters

#### M-FIAM7

- MIL-STD-461E conducted emissions / susceptibility
- MIL-STD-704A-F, MIL-STD-1275A/B/D & DO-160E transient protection
- Compatible with 28 Vdc V•I Chip modules

#### MVA-FIAM5B & MVA-FIAM9

Coldplate connector mounting option for M-FIAM5B and M-FIAM9

#### **MI-IAM** Input Attenuator Module

The MI-IAM provides EMI filtering to MIL-STD-461C/D/E and transient protection to the most severe levels of MIL-STD-704A-F, MIL-STD-1275A/B/D and DO-160E using MI-200 or MI-J00 DC-DC converters.

#### Features

- Input: 28 or 270 Vdc
- MIL-STD-704A-F, MIL-STD-1275A/B/D & DO-160E transient protection
- MIL-STD-461C/D/E conducted emissions / susceptibility
- MIL-STD-810 and MIL-STD-202 qualified
- Compatible with MI-200 and MI-J00 DC-DC converters



Web ExpressCode: miam

Web ExpressCode: **mfiam** 

#### Web ExpressCode: muram



### **MIL-COTS** Configurable Power Supplies

#### **MI-MegaMod Family** Chassis-Mount DC-DC Converter

DC input power converters delivering up to 300 W from one, two, or three outputs in a package just 0.62" in height.

#### Features

- Standard inputs: 28, 155 & 270 Vdc
   Power density: Up to 13.5 W/in<sup>3</sup>

- Output voltages: 2 48 Vdc
   1, 2 or 3 outputs: Up to 300 W

#### **MI-ComPAC** DC-DC Configurable Power Supply

The MI-ComPAC is a complete single, dual, or triple output DC-DC power supply that delivers up to 300 W from inputs of 28 or 270 Vdc.

#### Features

- Complete single, dual, or triple output power supply 50 - 300 W
- MIL-STD-704A-F, MIL-STD-1275A/B/D & DO-160E transient protection
- MIL-STD-461C/D/E conducted emissions / susceptibility
- Conduction-cooled models available

#### MIL-COTS VIPAC Arrays Chassis Mount DC-DC Converter

VIPAC Arrays are a highly flexible input power systems that can be configured with up to four user-defined outputs, with power capability, up to 650 W.

#### Features

- Inputs: 24, 28 & 300 Vdc
- Configurable multi outputs; Up to 650 W
- –55°C operation

–55°C operation

MIL-STD-810F shock & vibration

Profile as low as 0.75 in. (19.0 mm)

MIL-STD-810F shock & vibration

#### **28 Vdc MIL-COTS VIPAC** DC-DC Configurable Power Supply

The 28 Vdc VIPAC can be specified with up to 3 outputs in a choice of connections with voltages as low as 3.3 Vdc to as high as 48 Vdc and power levels from 50 to 400 watts per output for MIL-COTS applications.

#### Features

- 28 Vdc input
- MIL-STD-704A-F and MIL-STD-1275A/B/D input transient protection
- MIL-STD-461E EMI compliance

#### VME450<sup>™</sup> DC-DC Configurable Power Supply \_

Powered with Vicor V-I Chips, this single-slot VME power supply is small, light weight and very efficient.

#### Features

- 28 Vdc input
- MIL-STD-704A-F and MIL-STD-1275A/B/D input transient protection
- MIL-STD-461E EMI compliance

- 4 output voltages, 550 W
- -40°C to +85°C

Web ExpressCode: mvipac

Web ExpressCode: vme450



#### Consult back cover for a complete list of contacts.

### Web ExpressCode: mvipacary





Web ExpressCode: mmega

Web ExpressCode: mcompac

### AC-DC Westcor Division Configurable Power Supplies

### LoPAC Family Switcher Power Supplies

Web ExpressCode: lopac

The LoPAC Family consists of three power supplies available as one-, two-, or three-slot packages. For maximum flexibility, they are configured with standard Vicor DC-DC converters. These modules cover the entire range of outputs from 2 – 95 Vdc (higher through series arrays) and 25 – 600 W per output, as well as an array of non-standard voltages. Depending on the configuration, the LoPACs can provide up to six user-specifiable isolated outputs.

#### Features

- Near unity power factor
- Power factor corrected
- Output power: Up to 1,500 W
- Up to 6 user-specifiable outputs
- Power density: Up to 11 W/in<sup>3</sup>
- Fan cooled

- MIL- STD-810E-Vibration (PFC Mini)
- Agency approvals: UL, cTÜVus, CE Marked
- Choice of full, half, or quarter brick



LoPAC Family Accessories Page 52

Configure Your LoPAC Online

vicorpower.com/vspoc

#### **General Performance** Refer to data sheet for detailed specifications

Product	Dimensions	Input Voltage	Number of Slots	Number of Outputs	Maximum Ou @ 230 Vac	utput Power @ 115 V	Modules per Slot
PFC Mini	12.2" x 6" x 1.72" (309,9 x 152,4 x 43,6 mm)	85 – 264 Vac 100 – 380 Vdc	3	6	1,500 W	800 W	1 Full or 2 Half
PFC Micro	10.4" x 5.06" x 1.86" (264,1 x 128,5 x 47,3 mm)	85 – 264 Vac 100 – 300 Vdc	2	6	800 W	500 W	1 Full or 2 Half or 3 Quarter
PFC MicroS	7.95" x 5.06" x 1.86" (201,9 x 128,5 x 47,3 mm)	85 – 264 Vac 100 – 300 Vdc	1	3	600 W	500 W	1 Full or 2 Half or 3 Quarter

Note: For detailed information, review specific product design guides available online at vicorpower.com

#### Part Numbering Ordering, see back cover for contacts

ΡΜ	<b>X</b> <sub>1</sub> –	<b>X</b> <sub>2</sub>	<b>X</b> <sub>3</sub>	<b>X</b> <sub>4</sub> –	XXXX	-X <sub>5</sub>	- <b>X</b> <sub>6</sub>
Product Prefix PM = PFC Mini PC = PFC Micro PS = PFC MicroS	Number of Outputs 1 - 6	Number of VI-200 / VI-J00 Series Modules	Number of Maxi, Mini or Micro Series Modules	Optional Factory Assigned	Factory Assigned	Optional Factory Assigned 2 = FasTrak <sup>(a)</sup> G = RoHS	<b>Optional Codes</b> LL = Low Leakage <sup>(a)</sup> QF = Quiet Fan <sup>(a)</sup>

<sup>(a)</sup> PFC Mini Only

#### **Standard Single-Output Configurations**

Vout	Amps	Watts	PFC Micro <sup>[c]</sup>	Vout	Amps	Watts	PFC MicroS <sup>[d]</sup>	Vout	Amps	Watts
48	31.2	1,500	PC1-02B-48	48	16.7	800	PS1-01-48	48	12.5	600
28	53.6	1,500	PC1-02B-28	28	28.6	800	PS1-01-28	28	21.4	600
24	62.5	1,500	PC1-02B-24	24	33.3	800	PS1-01-24	24	25.0	600
15	100	1,500	PC1-02B-15	15	53.3	800	PS1-01-15	15	40.0	600
12	125.0	1,500	PC1-02B-12	12	66.7	800	PS1-01-12	12	50.0	600
5	240.0	1,200	PC1-02B-05	5	160.0	800	PS1-01-05	5	80.0	400
-	48 28 24 15 12	48         31.2           28         53.6           24         62.5           15         100           12         125.0	48         31.2         1,500           28         53.6         1,500           24         62.5         1,500           15         100         1,500           12         125.0         1,500	48       31.2       1,500       PC1-02B-48         28       53.6       1,500       PC1-02B-28         24       62.5       1,500       PC1-02B-24         15       100       1,500       PC1-02B-15         12       125.0       1,500       PC1-02B-12	48     31.2     1,500     PC1-02B-48     48       28     53.6     1,500     PC1-02B-28     28       24     62.5     1,500     PC1-02B-24     24       15     100     1,500     PC1-02B-15     15       12     125.0     1,500     PC1-02B-12     12	48       31.2       1,500       PC1-02B-48       48       16.7         28       53.6       1,500       PC1-02B-28       28       28.6         24       62.5       1,500       PC1-02B-24       24       33.3         15       100       1,500       PC1-02B-15       15       53.3         12       125.0       1,500       PC1-02B-12       12       66.7	48       31.2       1,500       PC1-02B-48       48       16.7       800         28       53.6       1,500       PC1-02B-28       28       28.6       800         24       62.5       1,500       PC1-02B-24       24       33.3       800         15       100       1,500       PC1-02B-15       15       53.3       800         12       125.0       1,500       PC1-02B-12       12       66.7       800	48       31.2       1,500       PC1-02B-48       48       16.7       800       PS1-01-48         28       53.6       1,500       PC1-02B-28       28       28.6       800       PS1-01-28         24       62.5       1,500       PC1-02B-24       24       33.3       800       PS1-01-24         15       100       1,500       PC1-02B-15       15       53.3       800       PS1-01-15         12       125.0       1,500       PC1-02B-12       12       66.7       800       PS1-01-12	48       31.2       1,500       PC1-02B-48       48       16.7       800       PS1-01-48       48         28       53.6       1,500       PC1-02B-28       28       28.6       800       PS1-01-28       28         24       62.5       1,500       PC1-02B-24       24       33.3       800       PS1-01-24       24         15       100       1,500       PC1-02B-15       15       53.3       800       PS1-01-15       15         12       125.0       1,500       PC1-02B-12       12       66.7       800       PS1-01-12       12	48       31.2       1,500       PC1-02B-48       48       16.7       800       PS1-01-48       48       12.5         28       53.6       1,500       PC1-02B-28       28       28.6       800       PS1-01-28       28       21.4         24       62.5       1,500       PC1-02B-24       24       33.3       800       PS1-01-24       24       25.0         15       100       1,500       PC1-02B-12       12       66.7       800       PS1-01-12       12       50.0

<sup>(b)</sup> Replace -2 with -G for RoHS compliant

<sup>[c]</sup> Add -G to end of part number for RoHS compliant

<sup>(d)</sup> Add -G to end of part number for RoHS compliant


#### VANTAGE Line – Westcor's Affordable Power Supply Option

Get the Westcor "advantage" of complete power supplies at a **15% discount**. Westcor's VANTAGE Line of power supplies was developed with all of the user configurability, field configurability, power density, and high efficiency that Westcor offers and with only minor specification changes. *Call a local Vicor Representative, or for your nearest Rep location go to vicorpower.com//company/contact\_us* 

38 U.S. & CANADA: 800-735-6200 VICORPOWER.COM

### AC-DC Westcor Division Configurable Power Supply

Web ExpressCode: flatpacen




VICOF

#### **General Performance** Refer to data sheet for detailed specifications

Product	Dimensions	Input Voltage	Output Power	Number of Outputs
FlatPAC-EN	9.2" x 5.0" x 1.4"	90 – 132 / 180 – 264 Vac	500 W	1 – 4
Hati AC EN	(233,7 x 127 x 35,6 mm)	250 – 380 Vdc	(425 W for EN compliance)	


(same model)

**Part Numbering** Ordering, see back for phone numbers



#### **Layout Configurations**

 Rugged: Meets MIL-STD-810E, category 10 for vibration



Note: The type of output connector a FlatPAC-EN has depends on which modules are used. For example, if a two output configuration uses two half bricks (instead of a full brick and half brick) this two output configuration will have the 18 pin Molex connectors, not stud connectors.

#### **VANTAGE Line** – Westcor's Affordable Power Supply Option

Get the Westcor "advantage" of complete power supplies at a 15% discount. Westcor's VANTAGE Line of power supplies was developed with all of the user configurability, field configurability, power density, and high efficiency that Westcor offers and with only minor specification changes. Call a local Vicor Representative, or for your nearest Rep location go to vicorpower.com/company/contact\_us

### AC-DC Westcor Division Configurable Power Supply

#### MegaPAC Family User & Field Configurable Power Supplies

The MegaPAC family consists of eight fan-cooled, configurable power supplies that enable users to factory configure almost any set of output requirements by combining appropriate slide-in output assemblies called ConverterPACs, with the appropriate chassis. The MegaPAC chassis has a standardized feature-laden front end with slots to accept the ConverterPACs. Models are available with single or three-phase AC inputs. MegaPACs will also operate from high-voltage DC input. Features include EMI / RFI filtering, enable / disable, general shut down, output sequencing and AC OK.

#### Features

- Output power: 200 4,000 Watts
- User-configurable outputs
- Up to 20 outputs
- DC input capability
- Power factor corrected (some models)
- Low ripple 10 mV p-p or 0.15%, whichever is greater (some models)
- Fan cooled
- Efficiency: >80%
- Agency approvals: UL, cTÜVus, CE Marked
- Low leakage option available (some models)
- Current sharing available

MegaPAC Family Accessories

Page 52




#### General Performance Refer to data sheet for detailed specifications

Product	Dimensions	Input Voltage	Output Power	# of Outputs	Slot Configurations
Mini	9.5" x 6.0" x 3.4" 90	) – 132/180 – 264 Vac; Strappable	e 1,000 W @ 115 Vac	1-10	ModuPAC, JrPAC,
MegaPAC	(241,3 x 152,4 x 86,4 mm)	260 – 380 Vdc	or 230 Vac	(5 slots)	DualPAC, RAMPAC, BatPAC
Autoranging	11.9" x 6.0" x 3.4"	90 – 132/180 – 264 Vac	1,200 W @ 115 Vac	1-16	ModuPAC, JrPAC,
MegaPAC	(302,3 x 152,4 x 86,4 mm)	260 – 380 Vdc	1,600 W @ 230 Vac	(8 slots)	DualPAC, RAMPAC, BatPAC
4 kW	17.0" x 7.5" x 4.9"	208 or 240 Vac; 3-Phase	2,000 W - 4,000 W, (3Ø)	) 1–20	QPAC, DualQPAC,
MegaPAC-EL	(431,8 x 190,5 x 124,5 mm)	260 – 352 Vdc	1,500 W, (1Ø)	(10 slots)	JrQPAC, QPAC (XQ)
PFC	12.3" x 6.0" x 3.4"	85 – 264 Vac	1,200 W @ 115 Vac	1-13	BatPAC, ModuPAC, JrPAC,
MegaPAC/HP	(312,4 x 152,4 x 86,4 mm)	100 – 380 Vdc	2,400 W @ 230 Vac	(8 slots)	DualPAC, RAMPAC, FinPAC
PFC	15.6" x 6.0" x 3.4"	85 – 264 Vac	1,200 W @ 115 Vac	1-13	QPAC, DualQPAC,
MegaPAC-EL/HPE	L (396,2 x 152,4 x 86,4 mm)	100 – 380 Vdc	2,400 W @ 230 Vac	(8 slots)	JrQPAC, FinQPAC
4 kW	14.0" x 7.5" x 4.9"	208 or 240 Vac; 3-Phase	2,000 W – 4,000 W, (3Ø	i) 1–20	ModuPAC, JrPAC, DualPAC,
MegaPAC	(355,6 x 190,5 x 124,5 mm)	260 – 352 Vdc	1,500 W, (1Ø)	(10 slots)	RAMPAC, BatPAC, UniPAC

Note: For detailed information, review specific product design guides available online at vicorpower.com

#### Part Numbering Ordering, see back cover for contacts



#### VANTAGE Line – Westcor's Affordable Power Supply Option

Get the Westcor "advantage" of complete power supplies at a **15% discount**. Westcor's VANTAGE Line of power supplies was developed with all of the user configurability, field configurability, power density, and high efficiency that Westcor offers and with only minor specification changes. *Call a local Vicor Representative, or for your nearest Rep location go to vicorpower.com//company/contact\_us* 

Web ExpressCode: megapac

RoHS

### AC-DC Westcor Division Configurable Power Supplies

#### **ConverterPACs** Output Power Up to 600 Watts

ConverterPACs incorporate VI-200 or VI-J00 and / or Maxi Vicor DC-DC converter bricks. For additional power, ConverterPACs can be paralleled. Some ConverterPACs are available for low-noise applications (VXI options, RamPACs and QPACs) and as current sources (BatPACs). All ConverterPACs can be easily removed in the field by loosening a single screw and sliding the unit out of the chassis.

#### VI-200 / VI-J00 ConverterPACs <sup>[a]</sup> Output Power Up to 200 Watts

For general electrical specifications for VI-200 / VI-J00 ConverterPACs, see module specifications on the VI-200 / VI-J00 data sheets in the library section of our website.



ModuPAC (M) Up to 200 W



JuniorPAC (J) Up to 100 W



RamPAC (R) Up to 100 W



BatPAC (B) Up to 200 W programmable current source



DualPAC (D) Dual outputs: Up to 100 W / output



QPAC (L) Up to 200 W



DualQPAC (LD) Up to 100 W / output



JrQPAC (LJ) Up to 100 W

Web ExpressCode: cpacs2

#### Maxi ConverterPACs <sup>[a]</sup> Output Power Up to 600 Watts

For general electrical specifications for Maxi ConverterPACs, see module specifications on the data sheets in the library section of our website.

<sup>[a]</sup> RoHS compliant ConverterPACs have a "G" added to their prefix (except the PZL where the RoHS version will be GPL).



UniPAC (XU) Up to 500 W



FinPAC (PZ) Up to 600 W



QPAC (XQ) Up to 500 W



FinPAC (PZL) Up to 600 W

Web ExpressCode: cpacs



Web ExpressCode: cpacs1

### Vicor CUSTOM

#### **Custom Power Solutions Designed To Fit Your Specific Needs**

#### Small company responsiveness, large company resources

The sole focus of Vicor Custom Power is designing and manufacturing turnkey custom power systems. Our custom power design centers maintain the flexibility of small entrepreneurial companies while taking advantage of Vicors technical and business resources to deal effectively with your most challenging power problems. Our total focus is on the power solution that best satisfies your needs.





#### Providing custom power solutions for:





INDUSTRIAL











COMMUNICATIONS

DATACOM

Locations: See our website page for complete details

TEST EQUIPMENT

MEDICAL

MILITARY / AEROSPACE TRANSPORTATION

Web ExpressCode: custom

#### **Custom Power Design Centers:**

**Aegis Power Systems** Tel: 1 828 837 4029 email: aegis@aegispower.com aegispower.com


**ConverTec Corporation** Tel: 1 651 604 0289 email: eswanson@vicorpower.com Freedom Power Systems Tel: 1 512 259 0941 email: sales@freedompower.com freedompower.com

**Granite Power Technologies** Tel: 1 603 623 3222 granitepower.com

**Mission Power Solutions** Tel: 1 760 631 6846 email: sales@mpwrs.com mpwrs.com

> m Power Solu 81

Northwest Power Integrations Tel: 1 503 652 6161 email: info@npi-inc.com npi-inc.com



# Vicor CUSTOM

#### **Capabilities Overview**

Vicor Custom Power has the capability to design, prototype, mass produce and certify a complete power system.

Design: Electrical and mechanical

- **Prototype:** By utilizing Vicor's standard power components, delivery of prototype units can be very fast and in some cases, just a matter of weeks.
- **Mass production:** Capacity to manufacture thousands of power systems per year.

Reliability / Certification:HALT (Highly Accelerated Life Test)Temperature CyclingBurn InThermal ShockHumidityAccelerated Life TestPower CyclingVibrationEMITransient ImmunityAltitudeExplosive AtmosphereMechanical ShockAcceleration







## Vicor Custom Off-the-Shelf Configurable Power Supplies

#### VME450<sup>™</sup> From Aegis Power Systems

Web ExpressCode: vme450

The single-slot VME450 power supply — filtered 28 Vdc, four output (3.3, 5, ±12 V), 550 W — is a MIL-COTS solution that is compliant to the vibration requirements of MIL-STD-810F and EMI per MIL-STD- 461E. When compared to VME power supplies using conventional technology, the one-slot VME450 provides users with higher efficiency (85%), lower weight (2.4 pounds), and higher power (up to 550 W).

**DC-DC MegaPAC<sup>™</sup>** From Mission Power Solutions

The DC MegaPAC allows users to instantly configure highly-efficient DC-DC power supplies. A complete power supply is configured by selecting and inserting up to eight slide-in output assemblies called "ConverterPACs". ConverterPACs incorporate one or two Vicor DC-DC converters and are available in a wide array of outputs and power levels. If output requirements change, the user can simply unlock a single screw and replace the slide-in

#### **Features**

- 28 Vdc per MIL-STD-704F
- 28 Vdc per MIL-STD-1275D
- Vin max range: 18 36 Vdc
- MIL-STD-461E conducted EMI
- Input power: 650 W
- Output power: 550 W
- 4 isolated outputs
- Temperature: -40 to +85°C
- Utilizes Vicor's V•I Chips
- Single slot VME

#### Web ExpressCode: dcmegapac



#### Features

- DC inputs: 12 72 V available
- Output power: Up to 16 outputs and 1,600 W total power (depending upon input voltage)
- Temperature rating: Full power to 45°C; half power to 65°C

ModuPAC assembly with one that has the desired rating.

- Dimensions: 3.4"H x 6.0"W x 12.0"L (86,3 x 152,4 x 304,8 mm)
- 9.25 lbs. fully configured
- Fan cooled
- Soft start for limiting inrush current

- Conducted EMI meets BTR 2511
- Remote sense capability and output overcurrent protection on all outputs
- Output overvoltage protection on most outputs
- Output overtemperature protection on all outputs
- Input over, under and reverse voltage protection
- Box-to-box paralleling capability
- Input temperature monitor, warning and shut down
- CE Marked

Consult back cover for a complete list of contacts.

44

### Vicor Custom Off-the-Shelf Configurable Power Supplies

#### Badger<sup>™</sup> From Mission Power Solutions

The Badger is a rugged PFC multi-output power supply, capable of withstanding extreme environments and stresses often inherent with military applications.

General Specifications Typical unless otherwise noted

Web ExpressCode: **badger** 

Web ExpressCode: javelin



Product	Dimensions	Input Voltage	Max # of Outputs	Maximum Power	Cooling	Notes
Badger	2.55" x 7.0" x 13.75" (64,8 x 177,8 x 349,3 mm)	85 – 264 Vac	12	1,800 W	Internal fans	OCP, OVP, and OTP on all outputs

#### Javelin<sup>™</sup> From Mission Power Solutions

The Javelin is an AC input power supply with a single DC output, capable of up to 5,400 W, in a rugged package suitable for industrial and military applications.



#### General Performance Refer to data sheet for detailed specifications

Product	Dimensions	Input Voltage	Max # of Outputs	Maximum Power	Cooling			
Javelin I	4.9" x 7.0" x 10.75" (124,5 x 177,8 x 273,05 mm)	85 – 254 Vac	1	600 – 1,800 W	Internal fans			
Javelin II	4.9" x 7.0" x 9.5" (124,5 x 177,8 x 241,3 mm)	85 – 254 Vac	1	600 – 1,800 W	No fan			
Javelin III	7.0" x 16.0" x 13.0" (177,8 x 406,4 x 330,2 mm)	85 – 254 Vac 3-Phase	1	1,800 – 5,400 W	Internal fans			

#### **PowerBank™** From Northwest Power Integrations

The PowerBank is a low-profile AC-DC switching power supply that offers up to six configurable outputs at up to 1,500 Watts.

#### **General Performance** Refer to data sheet for detailed specifications



Web ExpressCode: powerbank

Product	Dimensions	Input Voltage	Max # of Outputs	Maximum Power	Cooling	Notes
PB1004PFC	1.74" x 8.08" x 10.28" (44,2 x 205,2 x 261,1 mm)	85 – 264 Vac	4	1,000 W	Internal fans	Low power stand-by output
PB1005AC	1.68" x 7" x 10.5" (42,7 x 177,8 x 266,7 mm)	115/230 Vac 300 Vdc	5	1,000 W	Internal fans	SEMI F47 compatible
PB1506PFC	1.75" x 12.6" x 16.84" (44,5 x 320,04 x 427,7 mm)	90 – 264 Vac	6	1,500 W	Internal fans	Two aux. low power outputs
PBC1002AC	2.5" x 7.38" x 9" (63,5 x 187,5 x 228,6 mm)	115/230 Vac	2	1,000 W	Cond., conv., liquid	Customizable baseplate / heat sink
PBC1002PFC	2" x 6.5" x 13.5" (50,8 x 165,1 x 342,9 mm)	90 – 264 Vac	2	1,000 W	Cond., conv., liquid	Customizable baseplate / heat sink

### Evaluation Boards V-I Chip Products

### V•I Chip BCM

The BCM Evaluation Board has been designed to facilitate the verification of the V•I Chips superior performance in the areas of power density, efficiency (over a wide load range), fast response and quiet, low-noise operation. Adding the suffix "EB" to the BCM model number designates the Evaluation Board. For example the B048F120T30-EB specifies a 48 V to 12 V at 300 W BCM mounted to an Evaluation Board.

RoHS

Web ExpressCode: bcmeb

Example Number B048F120T30-EB

Web ExpressCode: viceb

#### PRM & VTM

The PRM and VTM Evaluation Boards allow the user to develop an understanding of Factorized Power Architecture (FPA<sup>™</sup>) using the PRM and VTM chip set. Simply select the PRM Evaluation Board to match your input voltage and VTM Evaluation Board to provide the desired output voltage and current and plug them together.

Example Number P045F048T32AL-CB



Example Number V048F040T050-CB

RoHS

#### High Voltage BCM

The HV BCM Evaluation Board is used for powering, testing and evaluating the 380 Vdc input BCMs. The HV BCM Evaluation Board is available as a Parallel Array Board with a 12 Vdc, 100 A output or as a Series Array Board with a 48 Vdc 25 A and / or 12 Vdc, 25 A with up to 1,200 Watts total.

#### Web ExpressCode: bcmpb



#### **PRM Constant Current Board**

The PRM Constant Current (CC) Demonstration Board is suitable for light-emitting diode (LED) applications such as street & stadium lighting, high-end projectors, active outdoor advertising and architectural installations. The board provides a precisely regulated current as required for direct drive multi-LED applications where the intensity and brightness are controlled by regulating the current through the LEDs.



Web ExpressCode: prmcc

Web ExpressCode: vibeb

RoHS

RoHS

Example Number P048F048T24AL-CC

# Evaluation Boards DC-DC VI BRICK Products

VI BRICK evaluation boards are available to verify the performance and simplify testing of VI BRICK modules. There are separate boards for the VI BRICK – PRM, VTM, BCM, and DC-DC converters.

#### Description

VI BRICK PRM evaluation board VI BRICK VTM evaluation board VI BRICK BCM evaluation board VI BRICK DC-DC evaluation board

#### Part Number

Add "-CB" suffix to the VI BRICK specific part #



46 U.S. & CANADA: 800-735-6200 VICORPOWER.COM

### Evaluation Boards DC-DC Brick / EMI Filters / Output Filters & Cool-ORing Products

#### Maxi, Mini & Micro

RoHS Three styles: Maxi, Mini or Micro Description Part Number Inboard and onboard compatible Maxi board style 24644R Easy I/O and control connections . Mini board style 24645R Includes fusing and capacitors . Micro board style 24646R Can be paralleled for higher power arrays

#### **OPI** Active EMI Filters & V•I Chip Optimized Filters

The QPI / QPO filter evaluation boards provide a quick and easy way to evaluate the EMI / EMC performance of the filters with a broad range of DC-DC converters. Available QPI input EMI filter boards include: boards compatible with V•I Chip evaluation boards, DOSA pin-out compatible evaluation boards, and universal style use "EVAL1" evaluation boards. QPO output ripple attenuator boards are available in a universal "EVAL1" configuration or with sockets compatible with Vicor Mini and Micro DC-DC converters.

#### Part Number Description

QPI-3-CB1<sup>[a]</sup> .....QPI-3LZ for 24 V input DC-DC up to 7 A QPI-4-CB1<sup>[a]</sup> .....QPI-4LZ for 48 V input DC-DC up to 7 A QPI-5-CB1<sup>[a]</sup> .....QPI-5LZ for 24 V input DC-DC up to 14 A QPI-6-CB1<sup>[a]</sup> .....QPI-6LZ for 48 V input DC-DC up to 14 A QPI-7-CB1<sup>[a]</sup> .....QPI-7LZ for 24 V input DC-DC up to 6 A, w/ integrated Hot-Swap QPI-8-CB1<sup>[a]</sup> .....QPI-8LZ for 48 V input DC-DC up to 6 A, w/ integrated Hot-Swap <sup>[a]</sup> The part numbers above are compatible with mounting DOSA compliant DC-DC converters.

For universal plug in evaluation boards substitute CB1 with EVAL1.

#### **QPI V-I Chip Optimized Filter Evaluation Boards**

QPI-9-CB1......QPI-9LZ for 24 V input V•I Chips up to 6 A, w/ integrated Hot-Swap QPI-10-CB1......QPI-10LZ for 48 V input V•I Chips up to 6 A, w/ integrated Hot-Swap QPI-11-CB1......QPI-11LZ for 24 V input V•I Chips up to 7 A QPI-12-CB1......QPI-12LZ for 48 V input V•I Chips up to 7 A

MQPI MIL COTS V•I Chip Optimized Filter Evaluation Board MQPI-18-CB1....MQPI-18LP for 28 V input V-I Chips up to 7 A

#### **QPO** Active Output Filters

#### Part Number Description

QPO-1-EVAL1....QPO-1LZ, 3 - 30 V input up to 10 A QPO-1-EVAL3....QPO-1LZ, board with sockets for Vicor Mini DC-DC converter QPO-1-EVAL5....QPO-1LZ, board with sockets for Vicor Micro DC-DC converter QPO-2-EVAL1....QPO-2LZ, 0.5 - 5.5 V input up to 20 A

#### **Cool-ORing** Discrete & Full-Function Active ORing Solutions

The Cool-ORing evaluation boards offer a quick and easy way for the user to complete functional testing of Picor's Cool-ORing solutions. These evaluation boards demonstrate solutions satisfying a range of Active ORing requirements, covering several typical redundant bus voltages. The user can chose to evaluate a discrete implementation or a high density integrated solution depending on system level requirements. The user can use the evaluation board to measure steady state efficiency as well as test dynamic performance of the Cool-ORing product under system level fault conditions.



# Web ExpressCode: **qpieb qpoeb**

Web ExpressCode: mmmeb

Web ExpressCode: coreb







#### Part Number Description

47

#### Mounting & Thermal Management

Web ExpressCode: mounting1

All parts are RoHS compliant unless otherwise noted

	Longitudinal Fins	Transverse Fins	Longitudinal Fins	Transverse Fins	Longitudinal Fins	Transverse Fins
VI-200	0.90" Fin	0.90" Fin	0.70" Fin	0.70" Fin	1.45" Fin	0.40" Fin
	(22,8 mm) 30089	(22,8 mm) 30090	(17,7 mm) 30775	(17,7 mm) 30193	(36,8 mm) 30780	(10,1 mm) 30194
	Longitu	dinal Fins	Transve	rse Fins	Transverse	Fins
00 <b>Г-</b> IЛ		0.90" Fin (22,8 mm) 30191		0.90" Fin (22,8 mm) 30771	Martin -	0.40 " Fin (10,1 mm) 30140
	Maxi He	at Sinks	Mini He	at Sinks	Micro He	eat Sinks
	Threaded	Through Hole	Threaded	Through Hole	Threaded	Through Hole
וal Fins		C. M. Market		and the		Carlieb
Longitudinal Fins	0.4" Fin (10,1 mm) 30482	0.4" Fin (10,1 mm) 30718	0.4" Fin (10,1 mm) 32188	0.4" Fin (10,1 mm) 30195	0.4" Fin (10,1 mm) 32174	0.4" Fin (10,1 mm) 30719
Го	0.9" Fin (22,8 mm) 30188	0.9" Fin (22,8 mm) 30181	0.9" Fin (22,8 mm) 30189	0.9" Fin (22,8 mm) 30182	0.9" Fin (22,8 mm) 30190	0.9" Fin (22,8 mm) 30183
e Fins	Witherstein		WWW .			A MARINE
Transverse Fins	0.4" Fin (10,1 mm) 30778	0.4" Fin (10,1 mm) 30720	0.4" Fin (10,1 mm) 30184	0.4" Fin (10,1 mm) 30721	0.4" Fin (10,1 mm) 32173	0.4" Fin (10,1 mm) 30722
Tra	0.9" Fin (22,8 mm) 30196	0.9" Fin (22,8 mm) 30723	0.9" Fin (22,8 mm) 30269	0.9" Fin (22,8 mm) 30724	0.9" Fin (22,8 mm) 30270	0.9" Fin (22,8 mm) 30725

#### V•I Chip Heat Sinks & Push-Pins

For use with PRM, VTM and BCM V•I Chip Power Components




Heat Sink (includes thermal interface)	Part Number	Push-Pins		Part Number (incudes spring)
Transverse Fins, 11 mm	32438	0.051"-0.069" F	РСВ	32434
Transverse Fins, 6.3 mm	32439	0.070"-0.104" F	PCB	32435
Longitudinal Fins, 11 mm	n 32440	0.105" - 0.132" F	РСВ	32436
Longitudinal Fins, 6.3 mr	n 32441	0.133" - 0.156" F	РСВ	32437

# Low-profile side-fin heat sinks – Height only 0.125" (3,1 mm) above module baseplate



#### **Thermal Management**

Web ExpressCode: mounting2



### **Mounting Standoffs**

Web ExpressCode: standoffs

#### **Module Standoffs** Standoffs and screws Bulk and single-module kits For mechanical mounting of VI-200 and VI-J00 Series modules. Also provides grounding of the module from the baseplate compatible with all standard mounting configurations. to the printed circuit board. (Sold individually) Description Part Number 0.525" (13,3 mm) Long 10692-01 0.25" (6,3 mm) Hex Sockets Sockets are available for all Vicor VI-200 and 30075 VI-J00 modules and are intended for applications 30074 **VIEW MECHANICAL DRAWINGS** requiring ease of module installation or removal. **ONLINE!** Vicor modules have nine pins, seven of which are vicorpower.com 0.040" and two are 0.080". Finish Part Number Pin Size 30074 0.040" (1,01 mm) Electro-tin 0.080" (2,03 mm) Electro-tin 30075

Minimum order quantities may apply.

#### ModuMate Socket Maxi, Mini & Micro Series

Web ExpressCode: **sockets** 

			brick (Ma	1XI)	Han	f <mark>brick</mark> (M	ini)	Quart	er brick (I	Vicro)	Use module
	ounting Style	Input	Output	5 Sets	Input	Output	5 Sets	Input	Output	5 Sets	pin style <sup>[b]</sup>
All	ourface mount	22100	22101	16017	22100	22102	16021	22103	22104	16025	S, F

#### SurfMate: Surface Mount Sockets [a]

#### InMate: Through Hole Sockets [a]

All sockets are supplied on InMate headers to assure proper alignment during installation

		Full	brick (Ma	axi)	Hal	f brick (M	lini)	Quart	er brick (	Micro)	Use module
Board Thickness	Mounting Style	Input	Output	5 Sets	Input	Output	5 Sets	Input	Output	5 Sets	pin style <sup>[b]</sup>
Nominal 0.062 " (1,57 mm)	Inboard	18374	18382	18362	18374	18384	18366	18376	18386	18370	S, F
Min / Max 0.055" / 0.071" (1,3 mm) (1,8 mm)	Onboard	18378	18388	18364	18378	18390	18368	18380	18392	18372	N, G
Nominal 0.094" (2,38 mm)	Inboard	18375	18383	18363	18375	18385	18367	18377	18387	18371	S, F
Min / Max 0.084" / 0.104" (2,1 mm) (2,64 mm)	Onboard	18379	18389	18365	18379	18391	18369	18381	18393	18373	N, G
Nominal 0.125" (3,17 mm) Min / Max 0.1125" / 0.1375"	Onboard	21539	21543	21510	21539	21544	21511	21540	21545	21512	N, G

[a] For individual input / output purchases, a 35-piece minimum (and multiples) applies to Maxis / Minis and a 40-piece minimum for Micros.
[b] Page 15 for pin styles.

#### Module Exchange Tool

Used in facilitating the proper extraction of modules from InMate or SurfMate sockets. **Removal without using the Exchange Tool may cause damage to the sockets.** 

Part Number
22827
22828
22829



#### Magnetics

Web ExpressCode: **chokes** 

	ation Transformer ation of PR Bus signal when used v	with Maxi Mini Micro	-	fferential Mode, Inpu	ut
	ions. Consult Vicor for applications		Inductance / Winding	DC Current / Resistance	Part Numbe
		t Number	22 µH	$12 \text{ A} / 5.8 \text{ m}\Omega$	33206
		29768	1 mH	4 A / 250 mΩ	36-00036
			Inductors, D	Differential Mode	
VI-HAM Lin The VI-HAM requi	e Filter res an external line filter. When use	ed in conjunction with	-	nay be used to reduce differential	output noise by
part number 30205, the VI-HAM / Filter combination will meet the			Inductance	DC Current (max.)	Part Number
requirements of w	vorldwide EMI standards.	t Number	0.2 µH	40 A	30268
		30205	27 µH	12 A	32012
			1.8 µH	10 A	32497
-	Common Mode rovide a high level of attenuation of	common-mode currents.	Common M	ode Output Inductor	s
Inductance /	DC Current /		Inductance	DC Current (max.)	Part Number
Winding	Resistance	Part Number	420 µH	20 A	36-00037
1000 µH	12 A / 6.5 mΩ	31743	350 µH	40 A	36-00029-01
3000 µH	7 A / 18 mΩ	31742	1.27 mH	10 A	36-00029-04
2163 µH	1 A / 42 m (low profile)	31943	70 µH	80 A	36-00029-06
1.3 mH	13 A / 14 mΩ	32006	110 µH	60 A	36-00029-07
Inductor, O	utput Sense Compens	ation			
<b>Inductance</b> 1 mH		<b>Part Number</b> 36-00030 <sup>[a]</sup>			
lot RoHS compliant					
anacita		pressCode: <b>caps</b>	Compos		ExpressCode: <b>coi</b>
apacito	rs		Compon		

Capacitor	s, X-type	<b>e</b> For filtering spe	cifications of FCC Level A.
Description			Part Number
"X" Cap., 0.68	3μF		11217
"X" Cap., 0.4	7 µF		03047
"X" Cap., 0.33	βµF		00927
"X" Cap., 0.22	2 μF		04068
"X" Cap., 0.1	5μF		03269
"X" Cap., 1.0	)μF		02573
Capacitor	s, Y-type	For EMI / RFI co	nsiderations.
Description			Part Number
"Y" Cap., 1,50	00 pF		00770
"Y" Cap., 4,70	00 pF		01000
"Y" Cap., 0.0			01501
"Y" Cap., 0.02	22 µF		03093
"Y" Cap., 4,70	00 pF - S	SMT version	25283
"Y" Cap., 1,50	00 pF 5	MT version	30802
Capacitor	s, Hold u	qu	
Product	Descrip	tion	Part Number
VI-AIM	270 µF, 2	200 V	30769
	270 µF, 4	00 V	30240
VI-HAM	470 µF, 4	50 V	30249
FARM / ARM	1,200 µF,	200 V	30275

30483

Minimum order quantities may apply.

2,200 µF, 200 V

MOVs For use with f	front-end modules.	
Description		Part Number
275 V MOV, 14 mm D	isc	30076
68 V MOV, 10 mm Dis	C	30234-068
120 V MOV, 10 mm D	isc	30234-120
200 V MOV, 10 mm D	isc	30234-200
220 V MOV, 10 mm D	isc	30234-220
Gas Discharge	Tube For use with t	the ENMods and VI-ARM.
Part Number	Spark Over (DC)	
13755	220 V	
26107	75 V	13755



**Connector Kits** FlatPAC, FlatPAC-EN, LoPAC, MegaPAC & PFC FrontEnd products

Web ExpressCode: connects

CSB02

All parts are RoHS compliant unless otherwise noted

#### **FlatPAC Accessories**

#### Input and Output Retrofit Kits

**Description** Input connector Output connector Part Number 14136<sup>[a]</sup> 14137<sup>[a]</sup>

Input and Output Mating Connectors				
Description	Part Number			
Input connector, 6 pin <sup>[b]</sup>	33100			
Output connector, 5 pin [b]	16385 <sup>[a]</sup>			

<sup>(a)</sup> Not RoHS compliant

[b] Insertion tool for use with FlatPAC input / output connectors are available from AMP, Inc., part number 58074-1. Manual hand tool, part number 58246-1, interchangeable head.

#### **LoPAC Accessories**

Connector Kits	
Description	Part Number
PFC Mini	19-130047
PFC Micro, PFC MicroS	19-130044
Current Share Boards	
Description	Part Number
Description LoPACs using VI-200 and VI-J00 Series modules	Part Number CSB01

#### **PFC FrontEnd Accessories**

Description	Part Number
Din Rail Mounting Kit	19-130060
Connector Kit	19-130059
VIPAC Array Adapter	19-130064

### MegaPAC Accessories

Connector Kits	
Description	Part Number
Single-phase input	19-130040
Three-phase input	19-130041
DualPAC / Dual QPAC output ConverterPacs	19-130042
Air block	96-00032-01
Current Share Boards	
Description	Part Number
MegaPACs using VI-200 and VI-J00 Series modules	CSB01

MegaPAC chassis and ConverterPACs can be purchased separately for scalable systems and / or spares.

#### **Bus Bars**

MegaPAC using Maxi modules

Description	Part Number
2 holes	88-00033-01
3 holes	88-00033-02
4 holes	88-00033-03
5 holes	88-00033-04
Series bus bar	88-00043

#### **FlatPAC-EN Accessories**

Connector Kit Description FlatPAC-EN	<b>Part Number</b> 19-130044
Current Share Boards FlatPAC-EN using VI-200 and VI-J00 Series modules	CSB01
FlatPAC-EN using Maxi, Mini and Micro Series modules	CSB02

12 U.S. & CANADA: 800-735-6200\_VICORPOWER.COM Consult back cover for a complete list of contacts.

### **QUALITY** Technical Information

#### Quality System

Web ExpressCode: qual

We use the "Plan-Do-Check-Act" model (PDCA) to foster continuous improvement. We focus on key performance metrics that are continuously measured and reviewed. This enables us to be proactive in improving our technology, our products, our processes, and our service to our customers.

#### **Quality Center Online**

- Explore Vicor's quality systems through a robust library of documentation, videos, and process charts.
- Generate a report based on ISO 9001:2000 criteria • that entirely meets your specific requirements.
- Get your report in PDF format with hyperlinks to • videos and other information of your choosing.

**Quality Library** See and hear quality systems at work

- White papers on specific quality issues
- ISO 9001:2000 certificates
- RoHS compliant information .
- Contact our quality team







Play Video 3



Play Video >>



Plav Video >>

Play Video >>



Browse

Create

Customize and Create a Report 📑

Vicor's Quality Process

**Custom Quality Reports** 

Standard Quality Reports

**Experience Vicor's** 

**Quality Center** 

vicorquality.com

Download







Play Video >>



Play Video >>

Play Video >>

### **RoHS** Technical Information

### **RoHS** Compliance

Vicor Corporation has a strong commitment to protecting our environment. As an ISO 9001:2000 registered company and a member of the global community, we are dedicated to meeting government regulations, international standards, and our customers' requirements. To those ends, we have developed and currently maintain Environmental Management Systems (EMS) and the requisite controlled business, design, and manufacturing processes to service our worldwide customer base.

#### ISO 9001:2000 Certified

Vicor is dedicated to developing and maintaining design and manufacturing processes to competitively service our world-wide customer base that meet government regulations, international standards, and our customers requirements.



U.S. & CANADA: 800-735-6200 VICORPOWER.COM Consult back cover for a complete list of contacts.

53

# VICORPOWER.COM

### Use the Power of the Web

Develop your power solution by going to vicorpower.com. It's one of the premiere power-conversion sites on the web. Vicorpower.com is especially designed to get you the information you need quickly. And, through Vicor's unique mass-customization capabilities, we can provide you with exactly the power specifications you want at a price that's always affordable. Whether it's converters, user-configurable or custom power, Vicor has the high-value solution.

#### Here's what you'll find on vicorpower.com

- Design Guides and Application Notes
- Data sheets and mechanical drawings for all Vicor products
- PowerBench product configurators and a converter simulator that specifically analyzes your best options
- Technical seminars with synchronized video, PowerPoint, and access to related resources
- Webcasts on technical subjects of interest
- Application demonstrations
- Online Product & Military catalog with direct links to product pages, data sheets, and mechanical drawings
- Dedicated quality site with detailed factory tour and a custom quality report generator
- Technical articles that cover a huge range of applications challenges

#### vicorpower.com

Experience one of the premiere power conversion sites on the web

Feel free to contact Applications for any technical questions you may have at 1-800-927-9474 or Customer Service for price and delivery at 1-800-735-6200. For all other phone numbers, please consult back cover.



DATA SHEETS

VIDEOS



CONFIGURATORS



QUALITY CENTER

54

### **PowerBench<sup>™</sup>** Online Product Configurator Tools



#### **Do-It-Yourself Power Design** Custom Design Systems

Web ExpressCode: pwrb

Design your own DC-DC converter or configurable power supply online – anytime using Vicor's custom configurators. Designs that you create are saved in your "My Designs" account for future review and editing. You register only once to access all Vicor's custom configurators via the "Single Sign-On" feature.

With Vicor's PowerBench Custom Module Design System you can design your own DC-DC converters using our proprietary simulator or using hundreds of predefined designs. You simply specify design parameters such as input voltage range, output voltage set point, output power, packaging, and environmental options. A true expert system, our Custom Module Design System generates a variety of valid designs, ranks them all, and selects the optimum one. A unique part number, unit price, and delivery schedule will be returned to you. You can even order online.

PowerBench's VCAD<sup>™</sup> is a patented system that enables users to specify online, the design of Vicor's VIPAC family from available input voltages, output configuration, thermal features, mechanical configurations, and an optional power up / power down sequencing feature.

PowerBench's VSPOC<sup>™</sup> enables the registered user to specify and verify complete AC-DC power supplies in real time. The system is fully integrated with Westcor manufacturing operations. Once the user approves the product configuration, a bill of materials is generated and an order can be placed immediately.

Vicor is committed to meeting designers' needs via mass customization. All our manufacturing facilities have this capability. We'll support you with the best applications group in the industry. Thousands of designers worldwide have taken advantage of custom Vicor DC-DC converters and power supplies designs. You can, too.



Design your own DC-DC converters at vicorpower.com/powerbench



SINGLE SIGN-ON



#### **My Designs**

An online tool for storing the designs you create

### SUPPORT Applications

#### **Locations Around The World**

Vicor understands that technical support is critical to our customers. As a result, the Vicor Applications Engineering staff is comprised of technically competent, highly experienced field applications engineers who provide our customers with detailed technical support — within 24 hours — anywhere in the world. Our Applications Engineers, each with a thoroughly equipped lab, are established in locations across the globe ready to assist you in the pursuit of the optimum power solution.

#### Specifically, Vicor Field Applications Engineers offer:

- Evaluation and recommendation on specific customer design issues backed by a team of factory based Product Line Engineers.
- Answers to your technical questions by phone, fax, email, or via the Vicor website.
- Assistance with component-based power system design and power architecture assessment.
- Support for user needs through visits to your facility or at the FAE's lab.
- Technical presentations / seminars, both scheduled and on demand, at your site or elsewhere.
- A comprehensive library of up-to-date design guides, application notes, and technical articles easily accessible on the Vicor website.

This highly skilled team – assembled to include a wide range of engineering experience – has helped users develop component power solutions for thousands of applications in nearly every market segment.

Contact the Vicor Applications Group and experience Vicor's special commitment to your design. There's one goal at Vicor: to help you optimize your power design quickly and affordably. Our worldwide applications engineering staff is ready to give you technical support — NOW!

We can easily be reached by telephone or email, in North America at 800-927-9474, in Europe at 00 800 8426 7000 or in Asia at +852-2956-1782 and by email: <u>apps@vicorpower.com</u>.



### MIL-COTS V-I Chips

#### Web ExpressCode: mvichips DC-DC V-I Chip Modules 28 V Regulator, Voltage Transformer, & Bus Converter \_

VTMs put isolated current multiplication and voltage division directly at the point of load (POL), and an upstream PRM (Regulator) controls the factorized bus voltage supplied to the VTM to provide line and load regulation. Together, the PRM and VTM chip set provides the full functionality of a DC-DC converter, but with breakthrough performance and flexibility in a rugged, miniature package. The BCM (Bus Converter Module) functions as a fixed-ratio DC-DC transformer and provides an isolated bus voltage to power the PRM and VTM chip set or other loads.

The MIL-COTS PRM operates from a wide input range of 16 – 50 Vdc, meeting many of the ground vehicle and airborne requirements of MIL-STD-1275 and MIL-STD-704. Rated for 120 W, the 28 V PRM produces a nominal factorized bus voltage of 36 Vdc, controllable over the range of 26 – 50 Vdc. The downstream isolated VTM is available with twelve voltage division ratios from 1:1 to 1:32 and provides the user with flexibility to supply up to 100 A or 120 W at any output voltage from 1 – 50 Vdc in a surface-mount package occupying only 1 in<sup>2</sup>. The MIL-COTS BCM is a high efficiency Sine Amplitude Converter (SAC) operating from a 240 to 330 Vdc primary bus to deliver an isolated 30 – 41.2 V nominal, unregulated secondary.

#### **Features for PRM**

- Input range: 16 50 Vdc
- 1.3 MHz switching frequency
- Efficiency: 95%
- -55°C to +125°C operation (Tj)
- ZVS buck-boost regulator

#### **Features for VTM**

- Isolated 1–50 Vdc output
- 1 µs transient response
- 3 MHz switching frequency
- Efficiency: Up to 96.5%
- –55 to +125°C operation (Tj)

### **Features for BCM**

- Input range: 240 330 Vdc
- Output range: 30.0 41.2 Vdc
- MIL-STD-704E/F Compliant
- Efficiency: >95%
- –55 to +125°C operation (Tj)


#### Web ExpressCode: mvib

### MIL-COTS VI BRICKS PRM / VTM Thermally Enhanced Package

The **PRM** Regulator Module is a very efficient non-isolated regulator specifically designed to provide a controlled Factorized Bus distribution voltage for powering downstream VI BRICK Voltage Transformation Modules. In combination, VI BRICK PRMs and VTMs form a complete DC-DC converter subsystem offering all of the unique benefits of Vicor's Factorized Power Architecture (FPA): high density and efficiency; low noise operation; architectural flexibility; extremely fast transient response; elimination of bulk capacitance at the point of load (POL); in a thermally enhanced package.

MQPI-18 Input EMI Filter

The MQPI-18 is a surface mount DC front-end filter that provides EMI filtering for Vicor's 28 V DC-DC V-I Chip or VI BRICK modules. The MQPI-18 enables designers to meet conducted emission / conducted susceptibility per MIL-STD-461E. The MQPI-18 accepts an input voltage of 10 – 80 Vdc and delivers output current up to 7 A.



The thermally enhanced **VTM** voltage transformer excels at speed, density and efficiency to meet the demands of advanced power applications. Combined with the PRM regulator they create a DC-DC converter with flexibility to provide isolation and regulation where needed. The PRM

can be located with the VTM at the point of load or remotely in the back plane or on a daughtercard.



### **MIL-COTS Product Catalog**

This document provides in-depth information on Vicor's line of MIL-COTS standard products, including DC-DC converters, custom solutions, and technical support.

- Environmental stress screening and MTBF
- Environmental gualification
- Custom configured modules
- Field tested... proven reliability

#### Visit vicorpower.com

to view the Military Catalog online. This will give you instant access to all technical documentation for a MIL-COTS product.









# **SUPPORT** Customer Support Specialists

### Ready to assist with all your power needs

Our worldwide staff of customer support representatives and applications engineers is at your service to assist in determining the most appropriate power solutions for your system and to assure the quickest delivery of prototype quantities.

#### Customer Support Representative can:

- Provide price and delivery information
- Help select the most appropriate product for your application
- Arrange a visit to your site by a Vicor applications engineer or sales representative
- Fulfill literature requests
- Process purchase order requirements .
- Provide order status information.

Vicor accepts VISA, MasterCard, American Express, a bank check or money order; an open account with established credit, or COD. Most products are covered by a two-year limited warranty. See vicorpower.com for Vicor's terms and conditions along with our complete warranty statement. F.O.B. Andover, Massachusetts, and Sunnyvale, California. For international pricing, please contact your local Vicor office or distributor.

Let us help you find the right solution. With offices around the world, Vicor is eager to help you meet your power needs. Our highly trained sales staff can help you find a solution that's right for your business.

Call us today. In North America call 1-800-735-6200. In Europe call 00-800-8426-7000.





#### USA vicorpower.com

Vicor Corporation (Corporate Headquarters) 25 Frontage Road Andover, MA 01810-5413

**For General Information** Tel: 978-470-2900 Fax: 978-475-6715

For Technical Support Tel: 800-927-9474 Fax: 978-749-3341 Email: apps@vicorpower.com

VICOR

For Sales Support In U.S. & Canada: 800-735-6200 Fax: 978-475-6715 Email: vicorexp@vicorpower.com

**Vicor Corporation** Lombard, IL Tel: 630-769-8780 Fax: 630-769-8782

Vicor, Westcor Division Sunnyvale, CA Tel: 408-522-5280 Fax: 408-774-5555 westcorpower.com

Picor Corporation Slatersville, RI Tel: 401-235-1100 Fax: 401-235-1117 picorpower.com Europe

vicoreurope.com

Vicor France Tel: +33 1 34 52 18 30 France: 0800 419 419 Benelux: 00 800 419 419 20 Fax: +33 1 34 52 28 30 Email: vicorfr@vicorpower.com

Vicor Germany Tel: +49 89 962 439 0 Germany: 0800 018 29 18 Denmark: 00800 8426 7000 Austria: 0800 20 37 27 Fax: +49 89 962 439 39 Email: vicorde@vicorpower.com

Vicor Italy Tel: +39 02 22 47 23 26 800 899 677 Fax: +39 02 22 47 31 66 Email: vicorit@vicorpower.com

Vicor UK Tel: +44 1276 678222 UK: 0800 980 8427 Sweden: 020 794 143 Fax: +44 1276 681269 Email: vicoruk@vicorpower.com

#### Asia-Pacific

Vicor Japan Co., Ltd. Tel: +81-3-5487-3880 Fax: +81-3-5487-3885 vicorpower.jp

Vicor Hong Kong Tel: +852-2956-1782 Fax: +852-2956-0782 vicor-asia.com

In Latin America: Argentina: 800-555-4288 Brazil: 0800-890-0288 Mexico: 011 52 333 647 7881

Ask the operator to connect you to: 800-735-6200.

#### **Vicor Custom**

Vicor Custom Technical Support Tel: 800-496-5570

**Aegis Power Systems** 

Murphy, NC Tel: 828-837-4029 Fax: 828-837-4106 Email: aegis@aegispower.com aegispower.com

**Convertec Corporation** 

Roseville, Minnesota Tel: 651-604-0289 Fax: 651-604-0293 Email: eswanson@vicr.com

#### **Freedom Power Systems**

Cedar Park, TX Tel: 512-259-0941 Fax: 512-259-4438 Email: sales@freedompower.com freedompower.com

**Granite Power Technologies** 

Manchester, NH Tel: 603-623-3222 Fax: 603-627-3222 Email: tduff@granitepower.com granitepower.com

#### **Mission Power Solutions**

Oceanside, CA Tel: 760-631-6846 Fax: 760-631-6972 Email: sales@mpwrs.com mpwrs.com

**Northwest Power Integrations** 

Milwaukie, OR Tel: 503-652-6161 Fax: 503-652-6868 Email: info@npi-inc.com npi-inc.com